
Varistor Products Thermally Protected Varistor Module > LSP05

LSP05 Module Series





Agency Approvals

Agency	Standard	Agency File Number
c 711 °us	UL1449 3rd Edition	E320116

Applications

- Outdoor and Commercial LED Lighting
- Roadway lighting
- Traffic lighting
- Digital signage
- Wash wall lighting
- Parking garage/lot lighting
- Flood lighting
- Tunnel lighting
- Street lighting

Description

The Littelfuse LSP05 thermally protected Surge Protective Device is a self-protected device which is specially designed to be used in outdoor and commercial LED lighting fixtures for transient overvoltage protection. It is constructed with Littelfuse thermally protected varistor technology. Its built-in thermal disconnect function provides additional protection to prevent catastrophic failure and fire hazard even under the extreme circumstances of varistor end-of-life or sustaining over voltage conditions. The LSP05 SPD facilitates customer's product compliance to IEEE C62.41.2 Location Category C Low and US Dept of Energy MSSLC Model Spec.

Features

- Maximum Discharge Current, 10kA, 8/20us
- Meets ANSI C136.2/ IEEE C62.41.2 Location Category C Low Exposure
- Parallel connected SPD device
- Thermally protected Varistor technology
- IP66 Water-proof and Dust-proof
- Indication wire lead options for Parallel connected modules

- CE Compliance IEC61643-11 Class II/ EN61643-11 Type 2
- Compact form factor (48x48x30mm) with mounting tabs
- 240Vac and 277Vac voltage ratings are CE compliant and available for Class I and Class II installation based on IEC protection classes

Additional Information









Samples

Notes:

- 1. These parts are in compliance with IEC61643-11 Class II (Low Voltage System) and EN61643-11 Type 2 (Low Voltage System).
- 2. Tested for temporary overvoltage from low-voltage system faults per IEC 61643-11

Absolute Maximum Ratings

• For ratings of individual members of a series, see Device Ratings and Specifications chart

	LSP05 Series	Units
Continous:		
Steady State Applied Voltage:		
Max AC Voltage Range (V _{MIACIRMS})	150 to 510	V
Transient:		
Maximum Discharge Current 8/20µs Waveform (Imax)	10,000	A
Nominal Discharge Current 8/20µs Waveform (I _n)	5,000	А
Operating Ambient Temperature Range (T _A)	-45 to +85	°C
Storage Temperature Range (T _{STG})	-45 to +125	°C
Isolation Voltage Capability (When the thermal disconnect opens)	600	V
Insulation Resistance	>1,000	ΜΩ

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.



LSP05 Series Device Ratings & Specifications


Part Number	Operating Voltage (VAC)	MCOV/Uc (VAC)	Maximum Discharge Current (Imax)(A) ²	Nominal Discharge Current (In)(A)¹	MLV (V)³	Up (V) ⁴	
LSP05120P	120	150	10,000	5,000	L-N:680 L-G:680 N-G:630	800	
LSP05240P	240	275	10,000	5,000	L-N:1100 L-G:1100 N-G:1100	1200	
LSP05277P	277	320	10,000	5,000	L-N:1270 L-G:1270 N-G:1220	1400	
LSP05347P	347	420	10,000	5,000	L-N:1600 L-G:1600 N-G:1580	1700	
LSP05480P	480	510	10,000	5,000	L-N:1780 L-G:1780 N-G:1730	1900	
LSP05240LLP	L-L:240	L-L:275	10,000	10.000	F 000	L-L:1100	L-L:1200
	L-N/G:120	L-N/G:150		5,000	L-N/G:680	L-N/G:800	
LSP05480LLP	L-L:480	L-L:510	10,000	10,000	5,000	L-L:1780	L-L:1900
	L-N/G:277	L-N/G:320		3,000	L-N/G:1270	L-N/G:1400	


Notes

- 1. Nominal Discharge Current (In)(A): The nominal discharge current is a measure of the SPDs endurance capability; 15 impulses of discharge current uses the 8/20us current waveform.
- Maximum Discharge Current (Imax)(A): The maximum discharge current is a measure of the SPDs maximum capability; single impulse of discharge current uses the 8/20us current waveform.
 MLV UL1449 Measured limiting voltage; the highest value of residual voltage measurements during the application of impulses of 8/20us nominal discharge current (In); an average
- voltage value of 15 impulses
 4. Up IEC 61643-11 Voltage protection level; the highest value of residual voltage measurements during the application of impulses of 8/20us nominal discharge current (In); a rounding voltage value of maximum measurement.

Dimensions

Typical Dimensions (mm)







Notes:

- 1. Black: Line; White: Neutral; Green: Ground (P/N with suffix X3333/X3316: Brown: Line; Blue: Neutral; Green-Yellow stripe: Ground)
- 2. Black: R1; Red: R2; Blue: R3
- 3. Wire Gauge: AWG14 wire Line in, AWG22 Wire for indication; Wire Length: 100mm or customized




Application/Installation Schematic







Notes:

1. LED indicator and associated circuitry are not included in the module.





Part Numbering System



X3333: with GND wire connection, available for 240Vac and 277Vac rating with CE Marking for Class I earth installation.

X3316: without GND wire connection, available for 240Vac and 277Vac rating with CE Marking for Class II unearth installation.