

ZS20-1A, ZS20-1B, ZS20-1C, ZS20-1K, ZS20-1L, ZS20-1P

POWER SUPPLIES

- Universal AC input range 90-264 V
- Universal DC input range 124-370 V
- High efficiency up to 87%
- Boost power capability 150%
- Hiccup mode
- Build-in "Power good" relay (ZS20-1B, ZS20-1C only)
- Isolation class II
- Suitable for indoor use
- DIN rail and Wall mounting















Power Supplies: One Solution, Many Application

Power Supplies Selection Chart

| Model | Size | Description |
|---------|---------------|--|
| ZS20-1P | 18x90x62 mm | I/P.:- Single-Phase: 115-230 VAC, O/P:- 24VDC / 0.63A, 15W |
| ZS20-1K | 54x90x62 mm | I/P.:- Single-Phase: 115-230 VAC, O/P:- 24VDC / 1.5A, 36W |
| ZS20-1L | 54x90x62 mm | I/P.:- Single-Phase: 115-230 VAC, O/P:- 24VDC / 1.75A, 45W |
| ZS20-1A | 54x90x62 mm | I/P:- Single-Phase: 115-230 VAC, O/P:- 24VDC / 2.50A, 60W |
| ZS20-1B | 55x110x105 mm | I/P.:- Single-Phase: 115-230 VAC, O/P:- 24VDC / 5.0A, 120W |
| ZS20-1C | 55x110x105 mm | I/P.:- Single-Phase: 115-230 VAC, O/P:- 24VDC / 7.5A, 180W |

More Flexibility In Input Voltage Wide Range

The power supplies ZS20-1B and ZS20-1C are suitable to wide range input voltage. With a single type it is therefore possible to meet almost all application and consequently improve design and inventory management.

More Power: "Power Boost"

As an example, ZS20-1C is a 24V dc Power supply that features acontinuous duty current of 5A at 60°C and a Power Boost of 150%, equivalent to 7.5A for at least 3min. This features allows the use of a smaller size instrument to power demanding loads such as motors, solenoid valves, lamps and other loads with transient overload behavior which would otherwise required an oversize power supply.

More Power At Changing Rated Temperature

As an example, ZS20-1C can be the right solution for two design cases in different temperature conditions:

- 1) 7.5A, 24V dc in continuous duty at 40°C.
- 2) 5A, 24V dc in continuous duty at 60°C + Power Boost 7.5A for at least 3 min.

Three Modes for Output Protection ON SITE

Hiccup Mode Automatic Restart

This is the default factory setting of all Zs20 units. In case of short-circuiting or overloading, the output current is interrupted. The device tries again to reestablish output voltage and normal condition about every 2 second till the problem is cleared.

Manual Reset Manual Restart By Operator

In case of short-circuit or overload, the output current is interrupted. In order to restart the output it is necessary to switch-off the input circuit for about 1 minute.

This protection mode is particularly suggested in application where safety procedures require that reset be carried out only be an authorized person.


Continuous Output Mode


In case of short –circuit or overload, the output current is kept at high values with near zero voltage. In case of short circuit the current can reach up to 3 times the rated current at 60°C. This protection mode is used to meet the requirements of demanding loads such as motors, solenoid valves, lamps, PLC with highly capacitive input circuits and other loads with marked transient overload behavior.


POWER SUPPLIES



Power Supplies: One Solution, Many Application







"Power Good" Relay For Monitoring The Output Voltage Level

Output voltage is continuously monitored. The units ZS20-1C and ZSC20-1B are equipped with Power Good relay. The NO contact triggers any time the output voltage level goes below 20VDC. This feature is particularly useful in redundant applications.




Reduced Dimensions & Snapon DIN Rail Bracket

The higher performances obtained with the ZS20 Line, allow almost half dimensions as conventional technology and higher performances. An example is ZS20-1A 60W with maximum current till 6A. In permanent duty at 40°C it can deliver 3A at 24V DC. All ZS20 units feature the new DIN rail mounting bracket, easy to use and safe against heavy loading and vibrations.



Output Circuits Protected By Magneto-thermic Circuit Breakers

Standard output circuit breakers can be triggered quickly and reliably with ZS20 technology, which allows three times the nominal current at 60°C. Defective current paths are selectively disconnected, the defect is limited and the important parts of the system remain in operation. This together with the 50% overload capacity in compliance with EN60204-1 allows to safely manage any overload and short circuit condition.



Applications In Compliance With The Standard EN 60204-

ZS20 units comply with the standard requirement that an overload of 50% over the nominal current be withstand by the power supply for at least 1 hour to allow the tripping of magneto-thermic switches on the output. These features allows the implementation of "Control of commands and Emergency stops" by means of industrial PC's, PLC, remote I/O, etc. required by the standard. LUMEL supplies a table for the sizing and length of connecting cable and the choice of proper magneto thermic switches.

A New Way To Make And Use Power Supplies

Yet another strong proposition by LUMEL for power supplies and power continuity specialists. LUMEL aim is to provide designers and users with a complete range of solutions in power supplies and power continuity products, focusing on both standard special application. Our target is to deliver problem free solutions so that you can safely dedicate your attention to the reset of the automation project. The ZS20 tehnology is the result of these corner stones of our corporate identity. Designed taking into account the pressure to optimal use of space, ZS20 units are very compact in size. The wide input voltage range allows to have just one article for many applications and minimize stock.

ZS20 is based on semi-resonant switching circuit which allows efficiency up to 87% and a very dynamic and robust power supply to a wide range of loads such as PLC, sensors, motors, resistive/inductive loads etc. The ZS20 range conforms with the highest quality standards and guarantees a reliable and durable operation with a MTBF upto 5,00,000 hours and a 3 year warranty.



| Power Supplies | | MAT STATE OF THE S | 10. 2000 10. 275 10. 275 | 2.000 |
|----------------|---|--|---|--|
| ō | Model | ZS20-1P | ZS20-1K | ZS20-1L |
| Data | Input Type | 1-Phase | 1-Phase | 1-Phase |
| Input Data | Rating | 24V / 0.63A | 24V / 1.5A | 24V / 1.75A |
| | Input Voltage | 115 / 230 V AC | 115 / 230 V AC | 115 / 230 V AC |
| | Input Voltage Range AC | 85 264 VAC | 85 264 VAC | 85 264 VAC |
| | Input Voltage Range DC Turn on delay after | 120 370 VDC | 120 370 VDC | 120 370 VDC |
| | applying mains Voltage | 1 second | 1 second | 1 second |
| | Frequency | 45 65 Hz | 45 65 Hz | 45 65 Hz |
| | Line Regulation | < ± 0.5 % | < ± 0.5 % | < ± 0.5 % |
| | Load Regulation | $< \pm 0.5$ % (change in load, | $<\pm0.5$ % (change in load, | < ±0.5 % (change in load, |
| | Lodd Regulation | static 10 % 90 % | static 10 % 90 % | static 10 % 90 % |
| | Input Current | 0.3 A (230 VAC), 0.4 A (115 VAC) | 0.48 A (230 VAC), 0.88 A (115 VAC) | 0.55 A (230 VAC), 0.95 A (115 VAC) |
| | Inrush Current | ≤ 36 A Typically | ≤ 36 A Typically | ≤ 36 A Typically |
| | Internal Fuse | T2 A | T4 A | T4 A |
| | External Fuse | 10 A (curve B) | 10 A (curve B) | 10 A (curve B) |
| | Output Voltage Range | 24 VDC +/-3% | 24 VDC +/-3% | 24 VDC +/-3% |
| | Adjustment Range (Vadj) Start up with Capacitive Load | _ | 22 - 27 Vdc | 22-27 VDC |
| | Output Current (@ 40°C) | 0.63A @ 40°C | | 1.75A @ 40°C |
| | Output Current (@ 50°C) | 0.63A @ 40 C 0.63A @ 50°C, 0.48A @ 60°C | 1.5A @ 50°C, 1.125A @ 60°C | 1.75A @ 40 C |
| | Power Boost (@ 60°C) for 3 minutes | 0.63 A | 1.5 A | 1.75 A |
| | Power | 15W | 36W | 45W |
| 8 | Hold Up Time | ≥ 50 msec (230 VAC) | ≥ 50 msec (230 VAC) | ≥ 30 msec (230 VAC) |
| Output Data | Parallel Connection | No | No | No |
| Δ | | | | |
| 2 | Derating | from 50°C 2.5% /°C | from 50 °C 2.5% / °C | from 50°C 2.5% /°C |
| 5 | Efficiency | > 87 % (for 230 VAC and nominal values) | | > 87 % (for 230 VAC and nominal values) |
| ō | Dissipation Power Load Max (W) | 2.24 W | 4.4 W | 2.24 W |
| | Output Over Voltage Protection | 35 VDC | 35 VDC | 35 VDC |
| | | short circuit, overload, over voltage, | short circuit, overload, over voltage, | short circuit, overload, over voltage, |
| | Protection | over temperature | over temperature | over temperature |
| | Protection Modes | Hiccup | Hiccup | Hiccup |
| | Ripple and Noise | ≤ 150 mVpp (with nominal values) | ≤ 150 mVpp (with nominal values) | ≤ 150 mVpp (with nominal values) |
| | Short Circuit Current (Permanent) | Not Available | Not Available | Not Available |
| | Resistance to reverse feed | max 35 VDC | max 35 VDC | max 35 VDC |
| | Relay Power Good | Not Available | Not Available | Not Available |
| eneral Data | RoHS Compliant | Yes | Yes | Yes |
| _ | Isolation Voltage (IN/OUT) | 3000 VAC | 3000 VAC | 3000 VAC |
| ō | Isolation Voltage (IN/PE) | _ | _ | _ |
| ne | Isolation Voltage (OUT/PE) MTBF | | - 450 000 by according to IEC (1700 | |
| Ģ | Safety Approvals | CE | CE | > 1 100 000 hrs according to IEC 61709 CE |
| | Type | DIN Rail | DIN Rail | DIN Rail |
| ij | Position (Recommended) | Vertical | Vertical | Vertical |
| Mounting | Location | Indoor | Indoor | Indoor |
| Ŵ | Environment (Preferred) | Dust Protected Panels | Dust Protected Panels | Dust Protected Panels |
| Compliance | Norms and Certifications | According to EMC and Low voltage | According to EMC and Low voltage | According to EMC and Low voltage |
| | Electrical Safety | According to IEC/EN 60950 (VDE 0805) & EN 50178 (VDE 0160) for assembling device. Input / Output separation: SELV EN60950-1 and PELV EN 60204-1. Double or reinforced insulation. IEC/ EN 60950 for Installation according | | According to IEC/EN 60950 (VDE 0805) & EN 50178 (VDE 0160) for assembling device. Input / Output separation: SELV EN60950-1 and PELV EN 60204-1. Double or reinforced insulation. IEC/EN 60950 for Installation according. |
| | FHC1 " | EN 61000-4-2, EN 61000-4-3, | EN 61000-4-2, EN 61000-4-3, | EN 61000-4-2, EN 61000-4-3, |
| | EMC Immunity EMC Emission | EN 61000-4-4, EN 61000-4-5, EN 61000-6-4, EN 61000-3-2 | EN 61000-4-2, EN 61000-4-5, EN 61000-6-4, EN 61000-3-2 | EN 61000-4-4, EN 61000-4-5, EN 61000-6-4, EN 61000-3-2 |
| | Standards Confirmity | EN 60204-1 Safety of | EN 60204-1 Safety of | EN 60204-1 Safety of |
| | | Electrical Equipment Machines | Electrical Equipment Machines | Electrical Equipment Machines |
| External Data | Operating Temperature | -30 to +70°C | -30 to +70°C | -30 to +70°C |
| | Storage Temperature | -40 85 °C | -40 85 °C | -40 85 °C |
| | Operating Humidity Pollution Degree Environment | 95% at +25°C, | 95% at +25°C, | 95% at +25°C, |
| | Degree of Protection | 2 IP 20 | 2 IP 20 | 2 IP 20 |
| | Class of Protection | IF 20 | II ZU | IF 20 |
| | Cooling | Free Air Convention | Free Air Convention | Free Air Convention |
| | Connection Terminal Blocks | Screw Type 2.5 mm | Screw Type 2.5 mm | Screw Type 2.5 mm |
| | Climatic Class | 3K3 | 3K3 | 3K3 |
| | Dimensions | 18 x 90 x 62 mm | 54 x 90 x 62 mm | 54 x 90 x 62 mm |
| | | | 0.25 kg approx. | |



| Power Supplies | | Section 2 Date | Towns Committee | The state of the s |
|----------------|--|---|---|--|
| - | Model | ZS20-1A | ZS20-1B | ZS20-1C |
| Data | Input Type | 1-Phase | 1-Phase | 1-Phase |
| ă | Rating | 24V / 2.5A | 24V / 5A | 24V / 7.5A |
| | Input Voltage | 115 / 230 V AC | 115 230 V AC | 115 230 V AC |
| | Input Voltage Range AC | 85 264 VAC | 85 264 VAC | 85 264 VAC |
| | Input Voltage Range DC | 120 370 VDC | 125 350 VDC | 125 350 VDC |
| | Turn on delay after | | | |
| Input Data | applying mains Voltage | 1 second | 2 seconds | 1.5 seconds |
| | Frequency | 45 65 Hz | 45 65 Hz | 45 65 Hz |
| | Line Regulation | < ± 1 % | 10 111 00 112 | < 0.1 % (change in input voltage ± 10% |
| | | < ±1 % (change in load, | < 0.1 % (change in input | < 1% (change in load, |
| | Load Regulation | static 10 % 90 % | voltage ± 10 %) | static 10% 90% |
| | Input Current | 0.8 A (230 VAC), 1.4 A (115 VAC) | 1.1 A (230 VAC), 2.8 A (115 VAC) | 1.5 A (230 VAC), 2.8 A (115 VAC) |
| | Inrush Current | ≤ 36 A Typically | ≤ 36 A Typically | ≤ 36 A Typically |
| | Internal Fuse | T4 A | T4 A | T4 A |
| | External Fuse | 10 A (curve B) | 10 A (curve B) | 10 A (curve B) |
| | Output Voltage Range | 24 VDC +/-3% | 24 VDC +/-3% | 24 VDC +/-3% |
| | Adjustment Range (Vadj) | 22 - 27 Vdc | 22 - 27 Vdc | 22 - 27 VDC |
| | Start up with Capacitive Load | _ | ≤ 50.000µF | ≤ 50.000µF |
| | Output Current (@ 40°C) | 2.5A @ 40°C | 5A @ 40°C | 7.5A @ 40°C |
| | Output Current (@ 50°C) | 2.0A @ 50 C, 1.875A @ 60°C | 4A @ 50°C, 3A @ 60°C | 6.5A @ 50 °C, 5A @ 60°C |
| | Power Boost (@ 60°C) for 3 minutes | 2.5 A | 4.5 A | 7.5 A |
| | Power | 60W | 95 120 W | 120 180 W |
| 5 | Hold Up Time | ≥ 20 msec (230 VAC) | ≥ 20 msec (230 VAC) | ≥ 20 msec (230 VAC) |
| Output Data | Parallel Connection | No | No | No |
| <u> </u> | | | | |
| 2 | Derating | from 50 °C 2.5% / °C | from 60 °C 2.5% / ℃ | from 60°C 2.5% /°C |
| 5 | Efficiency | > 87 % (for 230 VAC and nominal values) | , | |
| 0 | Dissipation Power Load Max (W) | 8.9 W | 17 W | 25 W |
| | Output Over Voltage Protection | _ | _ | 35 VDC |
| | Protection | short circuit, overload, over voltage, over temperature | short circuit, overload (EN 60204-1), over voltage, over temperature | short circuit, overload (EN 60204-1), over voltage, over temperature |
| | Protection Modes | Ніссир | Ніссир | Hiccup |
| | Ripple and Noise | ≤ 150 mVpp (with nominal values) | ≤ 120 mVpp (with nominal values) | ≤ 120 mVpp (with nominal values) |
| | Resistance to reverse feed | _ | _ | max 35 VDC |
| | Short Circuit Current (Permanent) | Not Available | Not Available | Not Available |
| ₽ | Relay Power Good | Not Available | Trigger 30VDC | Trigger 30 VDC |
| Ö | RoHS Compliant | Yes 3000 VAC | Yes | Yes |
| = | Isolation Voltage (IN/OUT) | 3000 VAC | 3000 VAC 1605 VAC | 3000 VAC 1605 VAC |
| 2 | Isolation Voltage (IN/PE) Isolation Voltage (OUT/PE) | _ | 500 VAC | 500 VAC |
| General Data | MTBF | > 300 000 hrs according to IEC 61709 | > 500 VAC > 500 000 hrs according to IEC 61709 | > 500 VAC > 500 000 hrs according to IEC 61709 |
| မိ | Safety Approvals | CE | CE | CE |
| _ | Type | DIN Rail | DIN Rail | DIN Rail |
| Mounting | Position (Recommended) | Vertical | Vertical | Vertical |
| Ē | Location | Indoor | Indoor | Indoor |
| ě | Environment (Preferred) | Dust Protected Panels | Dust Protected Panels | Dust Protected Panels |
| | | | According to EMC 89/336/EEC and | According to EMC 89/336/EEC and |
| Compliance | Norms and Certifications | According to EMC and Low voltage | Low voltage 93/68/EEC | Low voltage 93/68/EEC |
| | Electrical Safety | - According to IEC/EN 60950 (VDE 0805) & EN 50178 (VDE 0160) for assembling device. - Input / Output separation: SELV EN60950-1 and PELV EN 60204-1. Double or reinforced insulation IEC/ EN 60950 for Installation according | - According to IEC/EN 60950 (VDE 0805) & EN 50178 (VDE 0160) for assembling device. - Input / Output separation: SELV EN60950-1 and PELV EN 60204-1. Double or reinforced insulation. - IEC/ EN 60950 for Installation according. | - According to IEC/EN 60950 (VDE 0805) & EN 50178 (VDE 0160) for assembling device. - Input / Output separation: SELV EN60950-1 and PELV EN 60204-1. Double or reinforced insulation. - IEC/ EN 60950 for Installation according |
| | EMC Immunity | EN 61000-4-2, EN 61000-4-3, EN 61000-4-4, EN 61000-4-5, | EN 61000-4-2, EN 61000-4-3, EN 61000-4-4, EN 61000-4-5, | EN 61000-4-2, EN 61000-4-3, EN 61000-4-4, EN 61000-4-5, |
| | EMC Emission | EN61000-6-4, EN61000-3-2 | EN61000-6-4, EN61000-3-2 | EN61000-6-4, EN61000-3-2 |
| | | EN 60204-1 Safety of | EN 60204-1 Safety of | EN 60204-1 Safety of |
| | Standards Confirmity | Electrical Equipment Machines | Electrical Equipment Machines | Electrical Equipment Machines |
| _ | Operating Temperature | -30 to +70°C | -25 to +70°C | -25 to +70°C |
| External Data | Storage Temperature | | | |
| | Operating Humidity | -40 85 °C 95% at +25°C, | -40 85 °C 95% at +25°C, | -40 85 °C 95% at +25°C, |
| | Pollution Degree Environment | 95% di +25 C, | 95% di +25 C, | 95% df +25°C, |
| E | Degree of Protection | IP 20 | IP 20 | IP 20 |
| de | Class of Protection | II 20 | I, with PE connected | I, with PE connected |
| ũ | Cooling | Free Air Convention | Through Grid on housing & Metal caing | Through Grid on housing & Metal caing |
| | Connection Terminal Blocks | Screw Type 2.5 mm | Screw Type 2.5 mm | Screw Type 2.5 mm |
| | Climatic Class | 3K3 | 3K3 | 3K3 |
| | Dimensions | 54 x 90 x 62 mm | 55 x 110 x 105 mm | 55 x 110 x 105 mm |
| | Weight | 0.25 kg approx. | 0.5 kg approx. | 0.50 kg approx. |
| | Weight | 0.25 kg approx. | 0.5 kg approx. | 0.50 kg approx. |



LUMEL S.A.

ul. Sulechowska 1 65-022 Zielona Góra, Poland tel.: +48 68 45 75 100 www.lumel.com.pl