

BUL310FP

HIGH VOLTAGE FAST-SWITCHING NPN POWER TRANSISTOR

- STMicroelectronics PREFERRED SALESTYPE
- NPN TRANSISTOR
- HIGH VOLTAGE CAPABILITY
- LOW SPREAD OF DYNAMIC PARAMETERS
- MINIMUM LOT-TO-LOT SPREAD FOR RELIABLE OPERATION
- VERY HIGH SWITCHING SPEED
- FULLY CHARACTERIZED AT 125°C
- LARGE RBSOA
- FULLY MOLDED INSULATED PACKAGE
- 2000 V DC INSULATION (U.L. COMPLIANT)


APPLICATIONS


- HORIZONTAL DEFLECTION FOR COLOUR TV
- ELECTRONIC BALLASTS FOR FLUORESCENT LIGHTING
- FLYBACK AND FORWARD SINGLE TRANSISTOR LOW POWER CONVERTERS

DESCRIPTION

The BUL310FP is manufactured using high voltage Multi Epitaxial Planar technology for high switching speeds and high voltage capability. It uses a Cellular Emitter structure with planar edge termination to enhance switching speeds while maintaining a wide RBSOA.

The BUL series is designed for use in lighting applications and low cost switch-mode power supplies.





ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter	Value	Unit
V _{CES}	Collector-Emitter Voltage (V _{BE} = 0)	1000	V
V_{CEO}	Collector-Emitter Voltage (I _B = 0)	500	V
V _{EBO}	Emitter-Base Voltage (I _C = 0)	9	V
Ic	Collector Current	5	A
I _{CM}	Collector Peak Current (t _p <5 ms)	10	А
Ι _Β	Base Current	3	А
I _{BM}	Base Peak Current (t _p <5 ms)	4	А
P _{tot}	Total Dissipation at Tc = 25 °C	36	W
T _{stg}	Storage Temperature	-65 to 150	°C
Ti	Max. Operating Junction Temperature	150	°C

February 2002 1/6

THERMAL DATA


R _{thj-case}	Thermal Resistance Junction-Case	Max	3.5	°C/W
R _{thj-amb}	Thermal Resistance Junction-Ambient	Max	62.5	°C/W

ELECTRICAL CHARACTERISTICS (T_{case} = 25 °C unless otherwise specified)


Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
I _{CES}	Collector Cut-off Current (V _{BE} = 0)	$V_{CE} = 1000 \text{ V}$ $V_{CE} = 1000 \text{ V}$ $T_j = 125 ^{\circ}\text{C}$			100 500	μA μA
I _{CEO}	Collector Cut-off Current (I _B = 0)	V _{CE} = 500 V			250	μΑ
VCEO(sus)*	Collector-Emitter Sustaining Voltage (I _B = 0)	I _C = 100 mA	500			>
V _{EBO}	Emitter-Base Voltage (I _C = 0)	I _E = 10 mA	9			>
V _{CE(sat)} *	Collector-Emitter Saturation Voltage	$\begin{split} I_C &= 1 \ A & I_B = 0.2 \ A \\ I_C &= 2 \ A & I_B = 0.4 \ A \\ I_C &= 3 \ A & I_B = 0.6 \ A \end{split}$			0.5 0.7 1.1	V V
V _{BE(sat)} *	Base-Emitter Saturation Voltage	$ \begin{aligned} I_C &= 1 \ A & I_B &= 0.2 \ A \\ I_C &= 2 \ A & I_B &= 0.4 \ A \\ I_C &= 3 \ A & I_B &= 0.6 \ A \end{aligned} $			1 1.1 1.2	V V V
h _{FE} *	DC Current Gain	I _C = 10 mA V _{CE} = 5 V I _C = 3 A V _{CE} = 2.5 V	10 6	10	14	
t _s	INDUCTIVE LOAD Storage Time Fall Time	$\begin{array}{lll} I_{C} = 2 \; A & I_{B1} = 0.4 \; A \\ V_{BE(off)} = -5 \; V & R_{BB} = 0 \; \Omega \\ V_{CL} = 250 \; V & L = 200 \; \mu H \\ (see figure 1) & \end{array}$		1.2 80	1.9 160	μs ns
t _s	INDUCTIVE LOAD Storage Time Fall Time	$\begin{array}{lll} I_{C} = 2 \; A & I_{B1} = 0.4 \; A \\ V_{BE(off)} = \text{-5V} & R_{BB} = 0 \; \Omega \\ V_{CL} = 250 \; V & L = 200 \; \mu\text{H} \\ T_{j} = 125 \; ^{o}\text{C} & (\text{see figure 1}) \end{array}$		1.8 150		μs ns

^{*} Pulsed: Pulse duration = 300 μs, duty cycle 1.5 %

Safe Operating Areas




Derating Curve




47/

2/6


DC Current Gain




Collector Emitter Saturation Voltage




Inductive Load Fall Time




DC Current Gain



Base Emitter Saturation Voltage



Inductive Load Storage Time



4

Reverse Biased SOA






Figure 1: Inductive Load Switching Test Circuit



4/6

TO-220FP MECHANICAL DATA

DIM.	mm			inch			
DIIVI.	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.	
А	4.4		4.6	0.173		0.181	
В	2.5		2.7	0.098		0.106	
D	2.5		2.75	0.098		0.108	
E	0.45		0.7	0.017		0.027	
F	0.75		1	0.030		0.039	
F1	1.15		1.7	0.045		0.067	
F2	1.15		1.7	0.045		0.067	
G	4.95		5.2	0.195		0.204	
G1	2.4		2.7	0.094		0.106	
Н	10		10.4	0.393		0.409	
L2		16			0.630		
L3	28.6		30.6	1.126		1.204	
L4	9.8		10.6	0.385		0.417	
L6	15.9		16.4	0.626		0.645	
L7	9		9.3	0.354		0.366	
Ø	3		3.2	0.118		0.126	



Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specification mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

The ST logo is a trademark of STMicroelectronics

© 2002 STMicroelectronics – Printed in Italy – All Rights Reserved STMicroelectronics GROUP OF COMPANIES

Australia - Brazil - Canada - China - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States.

http://www.st.com

47/

This datasheet has been download from:

www.datasheetcatalog.com

Datasheets for electronics components.