

# M18 FCSRH66-0

## M18 FUEL™ REAR HANDLE CIRCULAR SAW FOR WOOD

- Delivers the power to rip cut at the same feed rate of an equivalent AC circular saw, with the ability to cross cut up to 570 pieces of 90 mm x 45 mm pine stud on one 12.0 Ah battery charge
- The HIGH OUTPUT™ system of tools elevates the M18 FUEL™ technologies to a new level and delivers extended performance and extended run time. These tools are designed to maximise the partnership with HIGH OUTPUT™ batteries
- Rear handle design circular saw with blade left allows the user excellent cut line visibility
- 190 mm blade which gives a 66 mm depth of cut, enabling the saw to cut 3 stacked OSB boards
- Durable metal rafter hang hook for work space management and safety
- Vacuum adaptor supplied fits directly to all MILWAUKEE® dust extractors
- Magnesium shoe reduces weight and maximises durability
- Integrated LED light for workspace illumination
- 53° bevel capacity
- -



### REDLITHIUM™

No load speed (rpm)	5800
Max. cutting depth 90° (mm)	66
Max. cutting depth 50 degrees [mm]	45
Max. cutting depth 45° (mm)	48
Blade diameter (mm)	190
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933471444

