





SPECIFICATIONS: LINEAR POWER SUPPLY IHD12-6.8


MADE IN THE U.S.A.

VAC INPUT: • 100/120/220/240 VAC, +10%, -13% • TOLERANCE FOR 230 VAC IS +15%, -10% • FREQUENCY RANGE: 47-63HZ	VAC JUMPERING ANI SILKSCREENED ON CHASSIS For Use at Jumper Apply AC Max Current / Fuse Rating		120VAC 183, 284 481	220VAC 2&3 1&5	ALS 230/240VAC 2&3 4&1 1A
VDC OUTPUT: • 12 VDC @ 6.8 AMP	OVERVOLTAGE PROTECTION: • NOT PROVIDED. AVAILABLE BY ADDING AN IOVP12 MODULE SHORT CIRCUIT PROTECTION: • AUTOMATIC FOLDBACK OVERLOAD PROTECTION: • AUTOMATIC CURRENT LIMIT				
• +/- 0.05% FOR A 10% LINE CHANGE	LOAD REGULATION: +/- 0.05% FOR A 50% LOAD CHANGE (DERATE OUTPUT CURRENT 10% FOR 50 HZ OPERATION)				
OUTPUT RIPPLE: 5.0mV PK-PK MAXIMUM TEMPERATURE RATINGS: OPERATING: 0°C TO 50°C FULL RATED DERATED LINEARLY TO 40% @ 70°C STORAGE: -40°C TO +85°C	TRANSIENT RESPONSE: < 50 µsec per 50% LOAD CHANGE TEMPERATURE COEFFICIENT: • TYPICAL: 0.01%/DEGREE C • MAXIMUM: 0.03%/DEGREE C				
STABILITY: +/- 0.3% FOR 24 HOURS AFTER 1 HOUR WARM-UP VIBRATION: MIL-STD-810G, METHOD 514.6, CATEGORY 1, PROCEDURE1 RANDOM VIBRATION 10Hz - 2KHz, 6.15 grams (3 axis)	SHOCK: • MIL-STD-810G, METHOD 516.6, PROCEDURE III • OPERATING: 20 GPK				
REMOTE SENSING: PROVIDED	OPERATING: 20 GPK EMI/RFI: INHERENT LOW CONDUCTED AND REDIATED NOISE LEVELS. EMI: FCC CFR TITLE 47 PART 15 SUB-PART B RFI: EN55022/CISPR22-LEVEL B COMPATIBILITY				

UL recognized for US and Canada – File#E133338/ CE Mark: LVD 92/59/EEC/ RoHs-5 Lead in Solder Exemption US and Canadian (Bi-National) standards: ANSI/UL 60950-1/-21; CAN/CSA C22.2 #60950-1/-21; IEC 60950-1



CASE SIZE: D



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

International Power: