

# TO-92 Plastic-Encapsulate Transistors

# 79L09

**CJ79L09** Three-terminal positive voltage regulator


**FEATURES**

Maximum Output current

$I_{OM}$ : 0.1 A

Output voltage

$V_o$ : -9 V



ABSOLUTE MAXIMUM RATINGS(Operating temperature range applies unless otherwise specified)

Parameter	Symbol	Value	Units
Input Voltage	$V_i$	-30	V
Operating Junction Temperature Range	$T_{OPR}$	0—+125	°C
Storage Temperature Range	$T_{STG}$	-55—+150	°C

ELECTRICAL CHARACTERISTICS( $V_i=-16V, I_o=40mA, 0^\circ C < T_j < 125^\circ C, C_1=0.33\mu F, C_o=0.1\mu F$ , unless otherwise specified)

Parameter	Symbol	Test conditions	MIN	TYP	MAX	UNIT
Output voltage	$V_o$	$T_j=25^\circ C$	-8.64	-9.0	-9.36	V
		$-12V \leq V_i \leq -24V, I_o=1mA-40mA$	-8.55	-9.0	-9.45	V
		$I_o=1mA-70mA$	-8.55	-9.0	-9.45	V (note)
Load Regulation	$\Delta V_o$	$T_j=25^\circ C, I_o=1mA-100mA$		19	90	mV
		$T_j=25^\circ C, I_o=1mA-40mA$		11	40	mV
Line regulation	$\Delta V_o$	$-12V \leq V_i \leq -24V, T_j=25^\circ C$		45	175	mV
		$-13V \leq V_i \leq -24V, T_j=25^\circ C$		40	125	mV
Quiescent Current	$I_q$			4.1	6.0	mA
Quiescent Current Change	$\Delta I_q$	$-13V \leq V_i \leq -24V$			1.5	mA
	$\Delta I_q$	$1mA \leq V_i \leq 40mA$			0.1	mA
Output Noise Voltage	$V_N$	$10Hz \leq f \leq 100KHz$		58		$\mu V$
Ripple Rejection	RR	$-15V \leq V_i \leq -24V, f=120Hz, T_j=25^\circ C$		45		dB
Dropout Voltage	$V_d$	$T_j=25^\circ C$		1.7		V

TYPICAL APPLICATION

