

Surface Mount Ultrafast Plastic Rectifier




DO-214AB (SMC)

PRIMARY CHARACTERISTICS					
I _{F(AV)}	3.0 A				
V _{RRM}	300 V, 400 V				
I _{FSM}	100 A				
t _{rr}	35 ns				
V _F at I _F	1.1 V				
T _J max.	150 °C				
Package	DO-214AB (SMC)				
Diode variations Single die					

FEATURES

- Glass passivated pellet chip junction
- · Ideal for automated placement
- · Ultrafast reverse recovery time
- Low switching losses, high efficiency
- High forward surge capability



- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

TYPICAL APPLICATIONS

For use in high frequency rectification and freewheeling application in switching mode converters and inverters for consumer, computer, and telecommunication.

MECHANICAL DATA

Case: DO-214AB (SMC)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade Base P/NHE3_X - RoHS-compliant and AEC-Q101 qualified ("_X" denotes revision code e.g. A, B,)

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 2 whisker test, HE3 suffix meets JESD 201 class 2 whisker test

Polarity: Color band denotes cathode end

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	ES3F	ES3G	UNIT	
Device marking code		EF	EG		
Maximum repetitive peak reverse voltage	V_{RRM}	300	400	V	
Working peak reverse voltage	V_{RWM}	225	300	V	
Maximum RMS voltage	V _{RMS}	210	280	V	
Maximum average forward rectified current at T _L = 110 °C	I _{F(AV)}	3.0		Α	
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	100		А	
Operating junction and storage temperature range	T _{J,} T _{STG}	-55 to +150		°C	



ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)						
PARAMETER	TEST CONDITIONS		SYMBOL	ES3F	ES3G	UNIT
Maximum instantaneous forward voltage	3.0 A		V _F ⁽¹⁾	1.1		V
Maximum DC reverse current at working		T _A = 25 °C	· · · · · · · · · · · · · · · · · · ·		0	
peak reverse voltage	ak reverse voltage $T_A = 100 ^{\circ}\text{C}$	'R	35	μΑ		
Maximum reverse recovery time	I _F = 0.5 A, I _R = 1.0 A, I _{rr} = 0.25 A		t _{rr}	35		ns
Maximum reverse recovery time	$I_F = 1.0 \text{ A}, \text{ dI/dt} = 100 \text{ A/}\mu\text{s}, \\ V_R = 30 \text{ V}, I_{rr} = 0.1 I_{RM}$		t _{rr}	50		ns
Maximum reverse recovery current	$I_F = 1.0 \text{ A}, \text{ dI/dt} = 100 \text{ A/}\mu\text{s}, \\ V_R = 30 \text{ V}, I_{rr} = 0.1 I_{RM}$		I _{RM}	3.0		А
Maximum stored charge	$I_F = 1.0 \text{ A}, \text{ dI/dt} = 100 \text{ A/}\mu\text{s}, \ V_R = 30 \text{ V}, I_{rr} = 0.1 I_{RM}$		Q _{rr}	50		nC
Typical junction capacitance	4.0 V, 1 MHz		CJ	30		pF

Note

 $^{^{(1)}}$ Pulse test: 300 μs pulse width, 1 % duty cycle

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	L ES3F ES3G		UNIT	
Typical tharmal registance	R _{0JA} (1)	50		°C/W	
Typical thermal resistance		15		C/VV	

Note

 $^{^{(1)}}$ Units mounted on PCB 5.0 mm x 5.0 mm (0.013 mm thick) land areas

ORDERING INFORMATION (Example)					
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE	
ES3G-E3/57T	0.211	57T	850	7" diameter plastic tape and reel	
ES3G-E3/9AT	0.211	9AT	3500	13" diameter plastic tape and reel	
ES3GHE3_A/H (1)	0.211	Н	850	7" diameter plastic tape and reel	
ES3GHE3_A/I (1)	0.211	I	3500	13" diameter plastic tape and reel	

Note

⁽¹⁾ AEC-Q101 qualified



RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 4 - Typical Reverse Leakage Characteristics




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 5 - Reverse Switching Characteristics




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 6 - Typical Junction Capacitance








Fig. 7 - Forward Power Loss Characteristics

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

DO-214AB (SMC)



Mounting Pad Layout





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

ES3F/51T ES3F/57T ES3F/7T ES3F/9AT ES3F/9CT ES3F-E3/51T ES3F-E3/57T ES3F-E3/9AT ES3F-E3/9CT ES3FHE3/57T ES3FHE3/9AT ES3FHE3/9CT ES3G/51T ES3G/57T ES3G/59T ES3G/9AT ES3G/9BT ES3G/9CT ES3G/9T ES3G-E3/57T ES3G-E3/57T ES3G-E3/9AT ES3G-E3/9CT ES3GHE3/57T ES3GHE3/