32.768kHz SMD LOW PROFILE CRYSTAL



ABS07

Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive -MSL = N/A: Not Applicable

3.2 x 1.5 x 0.9 mm

FEATURES:


- Low frequency in small size SMD
- 0.9mm height ideal for high density circuit boards
- Seam sealed ceramic package offers excellent environmental & heat resistance
- Extended temperature -55°C to +125°C for industrial applications

STANDARD SPECIFICATIONS

- **APPLICATIONS:**
 - Wide range in communication & measuring equipment
 - Commercial & Industrial applications
 - Wireless communications
 - PDA and Smartphone

Parameters	Minimum	Typical	Maximum	Units	Notes
Frequency		32.768			
Operation Mode	Flexura	Flexural Mode (Tuning Fork)			
Operating Temperature	-40		+85	°C	See options
Storage Temperature	-55		+125	°C	
Frequency Tolerance @+25°C	-20		+20	ppm	See options
Temperature Coefficient:	-0.040	-0.036		ppm/T ²	
Turn-over temperature:	+20	+25	+30	°C	
Equivalent series resistance (R1)			70	kΩ	
Shunt capacitance (C0)		0.9 ~ 1.2		pF	
Load capacitance (CL)		12.5		pF	See options
Drive Level		0.1	0.5	μW	
Q value	10000	30000			
Aging@25°C±3°C	-3		3	ppm	First year
Insulation Resistance	500			MΩ	(<i>a</i>) 100 Vdc ± 15 V

OPTIONS AND PART IDENTIFICATION (left blank if standard)



ABRACON IS ISO9001:2008 CERTIFIED Downloaded from Arrow.com.



2 Faraday, Suite# B | Irvine | CA 92618 **Revised: 08.19.15** Ph. 949.546.8000 | Fax. 949.546.8001 Visit www.abracon.com for Terms and Conditions of Sale


32.768kHz SMD LOW PROFILE CRYSTAL



3.2 x 1.5 x 0.9 mm


RoHS/RoHS II

FREQUENCY VS. TEMPERATURE CHARACTERISTICS



OUTLINE DIMENSIONS:

ABS07







2 Faraday, Suite# B | Irvine | CA 92618 **Revised: 08.19.15** Ph. 949.546.8000 | Fax. 949.546.8001 Visit www.abracon.com for Terms and Conditions of Sale

32.768kHz SMD LOW PROFILE CRYSTAL




ABS07


RoHS/RoHS II

3.2 x 1.5 x 0.9 mm

REFLOW PROFILE



TAPE & REEL



ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.





2 Faraday, Suite# B | Irvine | CA 92618 **Revised: 08.19.15** Ph. 949.546.8000 | Fax. 949.546.8001 Visit www.abracon.com for Terms and Conditions of Sale