


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [5039600696](#)  
**Status:** **Active**  
**Overview:** micro-SIM Card Sockets  
**Description:** 1.42mm Height micro-SIM Card Connector, 1.00mm Pitch, Push-Push, Surface Mount, Normal Mount, with Detect Switch, Stainless Steel Shell, 6 Circuits

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-503960-006-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification SPK-503960-001-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**General**

Product Family	Memory Card Sockets
Series	<a href="#">503960</a>
Overview	<a href="#">micro-SIM Card Sockets</a>
Product Name	micro-SIM
Style	Push-Push
UPC	889056143127

**Physical**

Card Detection Switch	Closed
Card Entry Location	Front
Circuits (Loaded)	6
Color - Resin	Black
Durability (mating cycles max)	2000
Ejector Button Side	N/A
Material - Contact	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Material - Shell	Stainless Steel
Net Weight	518.920/mg
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.54mm
Temperature Range - Operating	-25° to +85°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact	0.5A
Shielded	Yes
Voltage - Maximum	10V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	SPK-503960-001-001
Product Specification	PS-503960-006-001
Sales Drawing	SD-503960-009, SD-503960-010

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[503960 Series](#)