TENSATOR®

886 Heavy Duty

The 886 Heavy Duty post is perfect for indoor or outdoor use and features a plastic post. The base has easy to carry handles and is stackable for easy storage.

Features

- Single line post available with screw or bayonet fixings. Dual line available with screw fixing only
- More solid physical barrier, protecting people from dangerous areas **→**
- Recycled rubber stackable base **→**
- **→** Suitable for outdoor use, but should not be permanently placed outside
- Detachable plastic post available in five colours **→**
- Can be shipped flat packed **→**
- Available in twin pack, providing lower freight costs (twin pack order code 886/2) **→**
- Single or dual line versions **→**
- Easy to carry handles on the base **→**
- **→** Rubber ring around the post, providing added protection in storage
- Modular cassette design offering four-point anti-tamper connection as standard **→**
- **→** Constant torque webbing retraction
- 2.3m and 3.65m webbing options **→**
- **→** Accommodates the full range of sign holders



height	960mm	tube O.D.	64mm
base dia.	483mm	weight	8kg

Order Code: 886 Heavy duty

886T2 Heavy duty dual line

886/2 Twin Pack

Applications

Ideal for use indoors and outdoors in warehouses, loading bags, construction sites and manufacturing

Benefits

- Hard wearing base can be walked on or driven over and will still retain its shape
- Post and base detach from one another, making them easy to store
- Base has carry handles moudled into the rubber
- The ultimate in flexibility, the Tensabarrier[®] is easy to set up and simple to store
- Guide & inform your customers & employees
- Easily achieve the optimum queue layout for your floor space
- Reduces customer stress by removing ambiguity as to where the customer should queue and by providing separation between individuals and queue lines
- Durable & hardwearing dye print that does not scratch or deteriorate
- Digitally printed webbing offers branding opportunities



