


See note 1

PC board drilling dimensions(after plating)  
(thickness ≤ 3.20±0.30mm)



Notes:

- 1) The nut can protrude above the surface of insulator but maintaining the footprint dimension 6±0.15 mm.

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:  
SEE DRAWING C01-8646-0001

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S91C4PX00LF	D09S91C6PX00LF	D09S91C8PX00LF	D09S91C8PX00LF
15	39.14	33.32	25.18	24.54	19.18	D15S91C4PX00LF	D15S91C6PX00LF	D15S91C8PX00LF	D15S91C8PX00LF
25	53.03	47.04	39.12	38.25	33.12	D25S91C4PX00LF	D25S91C6PX00LF	D25S91C8PX00LF	D25S91C8PX00LF
37	69.32	63.50	55.68	54.71	49.68	D37S91C4PX00LF	D37S91C6PX00LF	D37S91C8PX00LF	D37S91C8PX00LF
						gold flash	0.76μ gold	1.25μ gold	

mat'l. code		surface	tolerance	projection	product family
ISO 1302	ISO 406	ISO 1101	ISO 1101	D-SUB	
tolerances unless otherwise specified		angles	linear	MM	
0°±2'		0±0.1	.00±0.1		
		.00±0.1	.000±0.1	scale 2:1	
dr		MASSON	2000/07/27	FCJ	
enfr		ALIAS BABU	2015/01/06	FEMALE CONNECTOR DELTA-D	
chr		MITHUN PAUL	2015/01/06	STRAIGHT - PRESS FIT	
appd		BLJU K PAUL	2015/01/06	dwg no sheet 1 of 1 size	
				C01-8646-0129 A3	
sheet index		revision	J	type Product Customer Drawing	
sheet 1		sheet 1			