

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized applications, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an equif prese

FAIRCHILD

SEMICONDUCTOR®


FQP6N80C / FQPF6N80C **N-Channel QFET® MOSFET** 800 V, 5.5 A, 2.5 Ω

Description

This N-Channel enhancement mode power MOSFET is • 5.5 A, 800 V, R_{DS(on)} = 2.5 Ω (Max.) @ V_{GS} = 10 V, produced using Fairchild Semiconductor's proprietary planar stripe and DMOS technology. This advanced MOSFET technology has been especially tailored to reduce on-state • Low Gate Charge (Typ. 21 nC) resistance, and to provide superior switching performance • Low Crss (Typ. 8 pF) and high avalanche energy strength. These devices are suitable for switched mode power supplies, active power • 100% Avalanche Tested factor correction (PFC), and electronic lamp ballasts.

Features

- I_D = 2.75 A



Absolute Maximum Ratings T_c = 25°C unless otherwise noted.

Symbol	Parameter		FQP6N80C	FQPF6N80C / FQPF6N80CT	Unit
V _{DSS}	Drain-Source Voltage	8	V		
I _D	Drain Current - Continuous ($T_C = 25^{\circ}C$)		5.5	5.5 *	А
	- Continuous (T _C = 100°C)		3.2	3.2 *	А
I _{DM}	Drain Current - Pulsed	(Note 1)	22	22 *	А
V _{GSS}	Gate-Source Voltage	±	V		
E _{AS}	Single Pulsed Avalanche Energy	(Note 2)	680		mJ
I _{AR}	Avalanche Current	(Note 1)	5	А	
E _{AR}	Repetitive Avalanche Energy	(Note 1)	1	mJ	
dv/dt	Peak Diode Recovery dv/dt (Note 3)		4	V/ns	
P _D	Power Dissipation ($T_C = 25^{\circ}C$)	158	51	W	
	- Derate above 25°C	1.27	0.41	W/°C	
T _J , T _{STG}	Operating and Storage Temperature Range	-55 to	°C		
ΤL	Maximum Lead Temperature for Soldering, 1/8" from Case for 5 Seconds.	3	°C		

Thermal Characteristics


Symbol	Parameter	FQP6N80C	FQPF6N80C / FQPF6N80CT	Unit °C/W	
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case, Max.	0.79	2.45		
$R_{\theta CS}$	Thermal Resistance, Case-to-Sink Typ, Max.	0.5		°C/W	
$R_{ ext{ heta}JA}$	Thermal Resistance, Junction-to-Ambient, Max.	62.5	62.5	°C/W	


December 2013


Part Number FQP6N80C FQPF6N80C		Top Mark	Pac	kage Packing Method Ree		Reel	Size	Tape Width		Quantity	
		FQP6N80C	TO-	-220	Tube	N//	۹.	N/A		50 units	
		FQPF6N80C	TO-2	220F Tube N/A		4	N/A		50 units		
FQPF	6N80CT	FQPF6N80CT	TO-220F		Tube	N/A		N/A		50 units	
lectri	cal Cha	racteristics	T _C = 25°0	C unless oth	erwise noted.		ŀ				
Symbol		Parameter			Test Conditions		Min.	Тур.	Max.	Unit	
Off Cha	aracterist	ice									
BV _{DSS}	1	urce Breakdown Voltage		V _{GS} = 0 V, I _D = 250 μA			800			V	
ΔBV _{DSS} / ΔT _J		Breakdown Voltage Temperature Coefficient		$I_D = 250 \ \mu$ A, Referenced to 25°C				0.97		V/°C	
I _{DSS}			V _{DS} = 800 V, V _{GS} = 0 V					10	μA		
	Zero Gate	e Voltage Drain Curre	ent	$V_{DS} = 640 \text{ V}, \text{ T}_{C} = 125^{\circ}\text{C}$					100	μA	
I _{GSSF}	Gate-Bod	y Leakage Current, F	orward	V _{GS} =	V _{GS} = 30 V, V _{DS} = 0 V		-		100	nA	
I _{GSSR}	Gate-Bod	y Leakage Current, F	Reverse	V _{GS} =	-30 V, V _{DS} = 0 V	1	-		-100	nA	
On Cha	aracterist	ics									
V _{GS(th)}	1	eshold Voltage	-	V _{DS} =	V _{GS} , I _D = 250 μA		3.0		5.0	V	
R _{DS(on)}	Static Dra On-Resist			V _{GS} =	10 V, I _D = 2.75 A		ł	2.1	2.5	Ω	
9 _{FS}	Forward T	ransconductance		V _{DS} =	50 V, I _D = 2.75 A		-	5.4		S	
D											
Dynam C _{iss}	Input Cap	cteristics acitance	-					1010	1310	pF	
C _{oss}		apacitance	_	$V_{DS} = 25 V, V_{GS} = 0 V,$				90	115	pF	
C _{rss}		Fransfer Capacitance		1 = 1.0	f = 1.0 MHz			8	11	pF	
	4	acteristics								p.	
t _{d(on)}		Delay Time	-					26	60	ns	
t _r	Turn-On F	,		$-V_{DD} = 400 \text{ V}, \text{ I}_{D} = 5.5 \text{ A},$				65	140	ns	
d(off)		Delay Time		R _G = 2	5 12			47	105	ns	
t _f	Turn-Off F			+		(Note 4)		44	90	ns	
Qg	Total Gate				640 V, I _D = 5.5 A,			21	30	nC	
Q _{gs}		rce Charge		V _{DS} =			-	6		nC	
Q _{gd}	Gate-Drai			- 68		(Note 4)		9		nC	
3-				1				I			
Drain-S		ode Characteri			-						
I _S	Maximum	n Continuous Drain-Source Diode Forward Current						5.5	А		
1	Maximum	Pulsed Drain-Sourc	e Diode F						22	A	
				1/ -	0 V, I _S = 5.5 A				1.4	V	
I _{SM} V _{SD}	Drain-Sou	Irce Diode Forward \	/oltage						1.4	v	
		Irce Diode Forward \ Recovery Time	/oltage	V _{GS} =	0 V, I _S = 5.5 A, = 100 A/μs			615		ns	


Notes: 1. Repetitive rating : pulse-width limited by maximum junction temperature. 2. L = 42 mH, I_{AS} = 5.5 A, V_{DD} = 50 V, R_G = 25 Ω , starting T_J = 25°C. 3. I_{SD} \leq 5.5 A, di/dt \leq 200 A/µs, V_{DD} \leq BV_{DSS} starting T_J = 25°C. 4. Essentially independent of operating temperature.


FQP6N80C / FQPF6N80C — N-Channel QFET[®] MOSFET
















Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:

http://www.fairchildsemi.com/package/packageDetails.html?id=PN_TT220-003





Rev. 166

Obsolete

Not In Production

Datasheet contains specifications on a product that is discontinued by Fairchild

Semiconductor. The datasheet is for reference information only.

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly ori indirectly, any claim of personal injury or death

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ON Semiconductor: FQPF6N80C FQPF6N80CT