

DWST83345-1

TSTAK IP54 Shallow Box

Selling Propositions

- IP54 WATERSEAL - Providing Water And Dust Protection To Tools And Fixings Inside The Box
- METAL-PIN SIDE LATCHES - allowing TSTAK modules to be connected together. The metal pin design provides longer life
- HEAVY DUTY METAL FRONT LATCHES - increasing strength, durability and longevity
- FRONT & TOP CARRY HANDLES - so the box can be carried in both orientations
- LOCKABLE - Via Padlock (Not Included) For Added Security
- INTERNAL FOAM INSERT - Customisable Foam Insert To Keep Powertools Safe During Transportation
- DEWALT TRACKER READY - Fixing point built into the TSTAK box to allow a DEWALT Tracker to be installed and the box tracked via DEWALT Tool Connect
- 30KG LOAD CAPACITY

Standard Equipment

- Customisable Foam Insert for power tools and batteries

Warranty specifications

- Standard Warranty

Specifications	
Width	440.0 mm
Depth	333.0 mm
Height	162.0 mm
Length	440.0 mm