

Part Electrical Specifications

| Product | Compliance | Status | Channels | Gain (V/V) | Gain Error Max (%) | V _s Min (V) | V _s Max (V) | V _{CM} (V) | I _q Typ (mA) | Bandwidth Typ (-3dB) | V _{os} Max (mV) | V _{os} Drift Max (μV/°C) | Operating Temperature Range (°C) | CMRR Typ (dB) | Package Type |
|----------------|------------------------|--------|----------|------------|--------------------|------------------------|------------------------|---------------------|-------------------------|----------------------|--------------------------|-----------------------------------|----------------------------------|---------------|-------------------------------|
| NCS199A1RSQT2G | Pb-free Halide free | Active | 1 | 50 | ±1.5 | 2.2 | 26 | -0.3 to 26 | 0.04 | 0.09 | 0.15 | 0.5 | -40 to 125 | 120 | SC-88-6 / SC-70-6 / SOT-363-6 |

For more information please contact your local sales support at www.onsemi.com.

Created on: 9/19/2018