


REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LL 09/25/06'	~	LJC 09/25/06'
B	整理图面	YCH 05/21/08'	~	

NOTES:


- ELECTRICAL CHARACTERISTICS:
 - CONTACT RESISTANCE: 20mΩ Max. INITIAL.
 - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
 - INSULATION RESISTANCE: 1000MΩ Min.
- ENVIRONMENT CHARACTERISTICS:
 - OPERATING TEMPERATURE: 0°C~+85°C.
 - STORAGE TEMPERATURE: -20°C~+70°C.

3. PRODUCT NUMBER CODE:

DS1077-	X	X	X	X	X	X	X	
								SCREW DIM. A
								S: Standard(W/O nut)
								1: 5.00
								2: 3.00
								3: 5.20
								4: 4.80
								5: 5.80
								6: 4.00
								SCREW TYPE
								S: Standard(W/O nut)
								1: CC TYPE
								2: CS TYPE
								3: BR TYPE
								4: BRJ TYPE DIM. DIM C: 3~4
								5: BRJ TYPE DIM. DIM C: 5~6
								SHELL PLATING
								T:FORNT & BACK SHELL TIN
								N:FORNT SHELL NICKEL,BACK SHELL TIN
								CONTACT PLATING
								8: FULL GOLD FLASH
								0: SELECTIVE GOLD FLASH
								HOUSING COLOR
								B:BLACK
								W:WHITE
								U:BLUE
								CONNECTOR TYPE
								M:MALE
								F:FEMALE
								No.OF CONTACTS
								15 26 44 62 78



78pin Figure




Standard TYPE

CC TYPE


CS TYPE

BR TYPE

BRJ TYPE



78pin Figure



Dimension

Position	A	B	C	E	F
15	17.90	24.99	30.80	16.33	2.29
26	26.50	33.32	39.14	24.66	2.29
44	40.00	47.04	53.04	38.38	2.29
62	56.50	63.50	69.32	54.84	2.41
78	54.30	61.00	67.04	52.34	2.41

GENERAL TOLERANCE	ANGLE TOLERANCE	PROJECTION	TITLE	D-SUB H.DIP STRAIGHT TYPE
X. ±0.60	X. ±5°	UNITS	mm	
.X ±0.38	.X ±3°	SHEET SIZE	A4	SERIES DS1077 SERIES
.XX ±0.25	.XX ±2°			
DRAWING TYPE	CUSTOMER	晨翔电子有限公司 CONNFLY ELECTRONIC CO. LTD		
SCALE	1:1 SHEET 1 OF 1			
DRAWING NO.	C-DS1077-XXXXXXX			

Tel: 86-574-63508787

Fax: 86-574-63510817

E-mail: cx@connfly.com
<http://www.connfly.com.cn>
 Add: West Lake Road, Cixi Ningbo, China
 P.C.: 31521