

0394	0393	0391	9016
0394-0-15-XX-07-XX-10-0 Solder mount in .120 min. mounting hole	0393-0-15-XX-07-XX-10-0 Solder mount in .144 min. mounting hole	0391-0-15-XX-07-XX-10-0 Solder mount in .159 min. mounting hole	9016-0-15-XX-07-XX-10-0 Press-fit in .131 mounting hole

0493	0490	0616	0387
0493-0-15-XX-07-XX-10-0 Press-fit in .144 mounting hole	0490-0-15-XX-07-XX-04-0 Press-fit in .144 mounting hole	0616-0-18-XX-07-XX-10-0 Press-fit in .144 mounting hole	0387-0-15-XX-07-XX-04-0 Solder mount in .063 min. mounting hole

0370	4040	0491	9214
0370-0-19-XX-07-XX-10-0 #18 Gage crimp barrel	4040-0-19-XX-07-XX-10-0 Wire Termination	0491-0-19-XX-07-XX-04-0 For use in stackable patch cords	9214-0-15-XX-07-XX-10-0 Solder mount in .083 min. mounting hole

<p>SPECIFICATIONS</p> <p>SHELL MATERIAL: Brass Alloy 360, 1/2 Hard</p> <p>CONTACT MATERIAL: Beryllium Copper Alloy 172, HT</p> <p>DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°</p>	<p>ORDER CODE: XXXX - X - 1X - XX - 07 - XX - XX - 0</p> <p>BASIC PART # →</p> <p>SPECIFY SHELL FINISH:</p> <p>01 200μ" TIN/LEAD OVER NICKEL</p> <p>80 200μ" TIN OVER NICKEL ◊</p> <p>15 10μ" GOLD OVER NICKEL ◊</p> <p style="text-align: center;">CONTACT</p> <p>#07 CONTACT (DATA ON PAGE 214)</p>	<p>SPECIFY CONTACT FINISH:</p> <p>01 200μ" TIN/LEAD OVER NICKEL</p> <p>80 200μ" TIN OVER NICKEL ◊</p> <p>27 30μ" GOLD OVER NICKEL ◊</p>
--	---	---

