

Max. 4.6 m<sup>3</sup>/h



## DC axial fans

□ 25 x 8 mm

- **Material:** Housing: GRP<sup>1)</sup> (PBT)  
Impeller: GRP<sup>1)</sup> (PA)
- **Direction of air flow:** Exhaust over struts
- **Direction of rotation:** Counterclockwise, looking towards rotor
- **Connection:** Via single wires AWG 28, TR 64
- **Weight:** 5 g

- **Possible special versions:**  
(See chapter DC fans - specials)
  - Speed signal
  - Moisture protection

1) Fiberglass-reinforced plastic


Series 250  
VWC0025AUBAS

### Nominal data

Type	Air flow		Nominal voltage		Sound pressure level	Sound power level	Sintec sleeve bearings Ball bearings	Power consumption	Nominal speed	Temperature range	Hours	Hours	Curve
	m <sup>3</sup> /h	cfm	VDC	VDC									
255 M	2.3	1.2	<b>5</b>	4.5...5.5	5	< 3	■	0.2	6 500	-10...+70	45 000 / 17 500	47 500	①
255 N	3.5	1.9	<b>5</b>	4.5...5.5	16	< 3	■	0.4	9 600	-10...+70	40 000 / 15 000	42 500	②
255 H	4.6	2.6	<b>5</b>	4.5...5.5	23	4.4	■	0.6	12 000	-10...+55	35 000 / 15 000*	37 500	③
252 N	3.4	1.9	<b>12</b>	10...14	15	< 3	■	0.5	9 000	-10...+70	40 000 / 15 000	42 500	②
252 H	4.6	2.6	<b>12</b>	10...14	23	4.4	■	0.7	12 000	-10...+55	35 000 / 15 000*	37 500	③

Subject to change

\* at 55 °C



Air performance measured as per: ISO 5801.  
Installation category A, without accidental contact.  
Noise: Total sound power level L<sub>WA</sub> ISO 10302  
measured on a hemisphere with a radius of 2 m.  
Sound pressure level L<sub>pA</sub> measured at 1 m distance  
from fan axis.  
The values given are applicable only under the specified  
measuring conditions and may differ depending on the  
installation conditions.  
In the event of deviation from the standard configuration,  
the parameters must be checked after installation!  
For detailed information see  
<http://www.ebmpapst.com/general conditions>

