



PARA LIGHT ELECTRONICS CO., LTD.

11F., No. 8, Jiankang Rd., Zhonghe Dist., New Taipei City 235, Taiwan

Tel: 886-2-2225-3733 Fax: 886-2-2225-4800 http://www.paralighttaiwan.com

DATA SHEET

PART NO.: L5T47UW5C-AHV

REV: <u>A/0</u>


PARA LIGHT ENGINEERING:		
CUSTOMER'S APPROVAL:	DCC:	



L5T47UW5C-AHV

REV:A/0

PACKAGE DIMENSIONS



ITEM	MATERIALS
RESIN	Epoxy Resin
LEAD FRAME	Sn Plating iron Alloy

Note:

- 1.All Dimensions are in millimeters.
- 2.Tolerance is ±0.25mm(0.010 ")
 Unless otherwise specified.
- 3.Protruded resin under flange is 1.5mm(0.059 ") max.



L5T47UW5C-AHV

REV:A / 0

FEATURES

- * High-brightness
- * High reliability
- * Low-voltage characteristics
- * Narrow view angle
- * Pb FREE Products
- * RoHS Compliant

CHIP MATERIALS

* Dice Material : GalnN/GaN* Light Color : ULTRA WHITE* Lens Color : WATER CLEAR

ABSOLUTE MAXIMUM RATING:(Ta=25°C)

SYMBOL	DESCRIPTION	ULTRA WHITE	UNIT	
Po	Power Dissipation Per Chip	120	mW	
VR	Reverse Voltage Per Chip	5	V	
lF	Average Forward Current Per Chip	30	mA	
IFP	Pulse Forward Current	100	mA	
-	Derating Linear From 25°C Per Chip	0.4 mA/°C		
Topr	Operating Temperature Range	-25°C to 85°C		
Tstg	Storage Temperature Range	-25°C to 85°C		
Esd	the led can withstand the max static level when assembling or operation (HBM)	<2000V		

IFP Conditions : Pulse Width≤10msec. And Duty≤1/10

ELECTRO-OPTICAL CHARACTERISTICS:(Ta=25°C)


SYMBOL	DESCRIPTION	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
VF	Forward Voltage	IF = 20mA		3.0	3.6	V
lR	Reverse Current	VR = 5V			100	μA
201/2	Half Intensity Angle	IF = 20mA		18		deg
lv	Luminous Intensity	IF = 20mA		8200		mcd
Х	Chromaticity Coordinates	IF = 20mA		0.25		
Y	Chilomaticity Cooldinates	IF = 20mA		0.24		



L5T47UW5C-AHV


REV:A/0

■ TJ=25°C
Forward Current Vs
Forward Voltage




■ TJ= 25 °C


(Mcd) Luminous Intensity VS. Forward Current



Duty Ratio vs.Allowable Forward Current



Ambient Temperature vs.
 Forward Voltage







L5T47UW5C-AHV

REV:A/0


■ Ambient Temperature vs. Relative Luminosity




Ambient Temperature vs.
 Allowable Forward Current



Forward Current vs.
 Chromaticity Coordinate




■ Spectrum





5.0 mm DIA LED LAMP L5T47UW5C-AHV REV:A / 0

VIEWING ANGLE





L5T47UW5C-AHV

REV:A/0

Label Explanation

PARA	NO.	•		
LOT	NO.	•		INSPECTED
BIN		:		
Q'	TY	:	PCS	
N. W		:	g	

PARA NO.: L5T47UW5C-AHV Refer to page 15

A---E: For series number B---L: Local F: Foreign

C---L: LAMP D---Year E---Month

F--- Serial number




L5T47UW5C-AHV

REV:A/0


SOLDERING

METHOD	SOLDERING CONDITIONS	REMARK
DIP SOLDERING	Bath temperature: 260℃ Immersion time: within 3 sec ,1 times	 Solder no closer than 3mm from the base of the package Using soldering flux," RESIN FLUX" is recommended.
SOLDERING IRON	Soldering iron: 30W or smaller Temperature at tip of iron: 300℃ or lower Soldering time: within 3 sec.	 During soldering, take care not to press the tip of iron against the lead. (To prevent heat from being transferred directly to the lead, hold the lead with a pair of tweezers while soldering)

1) When soldering the lead of LED in a condition that the package is fixed with a panel (See Fig.1), be careful not to stress the leads with iron tip.



2) When soldering wire to the lead, work with a jig (See Fig.2) to avoid stressing the package.



Regarding tinning the leads, compound made of tin ,copper and sliver is proposed with the temperature of 260° C. The proportion of the alloyed solution is 95.5% tin, 3.5 % copper, 0.5% silver. The time of tinning is 3 seconds.




L5T47UW5C-AHV

REV:A/0

3) Similarly, when a jig is used to solder the LED to PC board, take care as much as possible to avoid stressing the leads (See Fig.3).

0



- 4) Repositioning after soldering should be avoided as much as possible. If inevitable: select a best-suited method that assures the least stress to the LED.
- Lead cutting after soldering should be performed only after the LED temperature has returned to normal temperature.

STORAGE

- 1) The LEDs should be stored at 30° C or less and 70% RH or less after being shipped from PARA and the storage life limit is 1 year .
- 2) PARA LED lead frames are comprised of a tin plated iron alloy. The surface may be affected by environments which contain corrosive gases and so on. Please avoid conditions which may cause the LEDs to corrode, tarnish or discolor. This corrosion or discoloration may cause difficulty during soldering operations. It is recommended that the LEDs be used as soon as possible.
- 3) Please avoid rapid changes in ambient temperature, especially, in high humidity environments where condensation can occur.



L5T47UW5C-AHV

REV:A / 0


STATIC ELECTRICITY

- Static electricity or surge voltage damages the LEDs.
 It is recommended that a wrist band and an anti-electrostatic glove be used when handling the LEDs.
- 2) All devices, equipment and machinery must be properly grounded. It is recommended that measures be taken against surge voltage to the LED mounting equipment.
- 3) When inspecting the final products in which LEDs were assembled, it is recommended to check whether the assembled LEDs are damaged by static electricity. To find static-damaged LEDs, perform a light-on test or a VF test at a lower current (below 1mA is recommended).
- 4) Damaged LEDs will show some unusual characteristics such as the leakage current remarkably increases, the forward voltage becomes lower, or the LEDs do not light at the low current.

Criteria: (VF>2.0V at IF=0.5mA)

LED MOUNTING METHOD

4) When mounting the LED to a housing, as shown on Fig.4, ensure that the mounting holes on the PC board match the pitch of the leads correctly. Tolerance of dimensions of the respective components including the LEDs should be taken into account especially when designing the housing, PC board, etc. to prevent pitch misalignment between the leads and holes on PCB, the diameter of the holes should be slightly larger than the size of the lead. Alternatively, the shape of the holes could be made oval. (See Fig.4)






L5T47UW5C-AHV


REV:A/0

5) Use LEDs with stand-off (Fig.5) or the tube or spacer made of plastic (Fig.6) to position the LEDs.




FORMING LEAD

1) The lead should be bent at least 2mm away from the package. Bending should be performed with base fixed to a jig to pliers (Fig.7)



- 2) Forming lead should be carried our prior to soldering and never during or after soldering.
- 3) Form the lead to ensure alignment between the leads and the holes on PCB, so that stress against the LED is prevented. (Fig.8)






L5T47UW5C-AHV

REV:A/0

LEAD STRENGTH

1) Bend strength

Do not bend the lead more than twice. (Fig.9)



Tensile strength (@Room Temperature)
 If the force is 1kg or less, there will be no problem. (Fig.10)



HEAT MANAGEMANT

- Thermal design of the end product is of paramount importance. Please consider the heat generation of the LED when designing the system. The temperature increase is affected by the thermal resistance of the circuit board and density of LED placement on the board, as well as other components. It is necessary to avoid intense heat generation and operate within the maximum ratings given in this specification.
- The operating current (IF) should be decided after considering the ambient maximum temperature of LEDs.



L5T47UW5C-AHV

REV:A/0

•CHEMICAL RESISTANCE

- 1) Avoid exposure to chemicals as it may attack the LED surface and cause discoloration.
- 2) When washing is required, refer to the following table for the proper chemical to be used. (Immersion time: within 3 minutes at room temperature.)

SOLVENT	ADAPTABILITY
Freon TE	\odot
Chlorothene	X
Isopropyl Alcohol	\odot
Thinner	X
Acetone	X
Trichloroethylene	X

⊙--Usable X--Do not use.

NOTE: Influences of ultrasonic cleaning of the LED resin body differ depending on factors such as the oscillator output, size of the PC board and the way in which the LED is mounted. Therefore, ultrasonic cleaning should only be performed by confirming an ultrasonic cleaning trial run.

OTHER CONSIDERTIONS

- 1) Care must be taken to ensure that the reverse voltage will not exceed the absolute maximum rating when using the LEDs with matrix drive.
- 2) The LEDs described in this data sheet are intended to be used for ordinary electronic equipment (such as office equipment, communications equipment, measurement instruments and household appliances). Consult PARA's sales staff in advance for information on the applications in which exceptional quality and reliability are required, particularly when the failure or malfunction of the LEDs may directly jeopardize life or health (such as for airplanes, spacecraft, automobiles, traffic control equipment etc).
- 3) The formal specifications must be exchanged and signed by both parties before large volume purchase begins.



L5T47UW5C-AHV

REV:A/0

Bin Code List:

Luminous Intensity(IV),Unit:mcd@20mA					
Bin Code	Min	Max			
L	4130	5780			
M	5780	8090			
N	8090	11330			
0	11330	15860			
Р	15860	22200			

Tolerance of each bin are±15%

Forward Voltage (VF), Unit:v@20mA					
Bin Code	Min	Max			
V0	2.8	3.0			
V1	3.0	3.2			
V2	3.2	3.4			
V3	3.4	3.6			

Tolerance of each bin are±0.1Volt

	WA2					W	A 3		
Х	0.23	0.23	0.24	0.24	Χ	0.24	0.24	0.25	0.25
Υ	0.16	0.22	0.235	0.175	Υ	0.175	0.235	0.25	0.19
	WA4					W	A 5		
Х	0.25	0.25	0.26	0.26	Χ	0.26	0.26	0.264	0.28



L5T47UW5C-AHV

REV:A/0

LED Lamps: Part Number Rules

