




Product information GSSA 300 schwarz/black

Industrial Connectors:Rectangular connectors GDM-series:Type C Industrial Standard:Appliance connector:GSSA 300 schwarz/black


<http://www.e-catalog.beldensolutions.com/link/57078-24228-24309-24343-24345-35494/en/conf/ui/state>

Name	GSSA 300 schwarz/black
	
	appliance connector with central nut and 2 screws M 3 x 8
Delivery informations	
Availability	available
Product description	
Description	appliance connector with central nut and 2 screws M 3 x 8
Type	GSSA 300 schwarz/black
Order No.	933 116-100
Number of contacts	3 + PE
Standard	industrial standard (9.4 mm)
Housing Color	black
Construction type	C
Technical data	
Rated voltage	AC/DC 250 V
Rated current	4 A
Contact resistance	<= 4 mOhm
Type of termination	solder
Mounting	screw
Material	
Contact surface material	Sn
Contact bearer material	PA
Housing material	PA
Environmental conditions	
Protection class (IEC 60529)	IP 65
Pollution severity	3
Temperature range	-40 °C to +125 °C
Inflammability class	
Housing	94 HB
Contact bearer	94 V-2
Approvals	
UR	UR
VDE	VDE
SEV	SEV
CSA	CSA
Packing unit	
Packaging unit	200 pieces
Scope of delivery and accessories	
Accessories to order separately	(NBR) flat gasket GSSA 300-5, Order No. 730 233-002; (EPDM) flat gasket GSSA 300-6, Order No. 730 312-003

Industrial Connectors:Rectangular connectors GDM-series:Type C Industrial Standard:Appliance connector:GSSA 300 schwarz/black
<http://www.e-catalog.beldensolutions.com/link/57078-24228-24309-24343-24345-35494/en/conf/uistate>

Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.