











SNVS071C -MARCH 2000-REVISED SEPTEMBER 2015

LM2766

LM2766 Switched Capacitor Voltage Converter

Features

- **Doubles Input Supply Voltage**
- SOT-23 6-Pin Package
- 20-Ω Typical Output Impedance
- 90% Typical Conversion Efficiency at 20 mA
- 0.1-µA Typical Shutdown Current

Applications

- Cellular Phones
- **Pagers**
- **PDAs**
- **Operational Amplifier Power Supplies**
- Interface Power Supplies
- Handheld Instruments

3 Description

The LM2766 CMOS charge-pump voltage converter operates as a voltage doubler for an input voltage in the range of 1.8 V to 5.5 V. Two low-cost capacitors and a diode are used in this circuit to provide up to 20 mA of output current.

LM2766 operates at 200-kHz switching frequency to reduce output resistance and voltage ripple. With an operating current of only 350 µA (operating efficiency greater than 90% with most loads) and 0.1-µA typical shutdown current, the LM2766 provides ideal performance for batterypowered systems. The device is manufactured in a SOT-23 6-pin package.

Device Information⁽¹⁾

| PART NUMBER | PACKAGE | BODY SIZE (NOM) | |
|-------------|------------|-------------------|--|
| LM2766 | SOT-23 (6) | 2.90 mm × 1.60 mm | |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

Typical Voltage Doubler Application






Table of Contents

| 1 | Features 1 | | 8.3 Feature Description | 8 |
|---|--|-----|--------------------------------------|-----|
| 2 | Applications 1 | | 8.4 Device Functional Modes | 8 |
| 3 | Description 1 | 9 / | Application and Implementation | 9 |
| 4 | | | 9.1 Application Information | 9 |
| 5 | Pin Configuration and Functions3 | | 9.2 Typical Application | 9 |
| 6 | Specifications4 | 10 | Power Supply Recommendations | 12 |
| • | 6.1 Absolute Maximum Ratings | 11 | Layout | 13 |
| | 6.2 ESD Ratings 4 | | 11.1 Layout Guidelines | 13 |
| | 6.3 Recommended Operating Conditions 4 | | 11.2 Layout Example | 13 |
| | 6.4 Thermal Information4 | 12 | Device and Documentation Support | 14 |
| | 6.5 Electrical Characteristics5 | | 12.1 Device Support | 14 |
| | 6.6 Typical Characteristics 6 | | 12.2 Community Resources | 14 |
| 7 | Parameter Measurement Information | | 12.3 Trademarks | 14 |
| | 7.1 Test Circuit | | 12.4 Electrostatic Discharge Caution | 14 |
| 8 | Detailed Description 8 | | 12.5 Glossary | 14 |
| - | 8.1 Overview | | Mechanical, Packaging, and Orderable | 4.4 |
| | 8.2 Functional Block Diagram 8 | ı | nformation | 14 |
| | | | | |


4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Submit Documentation Feedback



5 Pin Configuration and Functions



Pin Functions

| PIN | | TVDE | DESCRIPTION | | | | | |
|-----|------------------|--------|---|--|--|--|--|--|
| NO. | NAME | TYPE | DESCRIPTION | | | | | |
| 1 | V+ | Power | Power supply positive voltage input. | | | | | |
| 2 | GND | Ground | Power supply ground input. | | | | | |
| 3 | CAP- | Power | Connect this pin to the negative terminal of the charge-pump capacitor. | | | | | |
| 4 | SD | Input | Shutdown control pin, tie this pin to V+ in normal operation. | | | | | |
| 5 | V _{OUT} | Power | Positive voltage output. | | | | | |
| 6 | CAP+ | Power | Connect this pin to the positive terminal of the charge-pump capacitor. | | | | | |



6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) (1)(2)

| | MIN | MAX | UNIT |
|---|-------------|------------|------|
| Supply voltage (V+ to GND, or V+ to V _{OUT}) | | 5.8 | V |
| SD | (GND - 0.3) | (V+ + 0.3) | V |
| V _{OUT} continuous output current | | 40 | mA |
| Output short-circuit duration to GND ⁽³⁾ | | 1 | sec |
| Continuous power dissipation (T _A = 25°C) ⁽⁴⁾ | | 600 | mW |
| T _{JMax} ⁽⁴⁾ | | 150 | °C |
| Storage temperature, T _{stg} | -65 | 150 | °C |

⁽¹⁾ Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- 2) If Military/Aerospace specified devices are required, contact the TI Sales Office/ Distributors for availability and specifications.
- 3) V_{OUT} may be shorted to GND for one second without damage. For temperatures above 85°C, V_{OUT} must not be shorted to GND or device may be damaged.
- (4) The maximum allowable power dissipation is calculated by using $P_{DMax} = (T_{JMax} T_A)/R_{\theta JA}$, where T_{JMax} is the maximum junction temperature, T_A is the ambient temperature, and $R_{\theta JA}$ is the junction-to-ambient thermal resistance of the specified package.

6.2 ESD Ratings

| | | | VALUE | UNIT |
|--------------------|---------------|---|-------|------|
| \/ | Electrostatic | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾ | ±2000 | \/ |
| V _(ESD) | discharge | Machine model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾ | ±200 | V |

⁽¹⁾ JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

| | MIN | NOM MAX | UNIT |
|---------------------------------------|-----|---------|------|
| Junction temperature | -40 | 100 | °C |
| Ambient temperature | -40 | 85 | °C |
| Lead temperature (soldering, 10 sec.) | | 240 | °C |

6.4 Thermal Information

| | LM2766 | |
|---|--------------|------|
| THERMAL METRIC ⁽¹⁾ | DBV (SOT-23) | UNIT |
| | 6 PINS | |
| R _{0JA} Junction-to-ambient thermal resistance | 210 | °C/W |

For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report, SPRA953.

⁽²⁾ JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.



6.5 Electrical Characteristics

Unless otherwise specified, typical limits are for $T_J = 25$ °C, minimum and maximum limits apply over the full operating temperature range: V+ = 5 V, $C_1 = C_2 = 10 \ \mu F$. (1)

| | PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|-------------------|----------------------------------|---------------------------------|-----|--------|-----|------|
| V+ | Supply voltage | | 1.8 | | 5.5 | V |
| IQ | Supply current | No load | | 350 | 950 | μΑ |
| | Chartelesses assembly assembly | T _J = 25°C | | 0.1 | 0.5 | μΑ |
| I _{SD} | Shutdown supply current | T _A = 85°C | | 0.2 | | |
| \/ | Chartelesses wie in mat volte en | | 0.6 | | | V |
| V_{SD} | Shutdown pin input voltage | | | | 2 | |
| | Output current | 2.5 V ≤ V _{IN} ≤ 5.5 V | 20 | | | 0 |
| IL | | 1.8 V ≤ V _{IN} ≤ 2.5 V | 10 | | | mA |
| R _{OUT} | Output resistance ⁽²⁾ | I _L = 15 mA | | 20 | 55 | Ω |
| fosc | Oscillator frequency | See ⁽³⁾ | 220 | 400 | 700 | kHz |
| $f_{\sf SW}$ | Switching frequency | See ⁽³⁾ | 110 | 200 | 350 | kHz |
| P _{EFF} | Power efficiency | I _L = 20 mA to GND | | 94% | | |
| V _{OEFF} | Voltage conversion efficiency | No load | | 99.96% | | |

⁽¹⁾ In the test circuit, capacitors C_1 and C_2 are 10- μ F, 0.3- Ω maximum ESR capacitors. Capacitors with higher ESR may increase output resistance, and reduce output voltage and efficiency.

Copyright © 2000-2015, Texas Instruments Incorporated

Specified output resistance includes internal switch resistance and capacitor ESR. See the details in Application and Implementation for positive voltage doubler. The output switches operate at one half of the oscillator frequency, $f_{\rm OSC}$ = 2 × $f_{\rm SW}$.

TEXAS INSTRUMENTS

6.6 Typical Characteristics

(Circuit of *Typical Voltage Doubler Application*, V_{IN} = 5 V, T_A = 25°C unless otherwise specified)




Figure 1. Supply Current vs Supply Voltage




Figure 2. Output Resistance vs Capacitance




Figure 3. Output Resistance vs Supply Voltage




Figure 4. Output Resistance vs Temperature




Figure 5. Output Voltage vs Load Current





Figure 6. Switching Frequency vs Supply Voltage

Submit Documentation Feedback




Typical Characteristics (continued)

(Circuit of *Typical Voltage Doubler Application*, V_{IN} = 5 V, T_A = 25°C unless otherwise specified)



7 Parameter Measurement Information

7.1 Test Circuit



* $\mathrm{C_{IN}},~\mathrm{C_{1}}$, and $\mathrm{C_{2}}$ are 1.0 $\mu\mathrm{F}$ OS-CON capacitors.

Figure 9. LM2766 Test Circuit




8 Detailed Description

8.1 Overview

The LM2766 CMOS charge-pump voltage converter operates as a voltage doubler for an input voltage in the range of 1.8 V to 5.5 V. Two low-cost capacitors and a diode (needed during start-up) are used in this circuit.

8.2 Functional Block Diagram



8.3 Feature Description

8.3.1 Test Circuit

The LM2766 contains four large CMOS switches which are switched in a sequence to double the input supply voltage. Energy transfer and storage are provided by external capacitors. Figure 10 illustrates the voltage conversion scheme. When S_2 and S_4 are closed, C_1 charges to the supply voltage V+. During this time interval, switches S_1 and S_3 are open. In the next time interval, S_2 and S_4 are open; at the same time, S_1 and S_3 are closed, the sum of the input voltage V+ and the voltage across C_1 gives the 2 V+ output voltage when there is no load. The output voltage drop when a load is added is determined by the parasitic resistance ($R_{ds(on)}$) of the MOSFET switches and the ESR of the capacitors) and the charge transfer loss between capacitors. See Application and Implementation for further details.




Figure 10. Voltage Doubling Principle

8.4 Device Functional Modes

8.4.1 Shutdown Mode

A shutdown (\overline{SD}) pin is available to disable the device and reduce the quiescent current to 0.1 μ A. In normal operating mode, the \overline{SD} pin is connected to V+. The device can be brought into the shutdown mode by applying to the \overline{SD} pin a voltage less than 20% of the V+ pin voltage.



9 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

9.1 Application Information

The LM2766 provides a simple and efficient means of creating an output voltage level equal to twice that of the input voltage. Without the need of an inductor, the application solution size can be reduced versus the magnetic DC-DC converter solution.

9.2 Typical Application

The main application of the LM2766 is to double the input voltage.




Figure 11. LM2766 Typical Application

9.2.1 Design Requirements

For typical switched-capacitor voltage converter applications, use the parameters listed in Table 1.

Table 1. Design Parameters

| DESIGN PARAMETER | EXAMPLE VALUE |
|---|-------------------|
| Minimum input voltage | 1.8 to 5.5 V |
| Output current (minimum), 2.5 V ≤ V _{IN} ≤ 5.5 V | 20 mA |
| Output current (minimum), 1.8 V ≤ V _{IN} ≤ 2.5 V | 10 mA |
| Switching frequency | 200 kHz (typical) |

9.2.2 Detailed Design Procedure

9.2.2.1 Positive Voltage Doubler




Figure 12. Voltage Doubling Principle



The output characteristics of this circuit can be approximated by an ideal voltage source in series with a resistance. The voltage source equals 2 V+. The output resistance R_{out} is a function of the ON resistance of the internal MOSFET switches, the oscillator frequency, and the capacitance and ESR of C_1 and C_2 . Because the switching current charging and discharging C_1 is approximately twice the output current, the effect of the ESR of the pumping capacitor C_1 is multiplied by four in the output resistance. The output capacitor C_2 is charging and discharging at a current approximately equal to the output current, therefore, its ESR only counts once in the output resistance. A good approximation of R_{out} is:

$$R_{OUT} \cong 2R_{SW} + \frac{2}{f_{OSC} \times C_1} + 4ESR_{C1} + ESR_{C2}$$

where

• R_{SW} is the sum of the ON resistance of the internal MOSFET switches shown in Figure 12. (1)

The peak-to-peak output voltage ripple is determined by the oscillator frequency as well as the capacitance and ESR of the output capacitor C_2 :

$$V_{RIPPLE} = \frac{I_L}{f_{OSC} \times C_2} + 2 \times I_L \times ESR_{C2}$$
 (2)

High capacitance, low ESR capacitors can reduce both the output resistance and the voltage ripple.

The Schottky diode D_1 is only needed to protect the device from turning on its own parasitic diode and potentially latching up. During start-up, D_1 also quickly charges up the output capacitor to V_{IN} minus the diode drop thereby decreasing the start-up time. Therefore, the Schottky diode D_1 must have enough current carrying capability to charge the output capacitor at start-up, as well as a low forward voltage to prevent the internal parasitic diode from turning on. A Schottky diode like 1N5817 can be used for most applications. If the input voltage ramp is less than 10 V/ms, a smaller Schottky diode like MBR0520LT1 can be used to reduce the circuit size.

9.2.2.2 Capacitor Selection

As discussed in *Positive Voltage Doubler*, the output resistance and ripple voltage are dependent on the capacitance and ESR values of the external capacitors. The output voltage drop is the load current times the output resistance, and the power efficiency is

$$\eta = \frac{{{P_{OUT}}}}{{{P_{IN}}}} = \frac{{{I_L}^2}{{R_L}}}{{{I_L}^2}{{R_L}} + {I_L}^2{{R_{OUT}}} + {I_Q}(V+)}$$

where

- I_O(V+) is the quiescent power loss of the device; and
- I_L²R_{OUT} is the conversion loss associated with the switch on-resistance, the two external capacitors and their ESRs.

The selection of capacitors is based on the specifications of the dropout voltage (which equals I_{OUT} R_{OUT}), the output voltage ripple, and the converter efficiency. Low ESR capacitors (Table 2) are recommended to maximize efficiency, reduce the output voltage drop and voltage ripple.


Table 2. Low ESR Capacitor Manufacturers

| MANUFACTURER | WEBSITE | CAPACITOR TYPE |
|----------------|------------------------------------|--|
| Nichicon Corp. | www.nichicon.com | PL & PF series, through-hole aluminum electrolytic |
| AVX Corp. | TPS series, surface-mount tantalum | |
| Sprague | www.vishay.com | 593D, 594D, 595D series, surface-mount tantalum |
| Sanyo | www.sanyovideo.com | OS-CON series, through-hole aluminum electrolytic |
| Murata | www.murata.com | Ceramic chip capacitors |
| Taiyo Yuden | www.t-yuden.com | Ceramic chip capacitors |
| Tokin | www.tokin.com | Ceramic chip capacitors |



9.2.2.3 Paralleling Devices

Any number of LM2766 devices can be paralleled to reduce the output resistance. Because there is no closed loop feedback, as found in regulated circuits, stable operation is assured. Each device must have its own pumping capacitor C_1 , while only one output capacitor C_{OUT} is needed as shown in Figure 13. The composite output resistance is:






Figure 13. Lowering Output Resistance By Paralleling Devices

9.2.2.4 Cascading Devices

Cascading the several LM2766 devices is an easy way to produce a greater voltage (a two-stage cascade circuit is shown in Figure 14).

The effective output resistance is equal to the weighted sum of each individual device:

$$R_{\text{out}} = 1.5R_{\text{out}_1} + R_{\text{out}_2} \tag{5}$$

Note that increasing the number of cascading stages is practically limited because it significantly reduces the efficiency, increases the output resistance and output voltage ripple.




Figure 14. Increasing Output Voltage By Cascading Devices

Copyright © 2000–2015, Texas Instruments Incorporated

Submit Documentation Feedback



9.2.2.5 Regulating V_{OUT}

It is possible to regulate the output of the LM2766 by use of a low dropout regulator (such as LP2980-5.0). The whole converter is depicted in Figure 15.

A different output voltage is possible by use of LP2980-3.3, LP2980-3.0, or LP2980-ADJ.

The following conditions must be satisfied simultaneously for worst case design:

$$2V_{\text{in_min}} > V_{\text{out_min}} + V_{\text{drop_max}} \text{ (LP2980)} + I_{\text{out_max}} \times R_{\text{out_max}} \text{ (LM2766)}$$
(6)

$$2V_{\text{in_max}} < V_{\text{out_max}} + V_{\text{drop_min}} \text{ (LP2980)} + I_{\text{out_min}} \times R_{\text{out_min}} \text{ (LM2766)}$$

$$(7)$$




Figure 15. Generate a Regulated 5-V From 3-V Input Voltage

9.2.3 Application Curve




Figure 16. Efficiency vs Load Current

10 Power Supply Recommendations

The LM2766 is designed to operate from as an inverter over an input voltage supply range from 1.8 V and 5.5 V. This input supply must be well-regulated and capable to supply the required input current. If the input supply is located far from the device, additional bulk capacitance may be required in addition to the ceramic bypass capacitors.



11 Layout

11.1 Layout Guidelines

The high switching frequency and large switching currents of the LM2766 make the choice of layout important. Use the following steps as a reference to ensure the device is stable and maintains proper LED current regulation across its intended operating voltage and current range.

- Place C_{IN} on the top layer (same layer as the LM2766) and as close to the device as possible. Connecting the input capacitor through short, wide traces to both the V+ and GND pins reduces the inductive voltage spikes that occur during switching which can corrupt the V+ line.
- Place C_{OUT} on the top layer (same layer as the LM2766) and as close as possible to the OUT and GND pin. The returns for both C_{IN} and C_{OUT} must come together at one point, as close to the GND pin as possible. Connecting Court through short, wide traces reduce the series inductance on the OUT and GND pins that can corrupt the V_{OUT} and GND lines and cause excessive noise in the device and surrounding circuitry.
- Place C1 on the top layer (same layer as the LM2766 device) and as close to the device as possible. Connect the flying capacitor through short, wide traces to both the CAP+ and CAP- pins.

11.2 Layout Example




Figure 17. LM2766 Layout Example



12 Device and Documentation Support

12.1 Device Support

12.1.1 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

12.2 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E™ Online Community T's Engineer-to-Engineer (E2E) Community. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

12.3 Trademarks

E2E is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.

12.4 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

12.5 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



PACKAGE OPTION ADDENDUM

10-Dec-2020

PACKAGING INFORMATION

www.ti.com

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead finish/ Ball material | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|------------|--------------|--------------------|------|----------------|--------------|-------------------------------|--------------------|--------------|-------------------------|---------|
| LM2766M6/NOPB | ACTIVE | SOT-23 | DBV | 6 | 1000 | RoHS & Green | SN | Level-1-260C-UNLIM | -40 to 85 | S16B | Samples |
| LM2766M6X/NOPB | ACTIVE | SOT-23 | DBV | 6 | 3000 | RoHS & Green | SN | Level-1-260C-UNLIM | -40 to 85 | S16B | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.






10-Dec-2020

PACKAGE MATERIALS INFORMATION

www.ti.com 20-Dec-2016

TAPE AND REEL INFORMATION





| | Dimension designed to accommodate the component width |
|----|---|
| | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | Package Type | Package Drawing | | | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------|-----------------|--------------------|---|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| LM2766M6/NOPB | SOT-23 | DBV | 6 | 1000 | 178.0 | 8.4 | 3.2 | 3.2 | 1.4 | 4.0 | 8.0 | Q3 |
| LM2766M6X/NOPB | SOT-23 | DBV | 6 | 3000 | 178.0 | 8.4 | 3.2 | 3.2 | 1.4 | 4.0 | 8.0 | Q3 |

www.ti.com 20-Dec-2016



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LM2766M6/NOPB | SOT-23 | DBV | 6 | 1000 | 210.0 | 185.0 | 35.0 |
| LM2766M6X/NOPB | SOT-23 | DBV | 6 | 3000 | 210.0 | 185.0 | 35.0 |



SMALL OUTLINE TRANSISTOR



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.25 per side.

- 4. Leads 1,2,3 may be wider than leads 4,5,6 for package orientation. 5. Refernce JEDEC MO-178.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated