

HB-2X2-O

~20° + 115° oval beam for aisle lighting

TECHNICAL SPECIFICATIONS:

Dimensions	50.0 x 50.0 mm
Height	10.6 mm
Fastening	glue, pin, screw
ROHS compliant	yes ⓘ


MATERIAL SPECIFICATIONS:

Component	Type	Material	Colour	Finish
HB-2X2-O	Multi-lens	PMMA	clear	

ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C13749_HB-2X2-O » Box size: 480 x 280 x 300 mm	800	160	160	10.4






See also our general installation guide: www.ledil.com/installation_guide


PHOTOMETRIC DATA (MEASURED):





LED QUICK FLUX XTP 2x4 xxx LS G5
FWHM / FWTM 21.0 + 111.0° / 32.0 + 148.0°
Efficiency 94 %
Peak intensity 1.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED QUICK FLUX XTP 2x6 xxx LS G5
FWHM / FWTM 22.0 + 111.0° / 33.0 + 149.0°
Efficiency 94 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:











LED XD16
FWHM / FWTM 29.0 + 116.0° / 44.0 + 141.0°
Efficiency 94 %
Peak intensity 1 cd/lm
LEDs/each optic 4
Light colour White
Required components:



LED XD16
FWHM / FWTM 19.0 + 127.0° / 28.0 + 141.0°
Efficiency 93 %
Peak intensity 1.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:





PHOTOMETRIC DATA (MEASURED):

<p>CREE ⇄ LED</p> <p>LED XHP35 HD FWHM / FWTM 29.0 + 117.0° / 48.0 + 148.0° Efficiency 94 % Peak intensity 0.9 cd/lm LEDs/each optic 1 Light colour White Required components:</p>		
<p>CREE ⇄ LED</p> <p>LED XM-L FWHM / FWTM 28.0 + 108.0° / 45.0 + 142.0° Efficiency 94 % Peak intensity 1 cd/lm LEDs/each optic 1 Light colour White Required components:</p>		
<p>CREE ⇄ LED</p> <p>LED XM-L2 FWHM / FWTM 30.0 + 106.0° / 48.0 + 143.0° Efficiency 94 % Peak intensity 1 cd/lm LEDs/each optic 1 Light colour White Required components:</p>		
<p>CREE ⇄ LED</p> <p>LED XP-G FWHM / FWTM 26.0 + 115.0° / 44.0 + 158.0° Efficiency 94 % Peak intensity 1.1 cd/lm LEDs/each optic 1 Light colour White Required components:</p>		

PHOTOMETRIC DATA (MEASURED):


CREE ⇄ LED

LED XP-G2
 FWHM / FWTM 27.0 + 112.0° / 42.0 + 146.0°
 Efficiency 94 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





CREE ⇄ LED

LED XP-L HD
 FWHM / FWTM 29.0 + 117.0° / 48.0 + 144.0°
 Efficiency 94 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





CREE ⇄ LED

LED XP-L HI
 FWHM / FWTM 25.0 + 123.0° / 41.0 + 143.0°
 Efficiency 94 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:











CREE ⇄ LED

LED XP-L2
 FWHM / FWTM 28.0 + 117.0° / 47.0 + 150.0°
 Efficiency 94 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





PHOTOMETRIC DATA (MEASURED):

<p>LUMILEDS</p> <p>LED LUXEON 5050 Round LES</p> <p>FWHM / FWTM 29.0 + 114.0° / 51.0 + 147.0°</p> <p>Efficiency 94 %</p> <p>Peak intensity 0.9 cd/m</p> <p>LEDs/each optic 1</p> <p>Light colour White</p> <p>Required components:</p>		
<p>LUMILEDS</p> <p>LED LUXEON MZ</p> <p>FWHM / FWTM 28.0 + 103.0° / 43.0 + 14.0°</p> <p>Efficiency 94 %</p> <p>Peak intensity 1.1 cd/m</p> <p>LEDs/each optic 1</p> <p>Light colour White</p> <p>Required components:</p>		
<p>LUMILEDS</p> <p>LED LUXEON R</p> <p>FWHM / FWTM 25.0 + 105.0° / 44.0 + 148.0°</p> <p>Efficiency 94 %</p> <p>Peak intensity 1.2 cd/m</p> <p>LEDs/each optic 1</p> <p>Light colour White</p> <p>Required components:</p>		
<p>LUMILEDS</p> <p>LED LUXEON Rebel ES</p> <p>FWHM / FWTM 25.0 + 106.0° / 42.0 + 150.0°</p> <p>Efficiency 94 %</p> <p>Peak intensity 1.2 cd/m</p> <p>LEDs/each optic 1</p> <p>Light colour White</p> <p>Required components:</p>		

PHOTOMETRIC DATA (MEASURED):



LUMILEDS

LED LUXEON T
 FWHM / FWTM 26.0 + 110.0° / 41.0 + 145.0°
 Efficiency 94 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




LUMILEDS

LED LUXEON TX
 FWHM / FWTM 24.0 + 118.0° / 42.0 + 146.0°
 Efficiency 94 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




LUMILEDS

LED LUXEON V
 FWHM / FWTM 26.0 + 108.0° / 44.0 + 141.0°
 Efficiency 94 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LUMINUS



LED SST-10-B130
 FWHM / FWTM 18.0 + 104.0° / 25.0 + 144.0°
 Efficiency 97 %
 Peak intensity 1.6 cd/lm
 LEDs/each optic 1
 Light colour Deep Red
 Required components:



PHOTOMETRIC DATA (MEASURED):



MST *Your solutions*

LED RecLED 122x50mm 1900lm 730 2x4 Opt G1
 FWHM / FWTM 23.0 + 99.5° / 32.5 + 145.0°
 Efficiency 97 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





NICHIA

LED NCSxx19B
 FWHM / FWTM 23.0 + 113.0° / 39.0 + 146.0°
 Efficiency 94 %
 Peak intensity 1.4 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





NICHIA

LED NVSW219D
 FWHM / FWTM 25.0 + 107.0° / 37.0 + 137.0°
 Efficiency 94 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:











NICHIA

LED NVSW319B
 FWHM / FWTM 25.0 + 113.0° / 41.0 + 144.0°
 Efficiency 94 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





PHOTOMETRIC DATA (MEASURED):

<p>NICHIA</p> <p>LED NVSW3x9A FWHM / FWTM 24.0 + 119.0° / 38.0 + 144.0° Efficiency 94 % Peak intensity 1.1 cd/lm LEDs/each optic 1 Light colour White Required components:</p>		
<p>NICHIA</p> <p>LED NVSW3x9A FWHM / FWTM 25.0 + 134.0° / 43.0 + 147.0° Efficiency 93 % Peak intensity 0.4 cd/lm LEDs/each optic 1 Light colour White Required components:</p>		
<p>NICHIA</p> <p>LED NVSxE21A FWHM / FWTM 17.0 + 125.0° / 27.0 + 139.0° Efficiency 94 % Peak intensity 1.7 cd/lm LEDs/each optic 1 Light colour White Required components:</p>		
<p>NICHIA</p> <p>LED NVSxx19A FWHM / FWTM 24.0 + 105.0° / 44.0 + 148.0° Efficiency 94 % Peak intensity 1.2 cd/lm LEDs/each optic 1 Light colour White Required components:</p>		



PHOTOMETRIC DATA (MEASURED):





LED NVSxx19B/NVSxx19C
 FWHM / FWTM 26.0 + 108.0° / 41.0 + 145.0°
 Efficiency 94 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





LED NWSx229A
 FWHM / FWTM 27.0 + 118.0° / 43.0 + 143.0°
 Efficiency 94 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED PL-BRICK HP 3800 2x8 SSG
 FWHM / FWTM 26.0 + 102.0° / 37.0 + 139.0°
 Efficiency 97 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED PrevaLED Brick HP 2x8
 FWHM / FWTM 23.0 + 111.0° / 32.0 + 141.0°
 Efficiency 94 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





PHOTOMETRIC DATA (MEASURED):

OSRAM

Opto Semiconductors



LED OSLON Square CSSRM2/CSSRM3
 FWHM / FWTM 23.0 + 111.0° / 32.0 + 141.0°
 Efficiency 94 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



OSRAM



Opto Semiconductors

LED OSLON Square PC
 FWHM / FWTM 25.0 + 124.0° / 42.0 + 145.0°
 Efficiency 91 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





PHILIPS

LED Fortimo FastFlex LED 2x8 DA G4
 FWHM / FWTM 21.0 + 108.0° / 31.0 + 147.0°
 Efficiency 94 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHILIPS



LED Fortimo FastFlex LED 2x8 DA G4+
 FWHM / FWTM 24.0 + 104.0° / 37.0 + 145.0°
 Efficiency 97 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHOTOMETRIC DATA (MEASURED):



PHILIPS

LED Fortimo FastFlex LED 2x8 DA G5
 FWHM / FWTM 24.0 + 103.0° / 34.0 + 144.0°
 Efficiency 97 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





PHILIPS

LED Fortimo FastFlex LED 2x8 DA HE
 FWHM / FWTM 32.0 + 98.0° / 51.0 + 142.0°
 Efficiency 98 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





SAMSUNG

LED HiLOM RC12 Z (LH181B)
 FWHM / FWTM 19.0 + 106.0° / 31.0 + 140.0°
 Efficiency 98 %
 Peak intensity 1.4 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



SAMSUNG



LED HiLOM RH12 Z (LH351C)
 FWHM / FWTM 23.0 + 102.0° / 36.0 + 139.0°
 Efficiency 97 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHOTOMETRIC DATA (MEASURED):



SAMSUNG

LED HiLOM RH16 (LH351C)
 FWHM / FWTM 23.0 + 106.0° / 36.0 + 140.0°
 Efficiency 94 %
 Peak intensity 1.2 cd/m
 LEDs/each optic 1
 Light colour White
 Required components:





SAMSUNG

LED HiLOM RM12 Z (LH502C)
 FWHM / FWTM 35.0 + 98.0° / 76.0 + 141.0°
 Efficiency 96 %
 Peak intensity 0.8 cd/m
 LEDs/each optic 1
 Light colour White
 Required components:





SAMSUNG

LED LH351B
 FWHM / FWTM 23.0 + 113.0° / 35.0 + 141.0°
 Efficiency 94 %
 Peak intensity 1.2 cd/m
 LEDs/each optic 1
 Light colour White
 Required components:



SAMSUNG


LED LH351C
 FWHM / FWTM 24.0 + 111.0° / 37.0 + 141.0°
 Efficiency 94 %
 Peak intensity 1.1 cd/m
 LEDs/each optic 1
 Light colour White
 Required components:



PHOTOMETRIC DATA (MEASURED):



SAMSUNG

LED LH351D
 FWHM / FWTM 27.0 + 116.0° / 44.0 + 144.0°
 Efficiency 94 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





SAMSUNG



LED LH351Z
 FWHM / FWTM 26.0 + 117.0° / 42.0 + 141.0°
 Efficiency 94 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:











LED LED-Pa-L15c2W11c2-xxx-C050-01
 FWHM / FWTM 22.0 + 105.0° / 36.0 + 142.0°
 Efficiency 98 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



SEOL SEMICONDUCTOR
 LED Z5M3
 FWHM / FWTM 23.0 + 113.0° / 39.0 + 146.0°
 Efficiency 94 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHOTOMETRIC DATA (MEASURED):

<p>SEOUL SEMICONDUCTOR</p> <p>LED Z5M4</p> <p>FWHM / FWTM 22.0 + 97.0° / 35.0 + 135.0°</p> <p>Efficiency 98 %</p> <p>Peak intensity 1.3 cd/lm</p> <p>LEDs/each optic 1</p> <p>Light colour White</p> <p>Required components:</p>		
<p>SEOUL SEMICONDUCTOR</p> <p>LED Z8Y22</p> <p>FWHM / FWTM 21.0 + 121.0° / 99.0 + 140.0°</p> <p>Efficiency 94 %</p> <p>Peak intensity 1.2 cd/lm</p> <p>LEDs/each optic 1</p> <p>Light colour White</p> <p>Required components:</p>		
<p>SEOUL SEMICONDUCTOR</p> <p>LED Z8Y22P</p> <p>FWHM / FWTM 23.0 + 121.0° / 34.0 + 150.0°</p> <p>Efficiency 94 %</p> <p>Peak intensity 1.1 cd/lm</p> <p>LEDs/each optic 1</p> <p>Light colour White</p> <p>Required components:</p>		
<p>TOSHIBA Leading Innovation >>></p> <p>LED TL1L4</p> <p>FWHM / FWTM 24.0 + 119.0° / 39.0 + 140.0°</p> <p>Efficiency 89 %</p> <p>Peak intensity 1.1 cd/lm</p> <p>LEDs/each optic 1</p> <p>Light colour White</p> <p>Required components:</p>		



PHOTOMETRIC DATA (MEASURED):

TRIDONIC

LED RLE 2x4 2000lm HP EXC2 OTD
 FWHM / FWTM 22.0 + 113.0° / 30.0 + 149.0°
 Efficiency 94 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:


TRIDONIC

LED RLE 2x8 4000lm HP EXC2 OTD
 FWHM / FWTM 22.0 + 113.0° / 30.0 + 149.0°
 Efficiency 94 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




TRIDONIC

LED RLE G1 49x121mm 2000lm xxx EXC OTD
 FWHM / FWTM 23.0 + 104.0° / 31.0 + 144.0°
 Efficiency 94 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



TRIDONIC


LED RLE G1 49x133mm 2000lm xxx EXC OTD
 FWHM / FWTM 23.0 + 104.0° / 31.0 + 144.0°
 Efficiency 94 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHOTOMETRIC DATA (MEASURED):



TRIDONIC

LED RLE G1 49x223mm 4000lm xxx EXC OTD
 FWHM / FWTM 23.0 + 104.0° / 31.0 + 144.0°
 Efficiency 94 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



TRIDONIC


LED RLE G1 49x245mm 4000lm xxx EXC OTD
 FWHM / FWTM 23.0 + 104.0° / 31.0 + 144.0°
 Efficiency 94 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




PHOTOMETRIC DATA (SIMULATED):




LED J Series 5050 Round LES
 FWHM / FWTM 30.0 + 97.0° / 51.0 + 141.0°
 Efficiency 94 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




LED XHP35 HI
 FWHM / FWTM 101.0 + 27.0° / 145.0 + 44.0°
 Efficiency 94 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED XHP50.3 HI
 FWHM / FWTM 28.0 + 100.0° / 44.0 + 144.0°
 Efficiency 95 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED XP-E2
 FWHM / FWTM 93.0 + 18.0° / 141.0 + 30.0°
 Efficiency 94 %
 Peak intensity 1.6 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




PHOTOMETRIC DATA (SIMULATED):

CREE LED


LED XP-G2
 FWHM / FWTM 21.0 + 98.0° / 33.0 + 141.0°
 Efficiency 91 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:

Protective plate, glass




CREE LED

LED XP-G2 HE
 FWHM / FWTM 28.0 + 103.0° / 41.0 + 144.0°
 Efficiency 94 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



CREE LED

LED XP-G3
 FWHM / FWTM 103.0 + 29.0° / 146.0 + 49.0°
 Efficiency 94 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



CREE LED

LED XQ-E HI
 FWHM / FWTM 96.0 + 14.0° / 144.0 + 25.0°
 Efficiency %
 LEDs/each optic 1
 Light colour White
 Required components:

PHOTOMETRIC DATA (SIMULATED):

<p>CREE LED</p> <p>LED: XT-E HE FWHM / FWTM: 100.0 + 24.0° Efficiency: 94 % LEDs/each optic: 1 Light colour: White Required components:</p>	
<p>LUMILEDS</p> <p>LED: LUXEON 5050 Round LES FWHM / FWTM: 30.0 + 96.0° / 48.0 + 140.0° Efficiency: 88 % Peak intensity: 0.9 cd/lm LEDs/each optic: 1 Light colour: White Required components:</p> <p style="background-color: #ADD8E6; padding: 2px; display: inline-block;">Protective plate, glass</p>	
<p>LUMILEDS</p> <p>LED: LUXEON 5050 Square LES FWHM / FWTM: 30.0 + 98.0° / 50.0 + 142.0° Efficiency: 95 % Peak intensity: 0.9 cd/lm LEDs/each optic: 1 Light colour: White Required components:</p>	
<p>LUMILEDS</p> <p>LED: LUXEON IR Domed 150 FWHM / FWTM: 16.0 + 98.0° / 28.0 + 149.0° Efficiency: 94 % Peak intensity: 1.4 cd/lm LEDs/each optic: 1 Light colour: White Required components:</p>	

PHOTOMETRIC DATA (SIMULATED):


<p>LUMILEDS</p> <p>LED: LUXEON IR Domed 90 FWHM / FWTM: 20.0 + 86.0° / 29.0 + 128.0° Efficiency: 95 % Peak intensity: 1.6 cd/lm LEDs/each optic: 1 Light colour: White Required components:</p>	
<p>MST <i>Your solutions</i></p> <p>LED: RecLED 122x50mm 1900lm 730 2x4 Opt G1 FWHM / FWTM: 24.0 + 97.0° / 34.0 + 141.0° Efficiency: 86 % Peak intensity: 1.1 cd/lm LEDs/each optic: 1 Light colour: White Required components:</p> <p style="background-color: #ADD8E6; padding: 2px; display: inline-block;">Protective plate, glass</p>	
<p>NICHIA</p> <p>LED: NV4WB35AM FWHM / FWTM: 28.0 + 100.0° / 42.0 + 144.0° Efficiency: 95 % Peak intensity: 1 cd/lm LEDs/each optic: 1 Light colour: White Required components:</p>	
<p>OSRAM <small>Opto Semiconductors</small></p> <p>LED: OSCONIQ C 2424 FWHM / FWTM: 18.0 + 96.0° / 30.0 + 141.0° Efficiency: 96 % Peak intensity: 1.5 cd/lm LEDs/each optic: 1 Light colour: White Required components:</p>	

PHOTOMETRIC DATA (SIMULATED):

OSRAM

Opto Semiconductors


LED OSCONIQ P 3030
 FWHM / FWTM 14.0 + 92.0° / 28.0 + 142.0°
 Efficiency 95 %
 Peak intensity 1.6 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



OSRAM

Opto Semiconductors


LED OSCONIQ P 3737 (2W version)
 FWHM / FWTM 99.0 + 19.0° / 142.0 + 31.0°
 Efficiency 94 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



OSRAM

Opto Semiconductors


LED OSCONIQ P 3737 (3W version)
 FWHM / FWTM 100.0 + 30.0° / 144.0 + 51.0°
 Efficiency 94 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



OSRAM

Opto Semiconductors

LED OSCONIQ P 3737 Flat
 FWHM / FWTM 22.0 + 98.0° / 35.0 + 142.0°
 Efficiency 96 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




PHOTOMETRIC DATA (SIMULATED):

OSRAM

Opto Semiconductors


LED OSCONIQ S 5050
 FWHM / FWTM 32.0 + 99.0° / 52.0 + 143.0°
 Efficiency 96 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



OSRAM

Opto Semiconductors

LED OSCONIQ S 5050
 FWHM / FWTM 32.0 + 98.0° / 53.0 + 140.0°
 Efficiency 85 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




Protective plate, glass

OSRAM

Opto Semiconductors

LED OSLON Square CSSRM2/CSSRM3
 FWHM / FWTM 23.0 + 101.0° / 33.0 + 140.0°
 Efficiency 85 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




Protective plate, glass

OSRAM

Opto Semiconductors

LED OSLON Square Flat
 FWHM / FWTM 16.0 + 90.0° / 30.0 + 140.0°
 Efficiency 96 %
 Peak intensity 1.6 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




PHOTOMETRIC DATA (SIMULATED):

OSRAM


Opto Semiconductors

LED OSTAR Projection Compact (Kx.CSLNM1.xx)
 FWHM / FWTM 16.0 + 89.0° / 28.0 + 140.0°
 Efficiency 96 %
 Peak intensity 1.7 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHILIPS


LED Fortimo FastFlex LED 2x8 DAX G4
 FWHM / FWTM 103.0 + 29.0° / 146.0 + 49.0°
 Efficiency 94 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



SAMSUNG


LED HiLOM RM12 Z (LH502C)
 FWHM / FWTM 36.0 + 98.0° / 78.0 + 140.0°
 Efficiency 89 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:

Protective plate, glass



SEOUL SEMICONDUCTOR

LED MJT 5050
 FWHM / FWTM 32.0 + 98.0° / 52.0 + 142.0°
 Efficiency 94 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHOTOMETRIC DATA (SIMULATED):

<p>SEOUL SEMICONDUCTOR</p> <p>LED: SEOUL DC 5050 6V</p> <p>FWHM / FWTM: 33.0 + 98.0° / 58.0 + 143.0°</p> <p>Efficiency: 94 %</p> <p>Peak intensity: 0.9 cd/lm</p> <p>LEDs/each optic: 1</p> <p>Light colour: White</p> <p>Required components:</p>	
<p>SEOUL SEMICONDUCTOR</p> <p>LED: Z5M1/Z5M2</p> <p>FWHM / FWTM: 22.0 + 97.0° / 34.0 + 142.0°</p> <p>Efficiency: 94 %</p> <p>Peak intensity: 1.2 cd/lm</p> <p>LEDs/each optic: 1</p> <p>Light colour: White</p> <p>Required components:</p>	
<p>SEOUL SEMICONDUCTOR</p> <p>LED: Z8Y22T</p> <p>FWHM / FWTM: 21.0 + 96.0° / 33.0 + 141.0°</p> <p>Efficiency: 94 %</p> <p>Peak intensity: 1.2 cd/lm</p> <p>LEDs/each optic: 1</p> <p>Light colour: White</p> <p>Required components:</p>	

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ledi:](#)

[C13749_HB-2X2-O](#)