CUI DEVICES

date 10/25/2019

page 1 of 4

MODEL: PJ-084BH | DESCRIPTION: DC POWER JACK

FEATURES

- 2.5 mm center pin
- 5 A rating
- shielded
- through hole
- 1 switch





SPECIFICATIONS

parameter	conditions/description	min	typ	max	units
rated input voltage			24		Vdc
rated input current				5.0	А
contact resistance ¹	between terminal and mating plug between terminal in a closed circuit			50 30	mΩ mΩ
insulation resistance	at 500 Vdc between adjacent contacts	100			MΩ
voltage withstand	for 1 minute, 0.5 mA between adjacent contacts			500	Vac
insertion/withdrawal force		0.3		3	kg
operating temperature		-25		85	°C
life	at a rate of 24 cycles/minute		5,000		cycles
flammability rating	UL94V-0				
RoHS	yes				


- 1. When measured at a current of less than 100 mA/1 kHz 2. All specifications measured at $10\sim35^{\circ}$ C, humidity at $45\sim85\%$, under standard atmospheric pressure, unless otherwise noted.

SOLDERABILITY

parameter	conditions/description	min	typ	max	units
reel storage	at relative humidity <80%			40	°C
reflow soldering ³	see reflow profile	255	260	265	°C
drying conditions ⁴	parts in reel: bake at 40°C ±5°C for 72 hours parts removed from reel: bake at 40°C ±5°C for 10) hours			


Note:

- 3. It is recommended to reflow solder within 72 hours from opening vacuum packaging at a temperature <30°C & relative humidity <60%.
- 4. When exceeding floor life by >72 hours.





MECHANICAL DRAWING


units: mm tolerance: $X.X \pm 0.2 \text{ mm}$ $X.XX \pm 0.10 \text{ mm}$ $X.XXX \pm 0.050 \text{ mm}$ PCB: ±0.05 mm





	MATERIAL	PLATING
center pin	copper	nickel
terminal 1	brass	silver
terminal 2	copper alloy	silver
terminal 3	brass	silver
shield A	brass	nickel
shield B	stainless steel	
insulator	PA10T	












Recommended PCB Layout Top View




MATING PLUG Jack Insertion Depth: 8.2 mm


SCHEMATIC	01
Model	PJ-084BH
Center Pin	Ø2.5 mm


PACKAGING

units: mm

Reel Size: Ø381 mm Reel QTY: 600 pcs per reel







CUI Devices | MODEL: PJ-084BH | DESCRIPTION: DC POWER JACK date 10/25/2019 | page 4 of 4

REVISION HISTORY

rev.	description	date
1.0	initial release	12/12/2018
1.01	brand update	10/25/2019

The revision history provided is for informational purposes only and is believed to be accurate.

CUI DEVICES

CUI Devices offers a one (1) year limited warranty. Complete warranty information is listed on our website.

CUI Devices reserves the right to make changes to the product at any time without notice. Information provided by CUI Devices is believed to be accurate and reliable. However, no responsibility is assumed by CUI Devices for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI Devices products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.