


## NOTES:

- 1. INSTALLATION:
  - 1. INSTALL THE JACK AND THE WASHER (IF NEEDED) FROM THE BACK OF THE PANEL.
  - 2. INSTALL THE ORING AND THEN THE HEX NUT FROM THE FRON OF THE PANEL.
  - 3. TIGHTEN THE NUT.
  - 4. SEE THE TABLE BELOW FOR INSTALLATION INSTRUCTIONS:

Panel thickness /Inches	0.050	0.055	0.060	0.065	0.070	0.075	0.080	0.085	0.090	0.095	0.100	0.105	0.110	0.115	0.120	0.125				
Kit part number		W07 (LARGE)										W11 (SMALL)								
Washer (K180)	yes	yes	yes	yes	yes	no	no	no	no	yes	yes	yes	yes	yes	no	no				

- 2. HEX NUT FINISH: NICKEL
- 3. TO BE USED WITH 250S15-S28 PLUGS.
- 4. IP RATING: IP66
- 5. RECOMMENDED HOLE DIAMETER:  $\emptyset$  0.375" [9.5MM]
- 6. RECOMMENDED WORKING TEMPERATURE: -20TO 50 °C.
- 7. RoHS COMPLIANT.



## **CUSTOMER DRAWING**

						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROF BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFID													
					UNLESS OTHERWISE SPECIFIED	SIZE *	٧	WIDTH * MU		MULT *		LBS/M		TEMPE					
					1. ALL DIMENSIONS IN INCHES [mm]	FINISH	*			MATERIAL			*	*					
					- TWO PLACE DECIMALS ±0.02 [0.5]	SPEC No.	*				SPEC No. *								
					- THREE PLACE DECIMALS ±0.005 [0.13]	FIRST USED C				ALE :1			.Γh.			TL®			
						DATE DRAWN	] ] ] 0		-   '"'-					) GF4					
	DDEL IMPLADA	0/47/00	NIO	000		2/17/20 NS		NS		SRC									
0A	PRELIMINARY	2/17/20	NS	SRC		2,17720	. 10	2/17/2	20   2	2/17/20		SHEET	1	OF	1				
REV	ECO NUMBER	DATE	BY	APVD		NAME		-			PART No					REV			
REVISIONS					DO NOT SCALE DRAWING	SEALED 1/4" JACK			11W07-W11				0A						