


## NOTES:

- 1. INSTALLATION:
  - 1. INSTALL THE JACK AND THE WASHER (IF NEEDED) FROM THE BACK OF THE PANEL.
  - 2. INSTALL THE ORING AND THEN THE HEX NUT FROM THE FRON OF THE PANEL.
  - 3. TIGHTEN THE NUT.
  - 4. SEE THE TABLE BELOW FOR INSTALLATION INSTRUCTIONS:

Panel thickness /Inche	s <b>0.050</b>	0.055	0.060	0.065	0.070	0.075	0.080	0.085	0.090	0.095	0.100	0.105	0.110	0.115	0.120	0.125		
Kit part number		W07 (LARGE)								W11 (SMALL)								
Washer (K180)	yes	yes	yes	yes	yes	no	no	no	no	yes	yes	yes	yes	yes	no	no		

- 2. HEX NUT FINISH: NICKEL
- 3. TO BE USED WITH 250S15-S28 PLUGS.
- 4. IP RATING: IP66
- 5. RECOMMENDED HOLE DIAMETER:  $\emptyset$  0.375" [9.5MM]
- 6. RECOMMENDED WORKING TEMPERATURE: -20TO 50 °C.
- 7. RoHS COMPLIANT.



## **CUSTOMER DRAWING**

			_												
						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									ED .
					UNLESS OTHERWISE SPECIFIED	SIZE *	W	/IDTH *	MULT	*	LBS/M		TEMP	ER *	
					1. ALL DIMENSIONS IN INCHES [mm]	FINISH *			<b>1</b>	MATERIAL *					
					- TWO PLACE DECIMALS ±0.02 [0.5]	SPEC No. *				SPEC No			*		
					- THREE PLACE DECIMALS ±0.005 [0.13]	FIRST USED ON *		N	SCALE 1:1					<u></u>	FI)®
						DATE DRAWN	BY	CHKD	APVD				أساك	<u>ال</u> اق	$\int \bigsqcup$
						2/17/20	NS	NS	SRC						
0A	PRELIMINARY	2/17/20	NS	SRC		2/1//20	INO	2/17/20	2/17/20		SHEET	1	OF	1	
REV	ECO NUMBER	DATE	BY	APVD		NAME			PART No	=				REV	
REVISIONS					DO NOT SCALE DRAWING	SEALED 1/4" JACK				12AW07-W11 0				0A	

4