

Potentiometers

Molded composition



Ohmite molded composition potentiometers are available in various models for applications in military devices, industrial equipment and in equipment requiring a convenient resistance control device.

FEATURES

- Low noise, smooth operation
- In accordance with “Mil” RV4N, RV4L, RV6L, RV6N, 2RV7N types
- RoHS compliant; non-RoHS version unavailable.



**February 2021:
Select parts have
been discontinued.
Please refer to the
ordering information below.**

SERIES SPECIFICATIONS

Model	Watts	Ohmic range	Behind panel (in./mm)	Diameter (in./mm)	Rotation	Voltage (RMS)
AS	0.5	50-5M	0.703/17.9	0.50/12.7	295° ±5°	350
ASM	0.5	50-5M	0.703/17.9	0.50/12.7	295° ±5°	350
CA	2.0	50-5M	0.625/15.9	1.16/29.4	312° ±3°	500
CB	2.0	50-5M	0.625/15.9	1.16/29.4	312° ±3°	500
CU	2.0	50-5M	0.625/15.9	1.16/29.4	312° ±3°	500
CCU	2.0	50-5M	1.266/32.1	1.16/29.4	312° ±3°	500
CLU	2.0	50-5M	0.625/15.9	1.16/29.4	312° ±3°	500
CMU	2.0	50-5M	0.625/15.9	1.16/29.4	312° ±3°	500

CHARACTERISTICS

Derating linear from 100% at +70°C to 0% at +120°C

Operating temp. range -55°C to 120°C

Construction Elements molded into a single, integral structure. Metal cover protects and shields the internal parts.

Sealing synthetic resin containing non-mercurial fungicide

Product life Since all rheostats/potentiometers are electro-mechanical devices, they are subject to mechanical wear and, therefore, have a finite life.

(continued)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Ohmite:

[CMU3531E](#) [ASM6667E](#) [CA1041E](#) [CCU1031E](#) [CLU1031E](#) [CLU1041E](#) [CLU1521E](#) [CLU2521E](#) [CLU2531E](#)
[CLU2541E](#) [CLU3531E](#) [CLU5021E](#) [CLU5041E](#) [CMU1011E](#) [CMU1021E](#) [CMU1031E](#) [CMU1521E](#) [CMU2521E](#)
[CMU2531E](#) [CMU2541E](#) [CMU5021E](#) [CMU5041E](#) [CU1011E](#) [CU1021E](#) [CU1031E](#) [CU2511E](#) [CU2521E](#) [CU2531E](#)
[CU5011E](#) [CU5021E](#) [CLA-TO-21E](#) [CLB-T218-21E](#)