

isc Three Terminal Positive Voltage Regulator

LM7815

FEATURES



- Output current in excess of 1.5A
- Output voltage of 15V
- Internal thermal overload protection
- Output transition SOA protection

ABSOLUTE MAXIMUM RATINGS(T<sub>a</sub>=25°C)

SYMBOL	PARAMETER	RATING	UNIT
V <sub>i</sub>	DC input voltage	35	V
I <sub>o</sub>	Output current	internally limited	
P <sub>tot</sub>	Power dissipation	internally limited	
T <sub>OP</sub>	Operating junction temperature	0~125	°C
T <sub>stg</sub>	Storage temperature	-65~150	°C

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	MAX	UNIT
R <sub>th j-c</sub>	Thermal Resistance, Junction to Case	5	°C/W
R <sub>th j-a</sub>	Thermal Resistance, Junction to Ambient	65	°C/W



**isc Three Terminal Positive Voltage Regulator****LM7815****• ELECTRICAL CHARACTERISTICS** $T_j=25^{\circ}\text{C}$  ( $V_i=23\text{V}$ ,  $I_o=0.5\text{A}$ ,  $C_i=0.33\ \mu\text{F}$ ,  $C_o=0.1\ \mu\text{F}$  unless otherwise specified)

SYMBOL	PARAMETER	CONDITIONS	MIN	MAX	UNIT
$V_o$	Output Voltage	$V_{in}=23\text{V}$ ; $I_o=0.5\text{A}$	14.4	15.6	V
$V_o$	Output Voltage	$17.5\text{V}\leq V_{in}\leq 30\text{V}$ ; $5\text{mA}\leq I_o\leq 1\text{A}$	14.25	15.75	V
$\Delta V_o$	Line Regulation	$17.5\text{V}\leq V_{in}\leq 30\text{V}$ ; $I_o=0.5\text{A}$		300	mV
$\Delta V_o$	Load Regulation	$5.0\text{mA}\leq I_o\leq 1.5\text{A}$ ; $V_{in}=23\text{V}$		300	mV
$I_q$	Quiescent Current	$V_{in}=23\text{V}$ ; $I_o=0.5\text{A}$		8.0	mA
$\Delta_{q1}$	Quiescent Current Change	$5.0\text{mA}\leq I_o\leq 1.0\text{A}$ ; $V_{in}=23\text{V}$		0.5	mA
$\Delta_{q2}$	Quiescent Current Change	$18\text{V}\leq V_{in}\leq 30.5\text{V}$ ; $I_o=0.5\text{A}$		0.8	mA