

## HDMI over Cat5/6 Extender Kit, Box-Style Transmitter/Receiver for Video/Audio, PoC, Up to 125 ft. (38 m)

MODEL NUMBER: B126-1A1-POC



Transmitter and receiver work in tandem to extend an HDMI signal via Cat5e/6/6a cable to a projector, monitor or television up to 125 ft. away. Ideal for digital signs, classrooms, churches, offices and retail settings.

### Description

The B126-1A1-POC HDMI over Cat5 Active Extender Kit includes a transmitter unit and a receiver unit that work in tandem to extend an HDMI audio/video signal to a projector, monitor or television. The kit is ideal for digital signs, trade shows, classrooms, churches, offices, retail settings and other applications where the source is located farther than conventional cables allow.

HDMI cable (see Tripp Lite's P569-Series) connects an optional local display and the audio/video source, such as a Blu-ray™ player, to the transmitter's HDMI ports and a remote display to the receiver. Cat5e/6/6a cable connects the two units (for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series). Built-in Power over Cable (PoC) technology powers the receiver over Cat5e/6/6a cable, so no external power supply on the display side is needed.

The B126-1A1-POC can extend a high-definition 1080p (@ 60 Hz) signal up to 125-ft. (38.1 m). In addition to crystal-clear video, the B126-1A1-POC delivers full, rich stereo and 7.1-channel surround sound (multi-channel or PCM). Built-in equalization control lets you fine-tune the image quality at the remote display. Supports 24-bit True Color (8 bits per channel) and HDCP. Easy to set up with no software or drivers to install. Mounts to a wall, rack or pole using the included hardware. Complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

### Features

#### Extends High-Definition Signals

- Extends a 1080p (@ 60 Hz) signal up to 125-ft. (38.1 m)
- Transmitter and receiver connect with one Cat5e/6/6a cable (for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series)
- Supports stereo and 7.1-channel surround sound (multi-channel or PCM) audio
- Supports 24-bit True Color (8 bits per channel) and HDCP
- Built-in equalization control lets you adjust the image on the local monitor

### Easy to Set Up and Use

### Highlights

- Built-in Power over Cable (PoC) technology powers the receiver
- Supports high-definition video resolutions up to 1080p (@ 60 Hz)
- Supports stereo and 7.1-channel surround sound audio
- Built-in equalization control lets you adjust monitor image
- Plug and play—no software or drivers to install

### System Requirements

#### Package Includes

- Transmitter unit
- Receiver unit
- Screwdriver for adjusting equalization
- External power supply with NEMA 1-15P plug and 5-ft. (1.52 m) cord (Input: 100-240V, 50/60 Hz, 0.5A; Output: 5V, 2A)
- Mounting hardware
- Owner's manual



- Plug-and-play engineering—no software or drivers to download and install
- Works with all operating systems and HDMI video sources
- Units connect quickly to monitors with HDMI cable, such as Tripp Lite's P569-Series
- LEDs indicate at a glance when the units are receiving power and an HDMI signal
- Included mounting hardware lets you install the units on a wall, rack or pole

**TAA Compliant**

- Complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332193117
Product Type	Extender Kit
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 5 ft.
Technology	HDMI; Cat5/5e; Cat6; POC
VIDEO	
Max Supported Video Resolution	1920x1080 (1080p @ 60Hz)
Max 1280 x 720 (720p) Range (ft)	125
Max 1920 x 1080 (1080p) Range (ft)	125
Transmitter Video Input	HDMI
Transmitter - Number of Video Outputs	1
Transmitter - Local Display Output	HDMI
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Recommended Cabling	N202-Series Cat6 Patch Cable
Max Supported Color Depth	24-bit True Color
HDR Support	No
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
Maximum Signal Range (ft)	125
Maximum Signal Range (m)	38
AUDIO	
Audio Input	HDMI; 3.5mm
Audio Output	HDMI



Audio Specification	Stereo Audio
<b>INPUT</b>	
Bus Powered	No
<b>POWER</b>	
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P
Power Source	Transmitter end only (Included)
Power Over Cable (PoC) Support	Yes
External Power Supply Input Specs (V / Hz / A)	100-240V / 50-60Hz / 0.5A
External Power Supply Output Specs (V / A)	5V/2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.37
DC Barrel Plug	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; PSE; TUV;RoHS; UL; cUL
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	TX & RX: Green (Power), Orange (Activity)
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Steel
Included Mounting Accessories	Wallmount
Number of Displays	1
Optional Mounting Accessory Notes	Can DIN Mount using Tripp Lite Bracket <a href="//www.tripplite.com/din-rail-mounting-bracket-for-digital-signage-version-2-B110-DIN-02">B110-DIN-02</a>
Form Factor/Mounting Options	Box; Wall-mount
Rackmountable	Yes
Receiver Unit Dimensions (hwd / cm.)	2.6 x 9.2 x 6.4
Receiver Unit Dimensions (hwd / in.)	1 x 3.6 x 2.5
Receiver Unit Weight (kg)	0.09
Receiver Unit Weight (lbs.)	0.2
Shipping Dimensions (hwd / cm)	5.51 x 21.41 x 16.41
Shipping Dimensions (hwd / in.)	2.17 x 8.43 x 6.46



Shipping Weight (kg)	0.65
Shipping Weight (lbs.)	1.43
Transmitter Unit Dimensions (hwd / cm.)	2.6 x 9.2 x 6.4
Transmitter Unit Dimensions (hwd / in.)	1 x 3.6 x 2.5
Transmitter Unit Weight (kg)	0.09
Transmitter Unit Weight (lbs.)	0.2
Unit Packaging Type	Box
Housing	Metal
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104 °F (0 to 40 °C)
Storage Temperature Range	5 to 122 °F (-15 to 50 °C)
Relative Humidity	0% to 85%, Non-Condensing
<b>COMMUNICATIONS</b>	
Signal Range (ft.)	125
Signal Range (m)	38
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
<b>CONNECTIONS</b>	
Side A - Connector 1	(2) HDMI (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)
Side A - Connector 3	3.5MM (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
HDCP Specification	1.4
Driver Required	No
Recommended Category Cable	Cat5/Cat5e/Cat6 Cables
10/100 Ethernet Extension Support	No



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Built-In Equalizer	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>