

Midi free-standing Beacons / EvoSIGNAL
Midi TwinFLASH 12/24VAC/DC YE



| | |
|------------------|-----------------------|
| Part No.: | 261.320.70 |
| Series: | EvoSIGNAL Midi |



| MECHANICAL DATA | |
|------------------------------|-----------------------------|
| Height | 130 mm |
| Diameter | 85 mm |
| Materials | PC PC/ABS |
| Dome colour | Yellow |
| Housing colour | Grey |
| Protection category | IP66 |
| Connection | Push-in terminal |
| cross-sectional area minimum | 0,25mm ² / 24AWG |
| cross-sectional area maximum | 1,50mm ² / 16AWG |
| Service life optical | 50,000 h minimum |
| Working temperature minimum | -30°C |
| Working temperature maximum | +60°C |
| UL Type Rating | Type 12 |
| Weight with packaging | 286 g |
| Product weight | 186 g |

| ELECTRICAL DATA | |
|-----------------------------|--------------------|
| Operating voltage | 12V 24V |
| Operating voltage type | AC/DC |
| Operating voltage type | 50Hz |
| Operating voltage tolerance | +/- 10% |
| Rated operational voltage | 12 VDC |
| Rated operational current | 150 mA |
| Rated inrush current | 1A |
| Protection class | Protection class 2 |
| Pollution degree | 3 |
| Overvoltage category | III |

| OPTICAL DATA | |
|----------------------|---------------------------|
| Light source | LED |
| Light colour | Yellow |
| Optical signal image | EVS Flash TwinFlash |
| Flash frequency | 1 Hz |

! For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.

Midi free-standing Beacons / EvoSIGNAL

Midi TwinFLASH 12/24VAC/DC YE



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.