www.ti.com

SCAS692F-APRIL 2003-REVISED APRIL 2007

FEATURES

- Controlled Baseline
 - One Assembly/Test Site, One Fabrication Site
- Extended Temperature Performance of up to -40°C to 85°C, -40°C to 125°C and -55°C to 125°C
- Enhanced Diminishing Manufacturing Sources (DMS) Support
- Enhanced Product-Change Notification
- Qualification Pedigree (1)
- Member of the Texas Instruments Widebus™
 Family
- State-of-the-Art Advanced BiCMOS
 Technology (ABT) Design for 3.3-V Operation
 and Low Static-Power Dissipation
- Supports Mixed-Mode Signal Operation (5-V Input and Output Voltages With 3.3-V V_{CC})
- Supports Unregulated Battery Operation Down to 2.7 V
- Typical V_{OLP} (Output Ground Bounce) <0.8 V at V_{CC} = 3.3 V, T_A = 25°C
- I_{off} and Power-Up 3-State Support Hot Insertion
- Bus Hold on Data Inputs Eliminates the Need for External Pullup/Pulldown Resistors
- Latch-Up Performance Exceeds 500 mA Per JESD 17
- ESD Protection Exceeds JESD 22
 - 2000-V Human-Body Model (A114-A)
 - 200-V Machine Model (A115-A)
- (1) Component qualification in accordance with JEDEC and industry standards to ensure reliable operation over an extended temperature range. This includes, but is not limited to, Highly Accelerated Stress Test (HAST) or biased 85/85, temperature cycle, autoclave or unbiased HAST, electromigration, bond intermetallic life, and mold compound life. Such qualification testing should not be viewed as justifying use of this component beyond specified performance and environmental limits.

48 20E 10E 1Y1 **1**2 47∏ 1A1 1Y2 🛮 3 46 🛛 1A2 GND [45 ¶ GND 1Y3 **∏** 5 44**∏** 1A3 1Y4 **∏**6 43 1A4 42 V_{CC} V_{CC} 8 41 2A1 2Y1 2Y2 **1**9 40 🛮 2A2 GND 110 39 | GND 38 🛮 2A3 2Y3 🛛 11 2Y4 112 37 **□** 2A4 3Y1 113 36 🛮 3A1 3Y2 [14 35 3A2 GND 15 34 GND 33 A3 3Y3 **∏** 16 3Ү4 П 17 32**∏** 3A4 18 31 V_{CC} V_{CC} **1**19 4Y1 30 4A1

4Y2 20

GND ∏21

4Y3 **1**22

4Y4 [23

24

4OE [

29 **1** 4A2

28∏ GND

27**∏** 4A3

26 **4**A4

25 🛮 30E

DGG, DGV, OR DL PACKAGE

(TOP VIEW)

DESCRIPTION/ORDERING INFORMATION

The SN74LVTH16244A is a 16-bit buffer and line driver designed for low-voltage (3.3 V) V_{CC} operation, but with the capability to provide a TTL interface to a 5-V system environment. This device can be used as four 4-bit buffers, two 8-bit buffers, or one 16-bit buffer. This device provides true outputs and symmetrical active-low output-enable (\overline{OE}) inputs.

Active bus-hold circuitry holds unused or undriven inputs at a valid logic state. Use of pullup or pulldown resistors with the bus-hold circuitry is not recommended.

AA.

Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

Widebus is a trademark of Texas Instruments.

SN74LVTH16244A-EP 3.3-V ABT 16-BIT BUFFER/DRIVER WITH 3-STATE OUTPUTS


SCAS692F-APRIL 2003-REVISED APRIL 2007



When V_{CC} is between 0 V and 1.5 V, the device is in the high-impedance state during power up or power down. However, to ensure the high-impedance state above 1.5 V, \overline{OE} should be tied to V_{CC} through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

This device is fully specified for hot-insertion applications using I_{off} and power-up 3-state. The I_{off} circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down. The power-up 3-state circuitry places the outputs in the high-impedance state during power up and power down, which prevents driver conflict.

GQL OR ZQL PACKAGE (TOP VIEW)



TERMINAL ASSIGNMENTS⁽¹⁾ (56-Ball GQL/ZQL Package)

	1	2	3	4	5	6
Α	1 OE	NC	NC	NC	NC	2 OE
В	1Y2	1Y1	GND	GND	1A1	1A2
С	1Y4	1Y3	V _{CC}	V _{CC}	1A3	1A4
D	2Y2	2Y1	GND	GND	2A1	2A2
E	2Y4	2Y3			2A3	2A4
F	3Y1	3Y2			3A2	3A1
G	3Y3	3Y4	GND	GND	3A4	3A3
Н	4Y1	4Y2	V _{CC}	V _{CC}	4A2	4A1
L	4Y3	4Y4	GND	GND	4A4	4A3
K	4 OE	NC	NC	NC	NC	3 OE

(1) NC - No internal connection

ORDERING INFORMATION(1)

T _A	PACKAGE	(2)	ORDERABLE PART NUMBER	TOP-SIDE MARKING		
-40°C to 125°C	SSOP - DL	Tape and reel	CLVTH16244AQDLREP	LH16244AEP		
	TSSOP – DGG	Tape and reel	CLVTH16244AQDGGREP	LH16244AEP		
	TVSOP - DGV	Tape and reel	CLVTH16244AIDGVREP	LL244AEP		
–40°C to 85°C	VFBGA – GQL	Tone and real	CLVTH162244AIGQLREP	LL 244AED		
	VFBGA – ZQL (Pb-free)	Tape and reel	CLVTH16244AIZQLREP	LL244AEP		
–55°C to 125°C	TSSOP - DGG	Tape and reel	CLVTH16244AMDGGREP	H16244AMEP		

⁽¹⁾ For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI website at www.ti.com.


⁽²⁾ Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.



FUNCTION TABLE (each 4-bit buffer)

INP	JTS	OUTPUT
ŌĒ	Α	Y
L	Н	Н
L	L	L
Н	X	Z

LOGIC DIAGRAM (POSITIVE LOGIC)



Pin numbers shown are for the DGG, DGV, and DL packages.

SN74LVTH16244A-EP 3.3-V ABT 16-BIT BUFFER/DRIVER WITH 3-STATE OUTPUTS

SCAS692F-APRIL 2003-REVISED APRIL 2007



Absolute Maximum Ratings⁽¹⁾

over operating free-air temperature range (unless otherwise noted)

			MIN	MAX	UNIT	
V_{CC}	Supply voltage range		-0.5	4.6	V	
VI	Input voltage range (2)		-0.5	7	V	
Vo	Voltage range applied to any output in the high-impe	dance or power-off state ⁽²⁾	-0.5	7	V	
Vo	Voltage range applied to any output in the high state	(2)	-0.5	V _{CC} + 0.5	V	
	Ourselists and advantisation law state	SN74LVTH16244AQ		96	0	
IO	Current into any output in the low state	SN74LVTH16244AI		128	mA	
	Occupation and the bight state (3)	SN74LVTH16244AQ		48	0	
IO	Current into any output in the high state (3)	SN74LVTH16244AI		64	mA	
I _{IK}	Input clamp current	V _I < 0		96 128 48		
I _{OK}	Output clamp current	V _O < 0		-50	mA	
		DGG package		70		
0	Decline the arread increasing a (4)	DGV package		58	0000	
θ_{JA}	Package thermal impedance (4)	DL package		63	°C/W	
		GQL/ZQL package		42		
T _{stg}	Storage temperature range		-65	150	°C	


⁽¹⁾ Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

Recommended Operating Conditions⁽¹⁾

			MIN	MAX	UNIT
V _{CC}	Supply voltage		2.7	3.6	V
V _{IH}	High-level input voltage		2		V
V _{IL}	Low-level input voltage			0.8	V
VI	Input voltage			5.5	V
		SN74LVTH16244AQ		-24	
I _{OH}	High-level output current	SN74LVTH16244AI		-32	mA
		SN74LVTH16244AM		-24	
		SN74LVTH16244AQ		24	
I _{OL}	Low-level output current	SN74LVTH16244AI		64	mA
		SN74LVTH16244AM		24	
Δt/Δν	Input transition rise or fall rate	Outputs enabled		10	ns/V
$\Delta t/\Delta V_{CC}$	Power-up ramp rate	·	200		μs/V
		SN74LVTH16244AQ	-40	125	
T _A	Operating free-air temperature	SN74LVTH16244AI	-40	85	°C
		SN74LVTH16244AM	-55	125	

⁽¹⁾ All unused control inputs of the device must be held at V_{CC} or GND to ensure proper device operation. See the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

 ⁽²⁾ The input and output negative-voltage ratings may be exceeded if the input and output clamp-current ratings are observed.
 (3) This current flows only when the output is in the high state and V_O > V_{CC}.
 (4) The package thermal impedance is calculated in accordance with JESD 51-7.





Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

PAR	AMETER	TEST COND	ITIONS	V _{cc}	MIN	TYP ⁽¹⁾ MAX	UNIT
V _{IK}		I _I = -18 mA		2.7 V		-1.2	2 V
		$I_{OH} = -100 \mu A$		2.7 V to 3.6 V	V _{CC} - 0.2		
V _{IK} V _{OH} VOL II Control inputs Data inputs	$I_{OH} = -8 \text{ mA}$		2.7 V	2.4			
			'LVTH16244AQ		2		
		I _{OH} = -24 mA	'LVTH16244AI				
V _{OH}			'LVTH16244AM	0.17	2		V
			'LVTH16244AQ	3 V			
		$I_{OH} = -32 \text{ mA}$	'LVTH16244AI		2		
			'LVTH16244AM				
		I _{OL} = 100 μA				0.2	2
		I _{OL} = 24 mA		2.7 V		0.0	5
		I _{OL} = 16 mA				0.4	1
			'LVTH16244AQ				
V_{OL}		I _{OL} = 32 mA	'LVTH16244AI			0.0	5 V
			'LVTH16244AM	3 V			
			'LVTH16244AQ				
		'LVTH16244AI			0.5	5	
			'LVTH16244AM				
			'LVTH16244AQ			50)
		V _I = 5.5 V	'LVTH16244AI	0 V or 3.6 V		10)
			'LVTH16244AM			50)
I _I	Control	V – V or CND				±	μΑ
	inputs			3.6 V			!
				3.0 V			l
	inputs	V _I = 0 V	T				5
			'LVTH16244AQ	_			
I _{off}		V_I or $V_O = 0 V$ to 4.5 V	'LVTH16244AI	0 V		±100) μΑ
	1		'LVTH16244AM				
		V _I = 0.8 V		3 V	75		
		V _I = 2 V	T	0.	-75		
I _{I(hold)}			'LVTH16244AQ				μΑ
(/	inputs	$V_1 = 0 \text{ V to } 3.6 \text{ V}$	'LVTH16244AI	3.6 V ⁽²⁾		500 -750	
			'LVTH16244AM	-		-750	_
la=::		V _O = 3 V	LVIIII0244AIVI	3.6 V			5 μΑ
I _{OZH}		V _O = 3 V V _O = 0.5 V		3.6 V		<u>;</u> 	•
I _{OZL}		$V_O = 0.5 \text{ V}$ $V_O = 0.5 \text{ V to 3 V}, \overline{OE} = \text{Don'}$	t care				
I _{OZPU}		-	to 3 V, \overline{OE} = Don't care 0 V to 1.5 V ±100 to 3 V, \overline{OE} = Don't care 1.5 V to 0 V ±100				
I _{OZPD}		V _O = 0.5 V to 5 V, OL = Doll	Outputs high	1.5 V 10 0 V		0.19	•
loo		$I_{O} = 0$,	Outputs low	3.6 V			5 mA
I _{CC}		$V_I = V_{CC}$ or GND	Outputs disabled	- 0.5 v		0.19	
Δl _{CC} ⁽³⁾		One input at V _{CC} – 0.6 V,	Outputs disabled	3 V to 3.6 V	0.2	0.18	
		Other inputs at V _{CC} or GND			-		
C_i		$V_I = 3 V \text{ or } 0 V$				4	pF

⁽¹⁾ All typical values are at $V_{CC} = 3.3 \text{ V}$, $T_A = 25^{\circ}\text{C}$. (2) This is the bus-hold maximum dynamic current. It is the minimum overdrive current required to switch the input from one state to another.

⁽³⁾ This is the increase in supply current for each input that is at the specified TTL voltage level, rather than V_{CC} or GND.

SN74LVTH16244A-EP 3.3-V ABT 16-BIT BUFFER/DRIVER WITH 3-STATE OUTPUTS

SCAS692F-APRIL 2003-REVISED APRIL 2007



Electrical Characteristics (continued)

over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	V _{cc}	MIN	TYP ⁽¹⁾	MAX	UNIT
Co	V _O = 3 V or 0 V			9		pF


Switching Characteristics

over recommended operating free-air temperature range, $C_L = 50 \text{ pF}$ (unless otherwise noted) (see Figure 1)

		TO (OUTPUT)	SN7	SN74LVTH16244AQ/M				SN74L	VTH162	244AI		
PARAMETER	FROM (INPUT)			V_{CC} = 3.3 V \pm 0.3 V		V _{CC} = 2.7 V		V_{CC} = 3.3 V \pm 0.3 V			V _{CC} = 2.7 V	
			MIN	MAX	MIN	MAX	MIN	TYP	MAX	MIN	MAX	
t _{PLH}	Α		1.1	4.4		4.6	1.2	2.5	3.2		3.7	ns
t _{PHL}	A	Ť	1.1	3.6		3.9	1.2	2	3.2		3.7	113
t _{PZH}	ŌĒ	Y	1.1	4.6		5.4	1.2	2.6	4		5	ne
t _{PZL}	OE	Y	1.1	5.4		6.2	1.2	2.7	4		5	ns
t _{PHZ}	ŌĒ		1.6	5.7		6.2	2.2	3.3	4.5		5	ns
t _{PLZ}	OE	ſ	1.2	5		4.7	2	3.1	4.2		4.4	115
t _{sk(o)}									0.5			ns



PARAMETER MEASUREMENT INFORMATION



NOTES: A. C_L includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, Z_O = 50 Ω , $t_r \leq$ 2.5 ns. $t_f \leq$ 2.5 ns.
- D. The outputs are measured one at a time, with one transition per measurement.

Figure 1. Load Circuit and Voltage Waveforms





10-Dec-2020

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
	()		_		-	()	(6)	(-)		(/	
8W244AMDGGREPG4	ACTIVE	TSSOP	DGG	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	H16244AMEP	Samples
CLVTH16244AIDGVREP	ACTIVE	TVSOP	DGV	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	LL244AEP	Samples
CLVTH16244AMDGGREP	ACTIVE	TSSOP	DGG	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	H16244AMEP	Samples
CLVTH16244AQDGGREP	ACTIVE	TSSOP	DGG	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	LH16244AEP	Samples
CLVTH16244AQDLREP	ACTIVE	SSOP	DL	48	1000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	LH16244AEP	Samples
V62/04601-01XE	ACTIVE	SSOP	DL	48	1000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	LH16244AEP	Samples
V62/04601-01YE	ACTIVE	TSSOP	DGG	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	LH16244AEP	Samples
V62/04601-02ZE	ACTIVE	TVSOP	DGV	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	LL244AEP	Samples
V62/04601-03YE	ACTIVE	TSSOP	DGG	48	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	H16244AMEP	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.



PACKAGE OPTION ADDENDUM

10-Dec-2020

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN74LVTH16244A-EP:

Catalog: SN74LVTH16244A

Military: SN54LVTH16244A

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Military QML certified for Military and Defense Applications

PACKAGE MATERIALS INFORMATION

www.ti.com 17-Dec-2020

TAPE AND REEL INFORMATION





	Dimension designed to accommodate the component width
	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

All dimensions are nominal	All ulfiletisions are notifical												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant	
CLVTH16244AIDGVREP	TVSOP	DGV	48	2000	330.0	16.4	7.1	10.2	1.6	12.0	16.0	Q1	
CLVTH16244AMDGGREP	TSSOP	DGG	48	2000	330.0	24.4	8.6	13.0	1.8	12.0	24.0	Q1	
CLVTH16244AQDGGREP	TSSOP	DGG	48	2000	330.0	24.4	8.6	13.0	1.8	12.0	24.0	Q1	
CLVTH16244AQDLREP	SSOP	DL	48	1000	330.0	32.4	11.35	16.2	3.1	16.0	32.0	Q1	

www.ti.com 17-Dec-2020



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
CLVTH16244AIDGVREP	TVSOP	DGV	48	2000	853.0	449.0	35.0
CLVTH16244AMDGGREP	TSSOP	DGG	48	2000	367.0	367.0	45.0
CLVTH16244AQDGGREP	TSSOP	DGG	48	2000	367.0	367.0	45.0
CLVTH16244AQDLREP	SSOP	DL	48	1000	367.0	367.0	55.0

DL (R-PDSO-G48)

PLASTIC SMALL-OUTLINE PACKAGE



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
- D. Falls within JEDEC MO-118

PowerPAD is a trademark of Texas Instruments.





SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
 4. Reference JEDEC registration MO-153.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 5. Publication IPC-7351 may have alternate designs.
- 6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.



DGG (R-PDSO-G**)

PLASTIC SMALL-OUTLINE PACKAGE

48 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold protrusion not to exceed 0,15.

D. Falls within JEDEC MO-153

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated