


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

NOTES:

- SPECIFICATION:
 JACKET: PVC. MULTI-LAYER, 1ST LAYER WHITE; 2ND LAYER "COLOR"
 OD: .154±.008 (3.9 mm)
 CONDUCTOR: BARE COPPER, STRANDING 651 x 0.07 mm = 2.50 mm², 13 AWG.
- RATING:
 VOLTAGE: 1,000 V CAT IV PER IEC 61010-031
 CURRENT: 36 A MAX.
 TEMPERATURE: -20° C TO +80° C.
- AVAILABLE IN 3 STANDARD LENGTHS AND 6 COLORS - SEE MODEL NUMBER BELOW.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
-	CLASS A RELEASED	7/11/99	
A	UPDATED FORMAT w/ CAGE CODE	4/18/04	



MODEL NUMBER

CT2882-#-XXX

COLOR: 0 - BLACK
 2 - RED
 4 - YELLOW
 5 - GREEN
 6 - BLUE
 9 - WHITE

LENGTH: 10 - 10 m PACKAGE
 50 - 50 m SPOOL
 100 - 100 m SPOOL

THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ± .005 DO NOT SCALE DRAWING	CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610	
			APPROVALS	DATE		
		MATERIAL	DRAWN WDH	7/11/99	WIRE, TEST LEAD, PVC JACKET, 2.50 mm ² , 13 AWG, 36 A	
		FINISH	CHECKED		SIZE A	CAGE CODE 43F45
NEXT ASSY	USED ON		ENGR.		DWG. NO. P288200	REV. A
APPLICATION			DESIGN ACTIVITY		SCALE NONE	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cal Test Electronics:

[CT2882-4-50](#) [CT2882-4-100](#) [CT2882-6-50](#) [CT2882-6-10](#) [CT2882-2-100](#) [CT2882-2-50](#) [CT2882-9-50](#) [CT2882-0-50](#)
[CT2882-2-10](#) [CT2882-5-50](#) [CT2882-0-100](#) [CT2882-9-100](#) [CT2882-6-100](#) [CT2882-4-10](#) [CT2882-9-10](#) [CT2882-5-100](#) [CT2882-0-10](#) [CT2882-5-10](#)