

公TDK SMD / SMT Inductors (Coils)

NLV32T-151J-EF RoHS Reach Halogen Free Pb Free

| Applications | Commercial Grade |
|---------------|---|
| Feature | No Directivity Wire Wound Wire Wound Ferrite Core |
| Series Type | NLV32-EF |
| Status | Production |
| Brand | TDK |



| | Size |
|------------------------------|----------------|
| Length(L) | 3.20mm ±0.20mm |
| Width(W) | 2.50mm ±0.20mm |
| Thickness Height | 2.20mm ±0.20mm |
| Recommended Land Pattern (A) | 1.20mm Nom. |
| Recommended Land Pattern (B) | 2.00mm Nom. |
| Recommended Land Pattern (C) | 2.00mm Nom. |

| Electrical Characteristics | | |
|--------------------------------|---------------------|--|
| Inductance | 150μH ±5% at 796kHz | |
| Rated Current | 65mA | |
| DC Resistance [Typ.] | | |
| DC Resistance [Max.] | 15Ω | |
| Self Resonant Frequency [Min.] | 8MHz | |
| Self Resonant Frequency [Typ.] | | |
| Q [Min.] | 20 at 796kHz | |
| Q [Typ.] | | |

| Other | | | |
|---|---------------------------------------|--|--|
| Operating Temp. Range (Including Self-Temp. Rise) | -40 to 105°C | | |
| | Wave (Flow) | | |
| Soldering Method | Reflow | | |
| | Iron Soldering | | |
| AEC-Q200 | NO | | |
| Packing | Embossed (Plastic)Taping [180mm Reel] | | |
| Package Quantity | 2000pcs | | |
| Weight | 0.05g | | |


[!] Images are for reference only and show exemplary products.


[!] This PDF document was created based on the data listed on the TDK Corporation website.


 $^{! \ \}mbox{All specifications}$ are subject to change without notice.


RoHS Reach Halogen Free Pb Free

Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)










[!] Images are for reference only and show exemplary products.


[!] This PDF document was created based on the data listed on the TDK Corporation website.

[!] All specifications are subject to change without notice.

RoHS Reach Halogen Free Pb Free

Associated Images





[!] Images are for reference only and show exemplary products.

[!] This PDF document was created based on the data listed on the TDK Corporation website.

 $^{! \ \}mbox{All specifications}$ are subject to change without notice.