#### MIRELLA-50-S-PF

~15° spot beam

#### **TECHNICAL SPECIFICATIONS:**

Ø 49.9 mm **Dimensions** Height 24 mm socket Fastening **ROHS** compliant yes 🕕



#### **MATERIAL SPECIFICATIONS:**

Colour **Finish** Component **Type** Material Coating MIRELLA-50-S-PF Reflector PC metal lacquer

#### **ORDERING INFORMATION:**


» Box size: 480 x 280 x 300 mm

Component Qty in box MOQ **MPQ** Box weight (kg)

336 C13085\_MIRELLA-50-S-PF 112 28 3.0




# **PRODUCT** C13085\_MIRELLA-50-S-PF




See also our general installation guide: www.ledil.com/installation\_guide














LED V8 Gen6  $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 15.0° / 34.0° Efficiency 90 % Peak intensity 5.6 cd/lm LEDs/each optic Light colour White Required components: C13761\_PF-SOCKET-CXA15




#### bridgelux.

LED V8 Gen6 FWHM / FWTM 16.0° / 36.0° Efficiency 84 % Peak intensity 4.9 cd/lm LEDs/each optic 1 White Light colour Required components: C13761\_PF-SOCKET-CXA15

C13333\_MIRELLA-CL





#### bridgelux

LED V8 Gen6  $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 20.0° / 62.0° Efficiency 71 % Peak intensity 3.4 cd/lm LEDs/each optic Light colour White Required components: C13709\_PF-SOCKET-VERO13-18

C12479\_MIRELLA-DL Bender Wirth: 460 Typ L1




#### bridgelux.


LED VERO10 FWHM / FWTM 23.0° / 63.0° Efficiency 83 % Peak intensity 2.6 cd/lm LEDs/each optic White Light colour Required components:

C13708\_PF-SOCKET-VERO10 C13333\_MIRELLA-CL











## **CITIZEN**

LED CLL01x
FWHM / FWTM 15.0° / 32.0°
Efficiency 84 %
Peak intensity 5.8 cd/lm
LEDs/each optic 1
Light colour White
Required components:



## **CITIZEN**

C13083\_PF-SOCKET C12479\_MIRELLA-DL


LED CLL01x
FWHM / FWTM 13.0° / 27.0°
Efficiency 84 %
Peak intensity 7.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C13083\_PF-SOCKET



#### **CITIZEN**

C13333\_MIRELLA-CL

LED CLL01x
FWHM / FWTM 14.0° / 27.0°
Efficiency 88 %
Peak intensity 7.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C13083\_PF-SOCKET



## **CITIZEN**

LED CLL02x/CLU02x (LES10)

FWHM / FWTM 20.0° / 54.0°
Efficiency 83 %
Peak intensity 4.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C13083\_PF-SOCKET

C12479\_MIRELLA-DL



#### PHOTOMETRIC DATA (MEASURED):

## **CITIZEN**

CLL02x/CLU02x (LES10)

 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 18.0° / 43.0° Efficiency 83 % Peak intensity 5.1 cd/lm LEDs/each optic Light colour White Required components: C13083\_PF-SOCKET



## **CITIZEN**


C13333\_MIRELLA-CL

LED CLL02x/CLU02x (LES10)

FWHM / FWTM 27.0° / 67.0° Efficiency 77 % Peak intensity 2 cd/lm LEDs/each optic 1 White Light colour Required components:

C13709\_PF-SOCKET-VERO13-18


C12479\_MIRELLA-DL Bender Wirth: 434 Typ L1



LED CLL02x/CLU02x (LES10)

 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 21.0° / 63.0° Efficiency 84 % Peak intensity 3.1 cd/lm LEDs/each optic Light colour White Required components: C13709\_PF-SOCKET-VERO13-18

Bender Wirth: 434 Typ L1



## **CITIZEN**

CLL02x/CLU02x (LES10)

FWHM / FWTM 25.0° / 64.0° Efficiency

Peak intensity 1.5 cd/lm LEDs/each optic White Light colour Required components: C13083\_PF-SOCKET

C13723\_MIRELLA-RZL




## **CITIZEN**

LED CLL02x/CLU02x (LES10)

FWHM / FWTM 20.0° / 61.0°
Efficiency 80 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour White

Required components: C13709\_PF-SOCKET-VERO13-18

C13333\_MIRELLA-CL Bender Wirth: 434 Typ L1



## **CITIZEN**

LED CLL02x/CLU02x (LES10)

FWHM / FWTM 19.0° / 46.0°

Efficiency 87 %


Peak intensity 4.2 cd/lm

LEDs/each optic 1

Light colour White

Required components:


C13083\_PF-SOCKET



## **CITIZEN**

LED CLU700/701/702
FWHM / FWTM 13.0° / 29.0°
Efficiency 89 %
Peak intensity 7.3 cd/lm
LEDs/each optic 1
Light colour White

Required components: C13083\_PF-SOCKET



## **CITIZEN**

 LED
 CLU700/701/702

 FWHM / FWTM
 23.0° / 61.0°

 Efficiency
 82 %


 Peak intensity
 2.5 cd/lm

 LEDs/each optic
 1

White

Required components: C13083\_PF-SOCKET C13723\_MIRELLA-RZL

Light colour






C13333\_MIRELLA-CL

#### **CITIZEN** CLU700/701/702 FWHM / FWTM 20.0° / 58.0° Efficiency 79 % Peak intensity 3.1 cd/lm LEDs/each optic Light colour White Required components: C13709\_PF-SOCKET-VERO13-18 C12479\_MIRELLA-DL Bender Wirth: 434 Typ L1 **CITIZEN** LED CLU700/701/702 FWHM / FWTM 17.0° / 47.0° Efficiency 82 % Peak intensity 4 cd/lm LEDs/each optic 1 White Light colour Required components: C13083\_PF-SOCKET C12479\_MIRELLA-DL **CITIZEN** LED CLU700/701/702 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 19.0° / 47.0° Efficiency 84 % Peak intensity 4 cd/lm LEDs/each optic Light colour White Required components: C13709\_PF-SOCKET-VERO13-18 Bender Wirth: 434 Typ L1 **CITIZEN** CLU700/701/702 FWHM / FWTM 13.0° / 30.0° Efficiency 83 % Peak intensity 6.6 cd/lm LEDs/each optic White Light colour Required components: C13083\_PF-SOCKET




#### **CITIZEN** CLU700/701/702 FWHM / FWTM 14.0° / 40.0° Efficiency 79 % Peak intensity 4.8 cd/lm LEDs/each optic Light colour White Required components: C13709\_PF-SOCKET-VERO13-18 C13333\_MIRELLA-CL Bender Wirth: 434 Typ L1




#### **CITIZEN** LED CLU720/721 FWHM / FWTM 29.0° / 69.0° Efficiency 75 % Peak intensity 1.7 cd/lm LEDs/each optic 1 White Light colour Required components: C13709\_PF-SOCKET-VERO13-18 C12479\_MIRELLA-DL Bender Wirth: 433 Typ L1

#### LED CLU720/721 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 23.0° / 67.0° Efficiency 82 % Peak intensity 2.6 cd/lm LEDs/each optic Light colour White Required components:






## **CITIZEN**



C13709\_PF-SOCKET-VERO13-18

C13333\_MIRELLA-CL Bender Wirth: 433 Typ L1




## CREE 💠

LED CXA/B 13xx
FWHM / FWTM 15.0° / 36.0°
Efficiency 81 %
Peak intensity 5.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13761\_PF-SOCKET-CXA15 C12479\_MIRELLA-DL






## CREE \$

LED CXA/B 13xx
FWHM / FWTM 12.0° / 25.0°
Efficiency 87 %
Peak intensity 9.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13761\_PF-SOCKET-CXA15





## CREE ÷

LED CXA/B 13xx
FWHM / FWTM 12.0° / 25.0°
Efficiency 82 %
Peak intensity 8.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:


C13761\_PF-SOCKET-CXA15 C13333\_MIRELLA-CL




## CREE \$

LED CXA/B 15xx
FWHM / FWTM 21.0° / 56.0°
Efficiency 87 %
Peak intensity 3.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13761\_PF-SOCKET-CXA15 C12479\_MIRELLA-DL








## CREE 💠

LED CXA/B 15xx
FWHM / FWTM 19.0° / 59.0°
Efficiency 79 %
Peak intensity 3.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13709\_PF-SOCKET-VERO13-18

C13333\_MIRELLA-CL Bender Wirth: 441 Typ L1



## CREE &

LED CXA/B 15xx
FWHM / FWTM 19.0° / 47.0°
Efficiency 84 %
Peak intensity 4.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13761\_PF-SOCKET-CXA15 C13333\_MIRELLA-CL




## CREE 🚓

LED CXA/B 1816 & CXA/B 1820 & CXA 1850

FWHM / FWTM 23.0° / 67.0°
Efficiency 89 %
Peak intensity 2.8 cd/lm
LEDs/each optic 1
Light colour White
Required components:

IDEAL: 50-2101CR + 50-2100MR




## CREE \$


LED CXA/B 1816 & CXA/B 1820 & CXA 1850

FWHM / FWTM 25.0° / 68.0°
Efficiency 85 %
Peak intensity 2.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C14115\_PF-SOCKET-CXA15-18








## CREE 💠

LED MK-R
FWHM / FWTM 12.0° / 27.0°
Efficiency 87 %
Peak intensity 8.1 cd/lm
LEDs/each optic 1

Light colour White Required components: C13083\_PF-SOCKET






## CREE &

LED MK-R
FWHM / FWTM 15.0° / 37.0°
Efficiency 82 %
Peak intensity 4.9 cd/lm
LEDs/each optic 1
Light colour White

Required components: C13083\_PF-SOCKET C12479\_MIRELLA-DL





## CREE 💠

LED MT-G
FWHM / FWTM 18.0° / 34.0°
Efficiency 86 %
Peak intensity 5.5 cd/lm
LEDs/each optic 1
Light colour White


Required components: C13083\_PF-SOCKET C13333\_MIRELLA-CL



## CREE \$

LED MT-G
FWHM / FWTM 17.0° / 34.0°
Efficiency 90 %
Peak intensity 5.3 cd/lm
LEDs/each optic 1
Light colour White

Required components: C13083\_PF-SOCKET





## CREE \$

LED MT-G
FWHM / FWTM 19.0° / 46.0°
Efficiency 85 %
Peak intensity 4.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:



## **CREE** ÷


C13083\_PF-SOCKET C12479\_MIRELLA-DL

LED MT-G2
FWHM / FWTM 16.0° / 33.0°
Efficiency 84 %
Peak intensity 5.8 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C13083\_PF-SOCKET
C13333\_MIRELLA-CL



## CREE 🕏

LED MT-G2
FWHM / FWTM 18.0° / 35.0°
Efficiency 88 %
Peak intensity 4.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C13083\_PF-SOCKET




## CREE 🕏

LED MT-G2
FWHM / FWTM 18.0° / 43.0°
Efficiency 85 %
Peak intensity 4.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C13083\_PF-SOCKET


C12479\_MIRELLA-DL












#### PHOTOMETRIC DATA (MEASURED):

## CREE \$

LED XM-L RGB
FWHM / FWTM 22.0° / 55.0°
Efficiency 80 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C13083\_PF-SOCKET
C13723\_MIRELLA-RZL





## CREE \$

LED XQ-E HI
FWHM / FWTM 21.0° / 58.0°
Efficiency 86 %
Peak intensity 3.1 cd/lm
LEDs/each optic 4
Light colour RGBW
Required components:



#### C13083\_PF-SOCKET C13723\_MIRELLA-RZL


## **DESCRIPTION** LUMILEDS

LED LUXEON CoB 1202/1203

FWHM / FWTM 20.0° / 61.0°
Efficiency 78 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13709\_PF-SOCKET-VERO13-18


C13333\_MIRELLA-CL Bender Wirth: 438 Typ L1




## **DESCRIPTION** LUMILEDS


LED LUXEON CoB 1202/1203

FWHM / FWTM 19.0° / 50.0°
Efficiency 87 %
Peak intensity 4 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C14037\_PF-NSX-SOCKET





Published: 03/05/2018




#### PHOTOMETRIC DATA (MEASURED):



LED LUXEON CoB 1202/1203

FWHM / FWTM 20.0° / 61.0°
Efficiency 84 %
Peak intensity 3.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13709\_PF-SOCKET-VERO13-18 Bender Wirth: 438 Typ L1



#### **MUMILEDS**

LED LUXEON CoB 1202s

FWHM / FWTM 15.0° / 36.0°
Efficiency 84 %
Peak intensity 5.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13761\_PF-SOCKET-CXA15 C12479\_MIRELLA-DL



## **DESCRIPTION** LUMILEDS

LED LUXEON CoB 1202s

FWHM / FWTM 13.0° / 30.0°
Efficiency 89 %
Peak intensity 7.9 cd/lm
LEDs/each optic 1
Light colour White

C13761\_PF-SOCKET-CXA15



#### **MILEDS**


Required components:

LED LUXEON CoB 1202s

FWHM / FWTM 23.0° / 63.0°
Efficiency 79 %
Peak intensity 2.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13709\_PF-SOCKET-VERO13-18

C12479\_MIRELLA-DL Bender Wirth: 452 Typ L1



Published: 03/05/2018



LED LUXEON CoB 1202s

FWHM / FWTM 13.0° / 28.0°
Efficiency 84 %
Peak intensity 7.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:


C13761\_PF-SOCKET-CXA15 C13333\_MIRELLA-CL



#### **MUMILEDS**

LED LUXEON Z
FWHM / FWTM 21.0° / 54.0°
Efficiency 78 %
Peak intensity 3.2 cd/lm
LEDs/each optic 4
Light colour RGBW
Required components:

equired components:
C13083\_PF-SOCKET
C13723\_MIRELLA-RZL




## LUMINUS

LED CxM-6 (12x13)
FWHM / FWTM 14.0° / 32.0°
Efficiency 86 %
Peak intensity 6.7 cd/lm
LEDs/each optic 1
Light colour White

Required components: C13083\_PF-SOCKET





## **ELUMINUS**

 LED
 CXM-7 (13x13)

 FWHM / FWTM
 17.0° / 38.0°


 Efficiency
 87 %

 Peak intensity
 5.1 cd/lm


 LEDs/each optic
 1

Light colour White Required components:
C13083\_PF-SOCKET




















#### PHOTOMETRIC DATA (MEASURED):




LED COB L-Type (LES 9)

FWHM / FWTM 19.0° / 57.0° Efficiency 85 % Peak intensity 3.4 cd/lm LEDs/each optic Light colour White Required components:

C13709\_PF-SOCKET-VERO13-18

Bender Wirth: 438 Typ L1



#### **WNICHIA**


LED NSCxL036A FWHM / FWTM 16.0° / 38.0° Efficiency 86 % Peak intensity 5.1 cd/lm LEDs/each optic 1 White Light colour Required components:

C14037\_PF-NSX-SOCKET

#### **OSRAM**

LED Duris S10  $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 13.0° / 31.0° Efficiency 87 % Peak intensity 6.6 cd/lm LEDs/each optic Light colour White Required components: C13083\_PF-SOCKET





#### **OSRAM**

LED

Duris S10 FWHM / FWTM 22.0° / 61.0° Efficiency 82 % Peak intensity 3 cd/lm LEDs/each optic White Light colour Required components: C13083\_PF-SOCKET

C13723\_MIRELLA-RZL



#### **OSRAM**

ED Duris S10
FWHM / FWTM 18.0° / 54.0°
Efficiency 80 %
Peak intensity 3.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13083\_PF-SOCKET C12479\_MIRELLA-DL




#### **OSRAM**

#### Opto Semiconductors

LED Duris S10
FWHM / FWTM 13.0° / 30.0°
Efficiency 81 %
Peak intensity 6.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C13083\_PF-SOCKET
C13333\_MIRELLA-CL





#### **OSRAM**

#### Opto Semiconductors

LED OSTAR Stage (S2WP)

 FWHM / FWTM
 21.0° / 58.0°

 Efficiency
 83 %

 Peak intensity
 3.3 cd/lm

 LEDs/each optic
 1

 Light colour
 White

 Required components:
 C13083\_PF-SOCKET

C13723\_MIRELLA-RZL




#### **OSRAM**


#### Opto Semicon

LED Ostar-SMT RGB
FWHM / FWTM 20.0° / 55.0°
Efficiency 82 %
Peak intensity 3.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C13083\_PF-SOCKET
C13723\_MIRELLA-RZL












#### SHARP

LED Mini Zenigata (GW6BM)

FWHM / FWTM 20.0° / 56.0°
Efficiency 84 %
Peak intensity 3.2 cd/lm

LEDs/each optic 1
Light colour White
Required components:
C13083\_PF-SOCKET


C12479\_MIRELLA-DL



## **XICATO**

LED XTM - 9mm LES
FWHM / FWTM 20.0° / 61.0°
Efficiency 82 %
Peak intensity 3.2 cd/lm
LEDs/each optic 1
Light colour White

Required components: C14636\_XTM-PF-ADAPTER




Published: 03/05/2018

#### PHOTOMETRIC DATA (SIMULATED):

## CREE 💠

XHP50.2  $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 11.0° / 22.0° Efficiency 90 % Peak intensity 11.2 cd/lm LEDs/each optic White

Light colour Required components:



### **MUMILEDS**

LED LUXEON CoB Compact

FWHM / FWTM 13.0° / 30.0° Efficiency 89 % Peak intensity 7.9 cd/lm LEDs/each optic 1 White Light colour

Required components:

C13761\_PF-SOCKET-CXA15

## LUMILEDS

LED LUXEON CoB Compact

 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 13.0° / 28.0° Efficiency 84 % Peak intensity 7.6 cd/lm LEDs/each optic 1 Light colour White Required components:

C13761\_PF-SOCKET-CXA15 C13333\_MIRELLA-CL

## **MUMILEDS**

LED LUXEON CoB Compact

FWHM / FWTM 15.0° / 36.0° Efficiency 84 % Peak intensity 4.8 cd/lm LEDs/each optic White Light colour Required components:

C13761\_PF-SOCKET-CXA15 C12479\_MIRELLA-DL

Published: 03/05/2018

33/41

### **MUMILEDS**

LED LUXEON CoB Compact

FWHM / FWTM 23.0° / 63.0°
Efficiency 79 %
Peak intensity 2.4 cd/lm
LEDs/each optic 1
Light colour White

Required components:


C13709\_PF-SOCKET-VERO13-18

C12479\_MIRELLA-DL Bender Wirth: 452 Typ L1

#### **MUMILEDS**

LED LUXEON K4
FWHM / FWTM 24.0° / 72.0°
Efficiency 88 %
Peak intensity 2.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:


C13761\_PF-SOCKET-CXA15



## **MATERIAL PROPERTY OF THE PROP**

LED LUXEON K4
FWHM / FWTM 42.0° / 87.0°
Efficiency 84 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13761\_PF-SOCKET-CXA15 C12479\_MIRELLA-DL



## **ELUMINUS**

LED CxM-14 (19x19)
FWHM / FWTM 31.0° / 70.0°
Efficiency 72 %
Peak intensity 1.7 cd/lm
LEDs/each optic 1
Light colour White

Required components:

C13709\_PF-SOCKET-VERO13-18

C13333\_MIRELLA-CL Bender Wirth: 433 Typ L1

#### PHOTOMETRIC DATA (SIMULATED):



LED CxM-14 (19x19)
FWHM / FWTM 29.0° / 72.0°
Efficiency 76 %
Peak intensity 1.8 cd/lm
LEDs/each optic 1
Light colour White

Required components:

C13709\_PF-SOCKET-VERO13-18

#### **ELUMINUS**

LED CxM-14 (19x19)
FWHM / FWTM 33.0° / 72.0°
Efficiency 69 %
Peak intensity 1.4 cd/lm
LEDs/each optic 1
Light colour White

Required components:

C13709\_PF-SOCKET-VERO13-18

C12479\_MIRELLA-DL Bender Wirth: 433 Typ L1

## LUMINUS

LED CxM-9 (13.5x13.5)
FWHM / FWTM 20.0° / 61.0°
Efficiency 80 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13709\_PF-SOCKET-VERO13-18

C13333\_MIRELLA-CL Bender Wirth: 434 Typ L1

## LUMINUS

LED CxM-9 (13.5x13.5)
FWHM / FWTM 21.0° / 63.0°
Efficiency 84 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13709\_PF-SOCKET-VERO13-18 Bender Wirth: 434 Typ L1

#### PHOTOMETRIC DATA (SIMULATED):



LED CxM-9 (13.5x13.5) FWHM / FWTM 27.0° / 67.0°

Efficiency 77 %
Peak intensity 2 cd/lm

LEDs/each optic 1
Light colour White

Required components:

C13709\_PF-SOCKET-VERO13-18

C12479\_MIRELLA-DL Bender Wirth: 434 Typ L1

#### **WNICHIA**

LED COB S-Type (LES 7)

FWHM / FWTM 15.0° / 41.0°
Efficiency 83 %
Peak intensity 4.9 cd/lm
LEDs/each optic 1
Light colour White

Required components:

C13709\_PF-SOCKET-VERO13-18

C13333\_MIRELLA-CL Bender Wirth: 452 Typ L1

#### **WNICHIA**

LED COB S-Type (LES 7)

FWHM / FWTM 19.0° / 49.0°
Efficiency 87 %
Peak intensity 3.9 cd/lm
LEDs/each optic 1
Light colour White

Required components:

C13709\_PF-SOCKET-VERO13-18 Bender Wirth: 452 Typ L1

#### **WNICHIA**

LED COB S-Type (LES 7)

FWHM / FWTM 23.0° / 63.0°
Efficiency 79 %
Peak intensity 2.4 cd/lm
LEDs/each optic 1
Light colour White

C13709\_PF-SOCKET-VERO13-18


C12479\_MIRELLA-DL Bender Wirth: 452 Typ L1

Required components:


36/41



#### **OSRAM** LED Duris S8 FWHM / FWTM 14.0° / 29.0° Efficiency 90 % Peak intensity 7.4 cd/lm LEDs/each optic Light colour White Required components: C13083\_PF-SOCKET C12479\_MIRELLA-DL **OSRAM**











Bender Wirth: 433 Typ L1



## **OSRAM**

LED Soleriq S9 FWHM / FWTM 24.0° / 61.0° Efficiency 87 % Peak intensity 2.9 cd/lm LEDs/each optic White Light colour Required components: C13083\_PF-SOCKET

C13333\_MIRELLA-CL





#### **OSRAM**

LED Soleriq S9

FWHM / FWTM 24.0° / 61.0°

Efficiency 86 %

Peak intensity 2.9 cd/lm


LEDs/each optic

Light colour White

Required components:

C13083\_PF-SOCKET

C12479\_MIRELLA-DL



#### **OSRAM**

LED Soleriq S9

FWHM / FWTM 19.0° / 56.0°

Efficiency 87 %


Peak intensity 3.7 cd/lm

LEDs/each optic 1 White Light colour

Required components:

C13709\_PF-SOCKET-VERO13-18

Bender Wirth: 434 Typ L1



#### **OSRAM**

LED Soleriq S9

FWHM / FWTM 21.0° / 54.0°


Efficiency 91 %

Peak intensity 3.5 cd/lm

LEDs/each optic 1

Light colour White

Required components: C13083\_PF-SOCKET



## **SAMSUNG**

LC010C

FWHM / FWTM 16.0° / 41.0°


Efficiency 87 % Peak intensity 4.8 cd/lm

LEDs/each optic

White Light colour

Required components: C13709\_PF-SOCKET-VERO13-18

Bender Wirth: 479 Typ L1



Published: 03/05/2018




## **SAMSUNG**

LED LC020C
FWHM / FWTM 16.0° / 49.0°
Efficiency 86 %
Peak intensity 4.1 cd/lm
LEDs/each optic 1
Light colour White

Required components:


C13709\_PF-SOCKET-VERO13-18 Bender Wirth: 479 Typ L1



## **SAMSUNG**

LED LC040C
FWHM / FWTM 23.0° / 66.0°
Efficiency 84 %
Peak intensity 2.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13709\_PF-SOCKET-VERO13-18 Bender Wirth: 480 Typ L1



39/41

## SEOUL SEMICONDUCTOR

LED ZC4/6
FWHM / FWTM 20.0° / 61.0°
Efficiency 80 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13709\_PF-SOCKET-VERO13-18

C13333\_MIRELLA-CL Bender Wirth: 434 Typ L1



#### SEOUL SEMICONDUCTOR

LED ZC4/6
FWHM / FWTM 21.0° / 63.0°
Efficiency 84 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:

C13709\_PF-SOCKET-VERO13-18 Bender Wirth: 434 Typ L1



#### PHOTOMETRIC DATA (SIMULATED):



LED ZC4/6 FWHM / FWTM 27.0° / 67.0°

Efficiency 77 %
Peak intensity 2 cd/lm
LEDs/each optic 1

Light colour White

Required components:

C13709\_PF-SOCKET-VERO13-18

C12479\_MIRELLA-DL Bender Wirth: 434 Typ L1



#### **GENERAL INFORMATION:**

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

#### **MATERIALS:**

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

#### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

#### **LEDIL Oy**

Joensuunkatu 13 FI-24240 SALO Finland

#### LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

## Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

## Local sales and technical support

www.ledil.com/ where\_to\_buy

#### **Shipping locations**

Salo, Finland Hong Kong, China

#### **Distribution Partners**

41/41

www.ledil.com/ where\_to\_buy