# **Model PSxx**

### **Features:**

- 100,000 cycle life
- Metal/plastic lever
- RoHS Compliant





# **Model Styles Available**

Single Gang	PSxx-1
Dual Gang	PSxx-2

### Electrical<sup>1</sup>

Resistance Range, Ohms	1K — 1M					
Standard Resistance Tolerance	± 20%					
Resistance Tapers	A, B, C					
Residual Resistance	Terminals 1 to 2: less than 10 ohm Terminals 2 to 3: less than 30 ohm					
Input Voltage, Maximum	Linear B taper: 200 Vac Other tapers: 150 Vac					
Power Rating, Watts (Single Unit / Dual Unit)	Linear B taper: 20mm: 0.1W / 0.05W, 30mm: 0.2W / 0.1W 45mm: 0.25W / 0.125W, 60mm: 0.2W / 0.2W / 0.4W Other tapers: 20mm: 0.05W / 0.025W, 30mm: 0.1W / 0.05W 45mm: 0.125W / 0.06W, 60mm: 0.1W / 0.1W					
Dielectric Strength	300 Vac, 1 minute					
Insulation Resistance, Minimum	100M ohms at 250Vdc / 1 minute					
Sliding Noise	Less than 100mV					
Gang Error	±3dB (-40dB to 0dB)					

### Notes:

<sup>&</sup>lt;sup>1</sup> Specifications subject to change without notice

### **Model PSxx**




### Mechanical

Static Stop Strength, Minimum	5.0 Kgf/cm
Operating Force	10gf to 100gf
Detent Slip-out force	30gf to 200gf

### **Durability**

Sliding Life	100,000 cycles
--------------	----------------

# **Ordering Information<sup>2</sup>**



# **Standard Resistance Values, Ohms**

1K	2K	5K	10K	20K	50K	100K	200K	500K	1 MEG

#### Notes:


Issue B 11/2020 Page 2

<sup>&</sup>lt;sup>2</sup> Contact our customer service for custom designs and features


### **Model PSxx**



# **Plastic Lever Types**



### **Metal Lever Types**




Issue B 11/2020 Page 3

# **Model PSxx**




# **Outline drawing**

### **PSxx-1 Single Gang**



### **PSxx-2 Dual Gang**



# **Model PSxx**




MODEL	Α	В	С	D	Е	F	G
PS15-1	30	26	15	17.8	20.2	28.8	
PS15-2	30	26	15	17.8	20.2	28.8	18
PS20-1	35	31	20	22.8	25.2	33.8	
PS20-2	35	31	20	22.8	25.2	33.8	23
PS30-1	45	41	30	32.8	35.2	43.8	
PS30-2	45	41	30	32.8	35.2	43.8	33
PS45-1	60	56	45	47.8	50.2	58.8	
PS45-2	60	56	45	47.8	50.2	58.8	48
PS60-1	75	71	60	62.8	65.2	73.8	
PS60-2	75	71	60	62.8	65.2	73.8	63

# **Circuit Diagram**

PSxx-1 Single Gang

2 0 3

PSxx-2 Dual Gang



Issue B 11/2020 Page 5