



## 120W - 480W Single Output DIN Rail Mount Power Supplies

Features	Benefits
• High Efficiency	• Saves Energy & Cost
• Narrow Width	• More Space in Control Equipment
• Curve B, Conducted & Radiated EMI	• Easier System Integration
• Up to 7 Year eCap-Life	• Prolonged Lifetime Expectation



Specification		DRB120-24-1	DRB240-24-1	DRB480-24-1	DRB480-48-1
Input Voltage Range	VAC	85 - 264 (withstands 300VAC for 5s)		90 - 264 <sup>(1)</sup>	
Input Frequency	Hz	47 - 63			
Inrush Current (Cold Start)	A	55A (Typical at 230VAC)		<40A (at 264VAC)	
Power Factor (115/230VAC) <sup>(2)</sup>	-	0.98 / 0.92		0.98 / 0.96	
Input Current (115/230VAC)	A	1.2 / 0.7 (115/230VAC)   2.4 / 1.4 (115/230VAC)		5 / 2.5 (115/230VAC)	
Leakage Current 264VAC 63Hz	mA	<1		<1.7	
Line Regulation	%	<0.1			
Load Regulation	%	<1			
Ripple and Noise	%	<1			
Temperature Coefficient	%/°C	<±0.02			
Overcurrent Protection	A	>6.06	>12.12	21 - 29	10.5 - 15
Overvoltage Protection <sup>(3)</sup>	V	30 - 35	30 - 35	30V ±2%	57V ±4%
Overtemperature Protection	-	Yes			
Hold Up Time	ms	20	20	>16	>16
No-load Power Consumption	W	<1	<1.5	<5	<5
Efficiency (120 / 230VAC)	%	See Model Selector			
Average efficiency (230VAC)	%	>87			
LED Indicator	-	Green LED = DC is OK			
DC OK Signal	-	Optocoupler; ON when Vout >80% of nominal output. 50V, 5mA maximum (20mA for DRB480)			
Operating Temperature	°C	DRB120/240: -25°C to +70°C. Start up at -40°C. (Derate linearly to 50% load from 55°C to 70°C) DRB480: -20°C to +70°C. Start up at -40°C. (Derate linearly to 62.5% load from 50°C to 70°C)			
Storage Temperature	°C	-40°C to +85°C			
Humidity (non condensing)	% RH	5 - 95%RH (Operating and storage)			
Parallel operation	-	No			
Series operation <sup>(4)</sup>	-	Yes			
Cooling	-	Convection			
Withstand Voltage (for 1 minute)	VAC	Input to Output 3kVAC, Input to GND 1.5kVAC, Output to GND 500VAC			
Isolation Resistance	MΩ	>100MΩ at 25°C, 70%RH & 500VDC			
Vibration (Non operating)	-	120/240W: 2G, 10 to 55Hz, 480W: 2G, IEC 60068-2-6, 10 to 500Hz			
Shock	-	120/240W: 20G, IEC 60068-2-27, half-sine, 22ms, 3 x each axis on DIN rail, 480W: 5G			
Safety agency certifications	-	UL508, IEC/EN/UL/CSA60950-1, CE Mark (LVD, EMC, RoHS2) In addition, for the DRB120 & 240: 120/240W: EN/UL/CSA62368-1, IEC/EN62477-1 OVC III (CB Report)			
Conducted & radiated EMI	-	EN55011-B, EN55032-B, CISPR11-B, CISPR22-B, EN61204-3 Class A			
Immunity	-	EN61000-4-2 (lvl 3), -3 (lvl 3), -4 (lvl 3), -5 (lvl 3), -6 (lvl 3), -8 (lvl 4), -11			
Line dips	-	SEMI -F47 (200VAC input)			
Weight (typ)	g	500	750	1000	1000
Size (W x H x D)	mm	35 x 124 x 125	41 x 124 x 125	84 x 124 x 125	
Case material	-	Metal			
Warranty	yrs	3			


**Notes:** (1) Derate linearly to 92.5% load from 100 to 90VAC (2) EN61000-3-2 Class A (3) Cycle input voltage to reset (4) See installation manual

## Model Selector


Model	Output Voltage (V)	Output Adjust Range (V)	Max Output Current (A)	Max Output Power (W)	Peak Output Current (5)	Peak Output Power (5)	Efficiency (120 / 230VAC)
DRB120-24-1	24V	24 - 28V	5A	120W	6A	144W	91 / 93% (Typ)
DRB240-24-1	24V	24 - 28V	10A	240W	12A	288W	91 / 93% (Typ)
DRB480-24-1	24V	24 - 26.4V	20A	480W	-	-	>90 / 92%
DRB480-48-1	48V	48 - 52.8V	10A	480W	-	-	>90 / 92%

Notes: (5) <10s, Duty Cycle < 35%


## Outline Drawing DRB120



## Outline Drawing DRB240



## Outline Drawing DRB480





## TDK-Lambda France SAS

3 Avenue du Canada  
Parc Technopolis  
Bâtiment Sigma  
91940 les Ulis  
France  
Tel: +33 1 60 12 71 65  
Fax: +33 1 60 12 71 66  
france@fr.tdk-lambda.com  
www.fr.tdk-lambda.com



## Italy Sales Office

Via Giacomo Matteotti 62  
20092 Cinisello Balsamo (MI)  
Italy  
Tel: +39 02 61 29 38 63  
Fax: +39 02 61 29 09 00  
info.italia@it.tdk-lambda.com  
www.it.tdk-lambda.com



## Netherlands

info@nl.tdk-lambda.com  
www.nl.tdk-lambda.com



## TDK-Lambda Germany GmbH

Karl-Bold-Strasse 40  
77855 Achern  
Germany  
Tel: +49 7841 666 0  
Fax: +49 7841 5000  
info.germany@de.tdk-lambda.com  
www.de.tdk-lambda.com



## Austria Sales Office

Aredstrasse 22  
2544 Leobersdorf  
Austria  
Tel: +43 2256 655 84  
Fax: +43 2256 645 12  
info@at.tdk-lambda.com  
www.de.tdk-lambda.com



## Switzerland Sales Office

Eichtalstrasse 55  
8634 Hombrechtikon  
Switzerland  
Tel: +41 44 850 53 53  
Fax: +41 44 850 53 50  
info@ch.tdk-lambda.com  
www.de.tdk-lambda.com



## Nordic Sales Office

Haderslevvej 36B  
DK-6000 Kolding  
Denmark  
Tel: +45 8853 8086  
info@dk.tdk-lambda.com



## TDK-Lambda UK Ltd.

Kingsley Avenue  
Ilfracombe  
Devon EX34 8ES  
United Kingdom  
Tel: +44 (0) 12 71 85 66 66  
Fax: +44 (0) 12 71 86 48 94  
powersolutions@uk.tdk-lambda.com  
www.uk.tdk-lambda.com



## TDK-Lambda Ltd.

1 Alexander Yanai  
Segula  
Petah-Tikva  
Israel  
Tel: +9 723 902 4333  
Fax: +9 723 902 4777  
info@tdk-lambda.co.il  
www.tdk-lambda.co.il



## C.I.S.

### Commercial Support:

Tel: +7 (495) 665 2627

### Technical Support:

Tel: +7 (812) 658 0463

info@tdk-lambda.ru

www.tdk-lambda.ru

## Local Distribution

