

## Water-Soluble Tacky Flux (REH1) 10cc Syringe w/plunger & tip (High Activity)

### Product Highlights

Ideal for all rework, solder, de-solder and reflow applications

Water-Soluble

Tack flux will not run all over PCB when applied

Has a pleasant odor

Excellent Wetting with High Activity (REH1) Flux

**Water-Soluble** Easily cleaned with water (60°C+)

For Leaded and Lead-Free applications

**RoHS 3 and REACH compliant**



### Specifications

Flux Type:	Synthetic Water-Soluble (for Leaded and Lead-Free applications)
Flux Classification:	REH1 (Residue must be water-washed at 60°C+ after reflow)
Flux Activation Temperature:	140°C (284°F)
Packaging:	10cc/10g Syringe
Shelf Life:	Refrigerated >24 months, Unrefrigerated >24 months

### Stencil Life

>8 hours @ 20-50% RH 22-28°C (72-82°F)

>4 hours @ 50-70% RH 22-28°C (72-82°F)

### Stencil Cleaning

Automated stencil cleaning systems for both stencil and misprinted boards. Manual cleaning using isopropyl alcohol (IPA).

### Storage and Handling

Store refrigerated or at room temperature 3-25°C (37-77°F). Do not freeze. Allow 4 hours for flux to reach an operating temperature of 20-25°C (68-77°F) before use.

### Transportation

This product has no shipping restrictions. Shipping below 0°C (32°F) or above 25°C (77°F) for normal transit times by ground or air will not impact this product's stated shelf life.

### Conforms to the following Industry Standards:

J-STD-004B, Amendment 1 (Solder Fluxes):	Yes
RoHS 3 Directive (EU) 2015/863:	Yes

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Chip Quik:](#)

[WS995](#)