

Han 100A crimp module, female



Part number	09 14 002 3151
Specification	Han 100A crimp module, female
HARTING eCatalogue	https://b2b.harting.com/09140023151

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Modules
Series	Han-Modular [®]
Type of module	Han [®] 100 A module
Version	
Termination method	Crimp termination
Gender	Female
Number of contacts	2
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	10 35 mm²
Rated current	100 A
Rated voltage	1,000 V
Rated impulse voltage	8 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500

Material properties

Material	(insert)
materia	(110011)

Polycarbonate (PC)

Page 1 / 2 | Creation date 2021-12-04 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties

Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No
California Proposition 65 substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	24 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440217 Module for industrial connectors (power/signals)