



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	A, C
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	485203835	Response Date	2014-07-22	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	280385-2	Amount	1992.8	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Substance Grouping									
JIG Level	Category Name	Threshold Level	Above Threshold Level	Mass	UOM	Description of Use	Concentration		
JIG 4.0	Chromium VI Compounds	1000.0 PPM	false						
JIG 4.0	1,2-Benzenedicarboxylic acid, 1,2-dibutyl ester	1000.0 PPM	false						
JIG 4.0	Arsenic oxide (As2O5)	1000.0 PPM	false						
JIG 4.0	Ethanol, 2-chloro-, phosphate (3:1)	1000.0 PPM	false						
JIG 4.0	Boron sodium oxide (B4Na2O7), pentahydrate	1000.0 PPM	false						
JIG 4.0	1,2-Benzenedicarboxylic acid, di-C7-11-branched and linear alkyl esters	1000.0 PPM	false						
JIG 4.0	Diocyltin Compounds (DOT) Textiles and Leather	1000.0 PPM	false						
JIG 4.0	Diocyltin Compounds (DOT) Children's Toys that can be Placed in Mouth/Child Care Articles	1000.0 PPM	false						
JIG 4.0	2-benzotriazol-2-yl-4,6-di-tert-butylphenol (UV-320)	Intentionally Added	false						
JIG 4.0	Diocyltin Compounds (DOT) RTV-2 molding kits	1000.0 PPM	false						
JIG 4.0	Chromic acid (H2CrO4), lead(2+) salt (1:1)	1000.0 PPM	false						
JIG 4.0	Lead Compounds Batteries	40.0 PPM	false						
JIG 4.0	Lead Compounds Paint/Surface Coatings of Child Products	90.0 PPM	false						

JIG 4.0	Lead Compounds Consumer Child Products	300.0 PPM	false				
JIG 4.0	Lead Compounds Thermoset/Thermoplastic Surface Coatings of Cables/cords	300.0 PPM	false				
JIG 4.0	Lead/Lead Compounds	1000.0 PPM	false				1000.0
JIG 4.0	Dimethyl fumarate	0.1 PPM or Intentionally Added	false				
JIG 4.0	Phthalates (DINP, DIDP, DNOP) Children's Toys that can be Placed in Mouth/Child Care Articles	1000.0 PPM	false				
JIG 4.0	Aluminosilicate Refractory Ceramic Fibres	1000.0 PPM	false				
JIG 4.0	Methanaminium, N-[4-[bis[4-(dimethylamino)phenyl]methylene]-2,5-cyclohexadien-1-ylidene]-N-methyl-, chloride (1:1)	1000.0 PPM	false				
JIG 4.0	Mercury Compounds Batteries	1.0 PPM	false				
JIG 4.0	Mercury/Mercury Compounds	1000.0 PPM	false				5.0
JIG 4.0	Certain Tributyl Tin (TBT) and Triphenyl Tin (TPT)	1000.0 PPM	false				
JIG 4.0	Shortchain Chlorinated Paraffins (C10 – C13)	1000.0 PPM	false				
JIG 4.0	Ozone Depleting Substances/Isomers	Intentionally Added	false				
JIG 4.0	Polybrominated Diphenylethers (PBDEs)	1000.0 PPM	false				
JIG 4.0	Brominated Flame Retardants (other than PBBs or PBDEs) Plastic Parts greater than 25 g other than in Printed Circuit Assemblies	1000.0 PPM	false				
JIG 4.0	1,2-Benzenedicarboxylic acid, 1,2-bis(2-methylpropyl) ester	1000.0 PPM	false				
JIG 4.0	Brominated Flame Retardants (other than PBBs or PBDEs) Printed wiring board laminate	900.0 PPM	false				
JIG 4.0	Formaldehyde Composite Wood Products	Intentionally Added	false				
JIG 4.0	Formaldehyde Textiles	75.0 PPM	false				
JIG 4.0	Asbestos	Intentionally Added	false				
JIG 4.0	Polychlorinated Naphthalenes (more than 3 chlorine atoms)	Intentionally Added	false				
JIG 4.0	Radioactive Substances	Intentionally Added	false				
JIG 4.0	Nickel Prolonged Skin Contact Expected	Intentionally Added	false				

JIG 4.0	Tetraboron disodium heptaoxide, hydrate	1000.0 PPM	false				
JIG 4.0	C.I. Pigment Red 104	1000.0 PPM	false				
JIG 4.0	Boric acid	1000.0 PPM	false				
JIG 4.0	1,2-Benzenedicarboxylic acid, 1,2-bis(2-ethylhexyl) ester (DEHP)	1000.0 PPM	false				
JIG 4.0	Cadmium/Cadmium Compounds	100.0 PPM	false				100.0
JIG 4.0	Cadmium Compounds Batteries	5.0 PPM	false				
JIG 4.0	Cobalt chloride (CoCl ₂)	1000.0 PPM	false				
JIG 4.0	Polybrominated Biphenyls (PBBs)	1000.0 PPM	false				
JIG 4.0	Borax (B ₄ Na ₂ O ₇ ·10H ₂ O)	1000.0 PPM	false				
JIG 4.0	Dibutyltin Compounds (DBT)	1000.0 PPM	false				
JIG 4.0	Perchlorates	0.0060 PPM	false				
JIG 4.0	Perfluorooctane sulfonate (PFOS)	Intentionally Added	false				
JIG 4.0	Polychlorinated Terphenyls (PCTs)	50.0 PPM	false				
JIG 4.0	Polyvinyl Chloride (PVC)	1000.0 PPM	false				
JIG 4.0	Distannoxane, 1,1,1,3,3,3-hexabutyl-	1000.0 PPM	false				
JIG 4.0	Phthalates (DEHP, DBP, BBP) Children's Toys that can be Placed in Mouth/Child Care Articles	1000.0 PPM	false				
JIG 4.0	Boron sodium oxide (B ₄ Na ₂ O ₇)	1000.0 PPM	false				
JIG 4.0	Arsenic oxide (As ₂ O ₃)	1000.0 PPM	false				
JIG 4.0	Amines from Azocolourants and Azodyes Textiles and Leather	30.0 PPM or Intentionally Added	false				
JIG 4.0	C.I. Pigment Yellow 34	1000.0 PPM	false				
JIG 4.0	Boric acid	1000.0 PPM	false				
JIG 4.0	Beryllium oxide (BeO) Ceramics	1000.0 PPM	false				
JIG 4.0	Zirconia Aluminosilicate Refractory Ceramic Fibres	1000.0 PPM	false				
JIG 4.0	Fluorinated greenhouse gases (HFC, PFC, SF ₆)	Intentionally Added	false				
JIG 4.0	1,2-Benzenedicarboxylic acid, di-C6-8-branched alkyl esters, C7-rich	1000.0 PPM	false				
JIG 4.0	1,2-Benzenedicarboxylic acid, 1-butyl 2-(phenylmethyl) ester (BBP)	1000.0 PPM	false				
JIG 4.0	Hexabromocyclo dodecane (HBCDD) and all major diastereoisomers	1000.0 PPM	false				
JIG 4.0	Polychlorinated Biphenyls (PCBs) and specific substitutes	Intentionally Added	false				
EU REACH	Formaldehyde, polymer with benzenamine	1000.0 PPM	false				

EU REACH	Ethane, 1,1-oxybis[2-methoxy-	1000.0 PPM	false				
EU REACH	1,2-Benzenedicarboxylic acid, 1,2-dibutyl ester	1000.0 PPM	false				
EU REACH	Phenol, 2,4,6-trinitro-, lead(2+) salt (2:1)	1000.0 PPM	false				
EU REACH	Arsenic oxide (As ₂ O ₅)	1000.0 PPM	false				
EU REACH	Ethanol, 2-chloro-, phosphate (3:1)	1000.0 PPM	false				
EU REACH	Ethene, 1,1,2-trichloro-	1000.0 PPM	false				
EU REACH	Boron sodium oxide (B ₄ Na ₂ O ₇), pentahydrate	1000.0 PPM	false				
EU REACH	1,2-Benzenedicarboxylic acid, di-C ₇ -11-branched and linear alkyl esters	1000.0 PPM	false				
EU REACH	Benzenamine, 4,4-methylenebis[2-chloro-	1000.0 PPM	false				
EU REACH	Chromic acid (H ₂ Cr ₂ O ₇)	1000.0 PPM	false				
EU REACH	Anthracene oil, anthracene paste	1000.0 PPM	false				
EU REACH	Anthracene oil, anthracene paste, anthracene fraction	1000.0 PPM	false				
EU REACH	Chromic acid (H ₂ CrO ₄), lead(2+) salt (1:1)	1000.0 PPM	false				
EU REACH	Aluminosilicate Refractory Ceramic Fibres	1000.0 PPM	false				
EU REACH	Anthracene oil, anthracene-low	1000.0 PPM	false				
EU REACH	Alkanes, C ₁₀ -13, chloro	1000.0 PPM	false				
EU REACH	1,2-Benzenedicarboxylic acid, 1,2-bis(2-methylpropyl) ester	1000.0 PPM	false				
EU REACH	Propane, 1,2,3-trichloro-	1000.0 PPM	false				
EU REACH	Arsenic acid (H ₃ AsO ₄), lead(2+) salt (1:1)	1000.0 PPM	false				
EU REACH	Arsenic acid (H ₃ AsO ₄), calcium salt (2:3)	1000.0 PPM	false				
EU REACH	Potassium zinc chromate hydroxide (KZn ₂ (CrO ₄) ₂ (OH))	1000.0 PPM	false				
EU REACH	Diamino-diphenylmethane (4,4-Diaminodiphenylmethane)	1000.0 PPM	false				
EU REACH	Pitch, coal tar, high-temp.	1000.0 PPM	false				
EU REACH	Chromic acid (H ₂ Cr ₂ O ₇), sodium salt (1:2)	1000.0 PPM	false				
EU REACH	1(3H)-Isobenzofuranone, 3,3-bis(4-hydroxyphenyl)-	1000.0 PPM	false				
EU REACH	Sulfuric acid, cobalt(2+) salt (1:1)	1000.0 PPM	false				
EU REACH	Zinc chromate hydroxide (Zn ₅ (CrO ₄)(OH) ₈)	1000.0 PPM	false				
EU REACH	2-Pyrrolidinone, 1-methyl-	1000.0 PPM	false				

EU REACH	Acetamide, N,N-dimethyl-	1000.0 PPM	false				
EU REACH	Ethane, 1,2-dichloro-	1000.0 PPM	false				
EU REACH	Tetraboron disodium heptaoxide, hydrate	1000.0 PPM	false				
EU REACH	C.I. Pigment Red 104	1000.0 PPM	false				
EU REACH	Ethanol, 2-ethoxy-, 1-acetate	1000.0 PPM	false				
EU REACH	Refractories, fibers, aluminosilicate	1000.0 PPM	false				
EU REACH	Chromic acid (H ₂ CrO ₄), sodium salt (1:2)	1000.0 PPM	false				
EU REACH	Boric acid	1000.0 PPM	false				
EU REACH	1,2-Benzenedicarboxylic acid, 1,2-bis(2-ethylhexyl) ester (DEHP)	1000.0 PPM	false				
EU REACH	Acetic acid, cobalt(2+) salt (2:1)	1000.0 PPM	false				
EU REACH	Lead azide (Pb(N ₃) ₂)	1000.0 PPM	false				
EU REACH	2-Methoxyaniline	1000.0 PPM	false				
EU REACH	Cobalt chloride (CoCl ₂)	1000.0 PPM	false				
EU REACH	Benzene, 1-methyl-2,4-dinitro-	1000.0 PPM	false				
EU REACH	Anthracene	1000.0 PPM	false				
EU REACH	Anthracene oil, anthracene paste, distn. Lights	1000.0 PPM	false				
EU REACH	Anthracene oil	1000.0 PPM	false				
EU REACH	Triethyl arsenate	1000.0 PPM	false				
EU REACH	Borax (B ₄ Na ₂ O ₇ ·10H ₂ O)	1000.0 PPM	false				
EU REACH	Carbonic acid, cobalt(2+) salt (1:1)	1000.0 PPM	false				
EU REACH	2-Methoxyethanol	1000.0 PPM	false				
EU REACH	Hydrazine	1000.0 PPM	false				
EU REACH	Arsenic acid (H ₃ AsO ₄)	1000.0 PPM	false				
EU REACH	Chromium oxide (CrO ₃)	1000.0 PPM	false				
EU REACH	Chromic acid (H ₂ Cr ₂ O ₇), ammonium salt (1:2)	1000.0 PPM	false				
EU REACH	Distannoxane, 1,1,1,3,3,3-hexabutyl-	1000.0 PPM	false				
EU REACH	Chromic acid (H ₂ Cr ₂ O ₇), potassium salt (1:2)	1000.0 PPM	false				
EU REACH	1,3-Benzenediol, 2,4,6-trinitro-, lead(2+) salt (1:1)	1000.0 PPM	false				
EU REACH	1,2-Benzenedicarboxylic acid, 1,2-bis(2-methoxyethyl) ester	1000.0 PPM	false				
EU REACH	Arsenic acid (H ₃ AsO ₄), lead(2+) salt (2:3)	1000.0 PPM	false				
EU REACH	Boron sodium oxide (B ₄ Na ₂ O ₇)	1000.0 PPM	false				
EU REACH	Nitric acid, cobalt(2+) salt (2:1)	1000.0 PPM	false				
EU REACH	Arsenic oxide (As ₂ O ₃)	1000.0 PPM	false				
EU REACH	Chromic acid (H ₂ CrO ₄)	1000.0 PPM	false				

EU REACH	Benzenamine, 2-methoxy-	1000.0 PPM	false				
EU REACH	5-tert-butyl-2,4,6-trinitro-m-xylene (musk xylene)	1000.0 PPM	false				
EU REACH	C.I. Pigment Yellow 34	1000.0 PPM	false				
EU REACH	Ethanol, 2-ethoxy-	1000.0 PPM	false				
EU REACH	2-Propenamide	1000.0 PPM	false				
EU REACH	Boric acid	1000.0 PPM	false				
EU REACH	Chromic acid (H ₂ CrO ₄), strontium salt (1:1)	1000.0 PPM	false				
EU REACH	Chromic acid (H ₂ CrO ₄), potassium salt (1:2)	1000.0 PPM	false				
EU REACH	Phenol, 4-(1,1,3,3-tetramethylbutyl)-	1000.0 PPM	false				
EU REACH	Zirconia Aluminosilicate Refractory Ceramic Fibres	1000.0 PPM	false				
EU REACH	Chromic acid (H ₂ CrO ₇), sodium salt, hydrate (1:2:2)	1000.0 PPM	false				
EU REACH	1,2-Benzenedicarboxylic acid, di-C6-8-branched alkyl esters, C7-rich	1000.0 PPM	false				
EU REACH	Chromic acid (H ₂ CrO ₄), chromium(3+) salt (3:2)	1000.0 PPM	false				
EU REACH	1,2-Benzenedicarboxylic acid, 1-butyl 2-(phenylmethyl) ester (BBP)	1000.0 PPM	false				
EU REACH	Hydrazine, monohydrate	1000.0 PPM	false				
EU REACH	Hexabromocyclo dodecane (HBCDD) and all major diastereoisomers	1000.0 PPM	false				
EU RoHS	Chromium VI Compounds	1000.0 PPM	false				
EU RoHS	Cadmium/Cadmium Compounds	100.0 PPM	false				100.0
EU RoHS	Polybrominated Biphenyls (PBBs)	1000.0 PPM	false				
EU RoHS	Lead/Lead Compounds	1000.0 PPM	false				1000.0
EU RoHS	Mercury/Mercury Compounds	1000.0 PPM	false				5.0
EU RoHS	Polybrominated Diphenylethers (PBDEs)	1000.0 PPM	false				