Shock-Safe Fuseholder, 5 x 20 mm, Slotted Cap/Fingergrip, IP 40 / IP 67, IEC 60335-1





Closed fuseholder 5 x 20 mm slotted black Screw-on mounting from front side horizontal with finger grip fingergrip

## 250 VAC · 2.5 W / 10 A (VDE) · 500 V · 16 A (UL/CSA)

#### Description

- Compact design
- Heading with fingergrip and slotted available
- Degree of protection IP67 available
- White color available on request

# Approvals and Compliances

Applications

Household appliancesMedical Equipment

#### Weblinks

See below:

pdf data sheet, html datasheet, General Product Information, Distributor-Stock-Check, Accessories, Detailed request for product, Microsite

| Technical Data               |   |                              |   |
|------------------------------|---|------------------------------|---|
| Shock-Safe Category          | PC2   | Soldering Methods            | Iron  |
| Fuse-Link                    | 5 x 20 mm   |                              | Soldering Profile                               |
| Mounting                     | Panel mount, Front Side   | Solderability                | 350 °C / 3 sec acc. to IEC 60068-2-20,          |
| Attachment                   | Fixing Nut  |                              | Test Ta, method 2                               |
| Terminal                     | Solder / Quick-Connect 4.8 x 0.5 mm   | Resistance to Soldering Heat | 350°C / 10 sec acc. to IEC 60068-2-20,          |
| Rated Voltage                | 250 VAC (VDE), 500 V (UL/CSA)   |                              | Test Tb, method 2                               |
| Rated current                | 10A (VDE), 16A (UL/CSA)   | Solderability                | 350 °C / 3 sec acc. to IEC 60068-2-20,          |
| Rated Power Acceptance IEC   | 2.5W / 10A @ Ta 23°C  |                              | Test Ta, method 2                               |
|                              | Admissible power acceptance at higher   | Contact Resistance           | $\leq 10 \text{ m}\Omega$ at 100 mA acc. to IEC |
|                              | ambient temperature see derating cur-   |                              | 60127-6   |
|                              | Ves   | Dielectric Strength          | > 3kV between life parts                        |
| Degree of Protection         | IP40 / IP67   |                              | (50Hz: 1 min)                                   |
| Protection Class             | Suitable for appliances with protection   | Impulse Withstand Voltage    | > 4 kV between life parts                       |
|                              | class I acc. to IEC 61140   | Insulation Resistance        | ≥ 10 M $\Omega$ between life parts              |
| Admissible Ambient Air Temp. | -40 °C to 85 °C   |                              | (500 VDC: 1 min)                                |
| Climatic Category            | 40/085/21 acc. to IEC 60068-1   | Overvoltage Category         | III acc. to IEC 60664-1                         |
| Material: Socket             | Thermoplastic, black, UL 94V-0  | Pollution Degree             | 3 acc. to IEC 60664-1                           |
| Material: Terminals          | Copper alloy, tin-plated  | Resistance to Vibration      | acc. to IEC 60068-2-6, test Fc                  |
| Unit Weight                  | 5.7 g   | Admissible Torque on Fixing  | max 1.2 Nm                                      |
| Storage Conditions           | 0°C to 60°C, max. 70% r.h.  | Nut                          |   |
| Product Marking              | <ul> <li>Type, Rated Voltage, Rated current,<br/>Power Rating, Certification marks</li> </ul> | Panel Thickness              | max 6mm   |

#### **Approvals and Compliances**

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

### Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: FPG1

| Approval Logo | Certificates  | Certification Body | Description                    |
|---------------|---------------|--------------------|--------------------------------|
| NE NE         | VDE Approvals | VDE                | VDE Certificate Number: 127216 |
|               | UL Approvals  | UL                 | UR File Number: E39328         |
| <u>s</u>      | KTL Approvals | KTL                | Korea Testing Laboratory       |

#### **Product standards**

Product standards that are referenced

| Organization | Design                | Standard             | Description  |
|--------------|-----------------------|----------------------|--|
| IEC          | Designed according to | IEC 60127-6          | Miniature fuses. Part 6. Fuse-holders for miniature fuse-links |
| (UL)         | Designed according to | UL 4248-1            | Industrial Control Equipment                                   |
| CSA<br>Group | Designed according to | CSA C22.2 no. 4248.1 | Industrial Control Equipment                                   |

#### **Application standards**

Application standards where the product can be used

| Organization | Design                         | Standard       | Description  |
|--------------|--------------------------------|----------------|--|
| IEC          | Designed for applications acc. | IEC/UL 62368-1 | Audio/video, information and communication technology equipment - Part<br>1: Safety requirements   |
| IEC.         | Designed for applications acc. | IEC 60335-1    | Safety of electrical appliances for household and similar purposes. Meets the requirements for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 & -13. |


#### Compliances

The product complies with following Guide Lines


| The product complies with following duide Lines |                                |             |   |  |
|---|--------------------------------|-------------|---|--|
| Identification                                  | Details                        | Initiator   | Description   |  |
| CE  | CE declaration of conformity   | SCHURTER AG | The CE marking declares that the product complies with the applicable<br>requirements laid down in the harmonisation of Community legislation on<br>its affixing in accordance with EU Regulation 765/2008. |  |
| UK<br>CA  | UKCA declaration of conformity | SCHURTER AG | The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.  |  |
| COMPLIANT                                       | RoHS                           | SCHURTER AG | Directive RoHS 2011/65/EU, Amendment (EU) 2015/863  |  |
| <b>©</b>  | China RoHS                     | SCHURTER AG | The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.  |  |
| REACH   | REACH                          | SCHURTER AG | On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration,<br>Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as<br>"REACH") entered into force.                               |  |
| 00  | White Paper Glow wire test     | SCHURTER AG | Meets the requirements of IEC 60335-1 for appliances in unattended use.<br>This includes the enhanced requirements of glow wire tests acc. to IEC<br>60695-2-11 or -12 &-13.                                |  |

#### **Dimension** [mm]







IP40 / Variants 3101.0010 and 3101.0210




 $\ensuremath{\mathsf{IP40}}\xspace$  / Variants Fingergrip 3101.0015 and 3101.0215






IP67 / Variants 3101.0110 and 3101.0310

IP67 / Variants Fingergrip 3101.0115 and 3101.0315



#### Panel cut-out

#### **Derating Curves**



#### **All Variants**

| Holder | Сар        | Terminal                   | Degree of<br>Protection | Material      | Remark | Order Number |
|--------|------------|----------------------------|-------------------------|---------------|--------|--------------|
| •      | slotted    | Solder                     | IP40                    | Thermoplastic | -      | 3101.0010    |
| •      | slotted    | Quick-Connect 4.8 x 0.5 mm | IP40                    | Thermoplastic | -      | 3101.0210    |
| •      | Fingergrip | Solder                     | IP40                    | Thermoplastic | -      | 3101.0015    |
| •      | Fingergrip | Quick-Connect 4.8 x 0.5 mm | IP40                    | Thermoplastic | -      | 3101.0215    |
| •      | slotted    | Solder                     | IP67                    | Thermoplastic | -      | 3101.0110    |
| •      | slotted    | Quick-Connect 4.8 x 0.5 mm | IP67                    | Thermoplastic | -      | 3101.0310    |
| •      | Fingergrip | Solder                     | IP67                    | Thermoplastic | -      | 3101.0115    |
| •      | Fingergrip | Quick-Connect 4.8 x 0.5 mm | IP67                    | Thermoplastic | -      | 3101.0315    |

#### Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Packaging Unit

Bulk 186 x 91 x 91 mm (100 pcs.)

# FPG1

#### Accessories

Description



Nut for fuse holder Mounting accessories for fuse holder



Designation plates for fuse holders Marking plate for Fuseholders