



Dustproof:
 Protection class IP 54 to IEC 529 (EN 60 529)
 Terminals shape similar to DIN ISO 8092-1:
 Coil terminals 6,3 mm x 0,8 mm
 Load terminals 9,5 mm x 1,2 mm
 Integrated component: Resistor

No.	PART	MATERIAL	COLOUR
5	Base	PA 66 GF 25	Black sim. RAL 9005
4	Cover	PA 66 GF 25	Grey sim. RAL 7005
3	Load terminal (87)	E-Cu	Pre-tinned Sn
2	Load Terminal (30)	E-Cu	Pre-tinned Sn
1	Coil terminals (85) and (86)	CuSn	Pre-tinned Sn

TE P/N	PART NUMBER	COUNTRY OF ORIGIN
1393304-5	V23134-J0056-X408	Portugal
8-1904094-4	V23134.J0056X408-SZ-CBOX	China

PROFITABILITY
 IN REPRODUCTION, TRANSMISSION OR USE OF THIS DOCUMENT OR ITS CONTENTS IS NOT PERMITTED WITHOUT EXPRESSED WRITTEN AUTHORITY. OFFENDERS WILL BE LIABLE FOR ALL DAMAGES, ALL RIGHTS, INCLUDING RIGHTS GRANTED BY REGISTERED PATENTS ARE RESERVED.
 CHANGES TO THIS DRAWING MUST BE DONE ONLY IN CAD
 SYMBOL SIZE: A2

DIMENSIONS APPLY		PLATING	
SCALE	WEIGHT		
2:1			
DIMENSIONS IN MM		PARTIAL	
OWN: 27.02.2009 L. Sandoval		PART NAME	
APP: [Signature]		POWER F RELAY MAXI Plug-in N/O	
LOCATION: AMR PE EVORA		PART NO. V23134-J0056-X408	
DATE: [Signature]		SHT. 1 OF 1	

