

1250 Rocker Switches 10A 250Vac



10(6)A 250Vac T100
6A 400Vac T100
1A 30Vdc



UL CSA 10A 250Vac
UL CSA 16A 250Vac Resistive
UL CSA 125Vac 1/2hp
UL CSA 1A 30Vdc
UL 100°C, file E45221, CSA file LR10990

In house test

Inrush 75A to EN61058-1



RoHS compliant

3mm contact gap
Technical data on pages 4 & 5

- ▶ Standard rocker switch
- ▶ Double pole in single pole body
- ▶ Snap in or sub panel mount
- ▶ Integral terminal barrier
- ▶ Push on or PCB terminals
- ▶ High inrush tolerance
- ▶ Panel cut out:
27.2 x 12.4 (snap in)
26.3 x 12.4 (sub panel mount)



C1250AP ---



C1250AN ---











Rocker switches

B BLACK
W WHITE
G GREY

C 1250 A P B B 085W


TERMINAL CODE FUNCTION CODE ROCKER CODE BODY CODE BODY COLOR ROCKER COLOR LEGEND & OPTIONS

ORDER FORMAT


TERMINAL	FUNCTION	ROCKER	BODY	OPTIONS						
<p>C</p>  <p>6.3 x 0.8</p>	 <p>On when pressed over terminal 1</p> <p>1250</p>  <p>ON - OFF Double pole</p> <p>Poles are 9.0mm between centres.</p>	<p>A Curved</p>  <p>Shown in N body</p>	<p>N</p> <p>Panel cut-out Bezel</p>  <p>Sub-panel Facia</p> <p>Panel thickness Dim X</p> <table border="0"> <tr> <td>0.75-1.24</td> <td>26.1/26.2</td> </tr> <tr> <td>1.25-1.99</td> <td>26.3/26.4</td> </tr> <tr> <td>2.00-3.00</td> <td>26.7/26.8</td> </tr> </table>	0.75-1.24	26.1/26.2	1.25-1.99	26.3/26.4	2.00-3.00	26.7/26.8	<p>Finish Matt finish only.</p> <p>Color Call factory for custom colors. A full range is available for large orders.</p> <p>Legend printing Select from the examples or call factory for custom legends.</p> <p>Contact factory for suggested terminals.</p>
0.75-1.24	26.1/26.2									
1.25-1.99	26.3/26.4									
2.00-3.00	26.7/26.8									
<p>X</p>  <p>PCB 0.8sq (N body only)</p>	 <p>On when pressed over terminal 1</p> <p>1250SP</p>  <p>ON - OFF Single pole</p>	<p>P</p>  <p>Shown in P body</p>	<p>P</p> <p>Panel cut-out Bezel</p>  <p>Panel thickness</p> <p>0.75-3.00</p> <p>Cut-outs must be punched in the direction of insertion</p>							

Dimensions (mm)


1250AN (C terminals shown)



1250AN (X terminals shown)



1250AP (C terminals shown)



Connector Housing F1344

