Relays

multicomp PRO



Coil Data

Nominal Power

Contact Data

| Contact Material | : Ag alloy |
|------------------|---|
| Contact Rating | : 1A : 15A 125V AC / 24V DC, 10A 250V AC 1C : 10A 120V AC / 24V DC, 6A 250V AC |
| | TV-5 |

: 360mW

| | 1 V-3 | |
|------------------------|------------------------|--|
| Max. Switching Voltage | : 250V AC / 24V DC | |
| Max. Switching Current | : 15A | |
| Max. Switching Power | : 1,800VA, 360W | |
| Min. Switching Load | : 5V DC, 100mA | |
| Contact Resistance | : Max. 50mΩ (6V DC 1A) | |
| | | |

Life

Electrical: 100,000 operationsMechanical: 10,000,000 operations

General Data

| Insulation Resistance | : Min. 1,000mW 500V DC |
|-----------------------|---|
| Dielectric Strength | : 750V AC, 1 min. between open contacts |
| | 1,500V AC, I min. between coil and contacts |
| Operate Time | : Max. 10ms |
| Release Time | : Max. 5ms |
| Operate Temperature | : -30°C to +85°C |

Shock Resistance

| Endurance | : 1,000m/s² |
|---------------|-------------|
| Mis-operation | : 100m/s² |

Vibration Resistance

| Endurance | : 10 to 55Hz, 1.5mm double amplitude |
|---------------|--------------------------------------|
| Mis-operation | : 10 to 50Hz, 1.5mm double amplitude |
| Humidity | : 35% to 95% RH, +40°C |
| Weight | : Approximately 10g |


Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

multicomp PRO


Coil Data Chart

| Nominal Voltage V DC | Coil Resistance W ±10% | Operate Voltage ≤V DC | Release Voltage ≥V DC | Coil Power mW | Contact Form | Part Number |
|----------------------------|------------------------------|-----------------------------|-----------------------------|------------------|-----------------|-------------|
| 12 | 400 | 8.4 | 1.2 | 360 | 1 Form C | MC25138 |
| 24 | 1,600 | 16.8 | 2.4 | | I FOITI C | MC25139 |

Dimensions




Characteristic Chart Data




Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro


Coil Temperature Rise



multicomp PRO

Characteristic Chart Data





Part Number Table

| Description | Part Number | |
|---|-------------|--|
| General Purpose Relay, Power, SPDT, 12V DC, 10A | MC25138 | |
| General Purpose Relay, Power, SPDT, 24V DC, 10A | MC25139 | |

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

