

ALMD-EL3D, ALMD-EG3D, ALMD-CM3D, ALMD-CB3D

High Brightness SMT Round LED Lamps Amber, Red, Green, and Blue Tinted LEDs



Description

The Broadcom[®] ALMD-xx3D LED series has the same or just slightly less luminous intensity than conventional high-brightness, through-hole LEDs.

The new LED lamps can be assembled using common SMT assembly processes and are compatible with industrial reflow soldering processes.

The LEDs are made with an advanced optical grade epoxy for superior performance in outdoor sign applications.

For easy pick-and-place assembly, the LEDs are shipped in EIA-compliant tape and reel. Every reel is shipped from a single intensity and color bin—except the red color—for better uniformity.

Features

- Compact form factor
- High brightness material
- Available in Red, Amber, Green, and Blue colors
- Red AllnGaP 626 nm
- Amber AllnGaP 590 nm
- Green InGaN 525 nm
- Blue InGaN 470 nm
- JEDEC MSL 2A
- Compatible with industrial reflow soldering process
- Typical Viewing angle: 30°
- Tinted, non-diffused

Applications


Variable message signs

CAUTION! InGaN devices are Class 1C HBM ESD sensitive, AlInGaP devices are Class 1B ESD sensitive per JEDEC Standard. Observe appropriate precautions during handling and processing. Refer to Application Note AN-1142 for additional details.

CAUTION! Keep the LED in the moisture barrier bag (MBB) when not in use because prolonged exposure to environment might cause the silver-plated leads to tarnish, which might cause difficulties in soldering.

Broadcom

Figure 1: Package Dimensions



NOTE:

- 1. All dimensions are in millimeters.
- 2. Tolerance is ± 0.20 mm unless other specified.
- 3. Copper lead frame.

Device Selection Guide

	Color and Dominant Wavelength λ_d (nm)	Luminous Intens	sity Iv (mcd) ^{b, c, d}	
Part Number	Typ. ^a	Min.	Max.	Viewing Angle Typ (°) ^e
ALMD-EG3D-WY002	Red 626	5500	12000	30
ALMD-EG3D-XY002	Red 626	7200	12000	
ALMD-EL3D-WY002	Amber 590	5500	12000	
ALMD-EL3D-XYK02	Amber 590	7200	12000	
ALMD-EL3D-XYL02	Amber 590	7200	12000	
ALMD-CM3D-Y1002	Green 525	9300	21000	
ALMD-CB3D-SU002	Blue 470	1900	4200	

a. Dominant wavelength, λ_d , is derived from the CIE Chromaticity Diagram and represents the color of the lamp.

b. The luminous intensity is measured on the mechanical axis of the lamp package and it is tested with pulsing condition.

c. The optical axis is closely aligned with the package mechanical axis.

d. Tolerance for each bin limit is \pm 15%.

e. $\theta_{1\!\!/_2}$ is the off-axis angle where the luminous intensity is half the on-axis intensity.

X₁

Part Numbering System

ALMD

x₂ x₃ x₄

x₅ x₆ x₇ x₈ x₉

Code	Description	Option			
x ₁	Package type	E	Round AllnGaP		
		С	Round InGaN		
x ₂	Color	В	Blue		
		G	Red		
		L	Amber		
		М	Green		
x ₃	Viewing angle	3	30°		
x ₄	Product specification designation	D			
x ₅	Minimum intensity bin	Refer to	o device selection guide		
x ₆	Maximum intensity bin	Refer to	o device selection guide		
х ₇	Color bin selection	0	Full distribution		
		К	Color bin 2 and 4		
		L	Color bin 4 and 6		
x ₈ x ₉	Packaging option	02 Tested 20 mA, 13-inch carrier tape			

Intensity Bin Limit Table (1.3:1 lv Bin Ratio)

	Intensity (mcd) at 20 mA			
Bin	Min.	Max.		
S	1900	2500		
Т	2500	3200		
U	3200	4200		
V	4200	5500		
W	5500	7200		
Х	7200	9300		
Y	9300	12000		
Z	12000	16000		
1	16000	21000		

Tolerance for each bin limit is \pm 15%.

V_F Bin Table (V at 20 mA) for Red and Amber

Bin ID	Min.	Max.
V _D	1.8	2.0
V _A	2.0	2.2
V _B	2.2	2.4

Tolerance for each bin limit is ± 0.05 V.

Red Color Range

Min. Dom.	Max. Dom.	X Min.	Y Min.	X Max.	Y Max.
618.0	630.0	0.6872	0.3126	0.6890	0.2943
		0.6690	0.3149	0.7080	0.2920

Tolerance for each bin limit is ± 0.5 nm.

Amber Color Range

Bin	Min. Dom.	Max. Dom.	X Min.	Y Min.	X Max.	Y Max.
1	584.5	587.0	0.5420	0.4580	0.5530	0.4400
			0.5370	0.4550	0.5570	0.4420
2	587.0	589.5	0.5570	0.4420	0.5670	0.4250
			0.5530	0.4400	0.5720	0.4270
4	589.5	592.0	0.5720	0.4270	0.5820	0.4110
			0.5670	0.4250	0.5870	0.4130
6	592.0	594.5	0.5870	0.4130	0.5950	0.3980
			0.5820	0.4110	0.6000	0.3990

Tolerance for each bin limit is ± 0.5 nm.

Green Color Range

Bin	Min. Dom.	Max. Dom.	X Min.	Y Min.	X Max.	Y Max.
1	519.0	523.0	0.0667	0.8323	0.1450	0.7319
			0.1200	0.7375	0.0979	0.8316
2	523.0	527.0	0.0979	0.8316	0.1711	0.7218
			0.1450	0.7319	0.1305	0.8189
3	527.0	531.0	0.1305	0.8189	0.1967	0.7077
			0.1711	0.7218	0.1625	0.8012
4	531.0	535.0	0.1625	0.8012	0.2210	0.6920
			0.1967	0.7077	0.1929	0.7816
5	535.0	539.0	0.1929	0.7816	0.2445	0.6747
			0.2210	0.6920	0.2233	0.7600

Tolerance for each bin limit is ± 0.5 nm.

Blue Color Range

Bin	Min. Dom.	Max. Dom.	X Min.	Y Min.	X Max.	Y Max.
1	460.0	464.0	0.1440	0.0297	0.1766	0.0966
			0.1818	0.0904	0.1374	0.0374
2	464.0	468.0	0.1374	0.0374	0.1699	0.1062
			0.1766	0.0966	0.1291	0.0495
3	468.0	472.0	0.1291	0.0495	0.1616	0.1209
			0.1699	0.1062	0.1187	0.0671
4	472.0	476.0	0.1187	0.0671	0.1517	0.1423
			0.1616	0.1209	0.1063	0.0945
5	476.0	480.0	0.1063	0.0945	0.1397	0.1728
			0.1517	0.1423	0.0913	0.1327

Tolerance for each bin limit is ± 0.5 nm.

Absolute Maximum Rating, $T_J = 25^{\circ}C$

Parameter	Red and Amber	Blue and Green	Unit
DC Forward Current ^a	50	30	mA
Peak Forward Current	100 ^b	100 ^c	mA
Power Dissipation	120	114	mW
Reverse Voltage	5 (I _R = 100 µA) ^d	5 (I _R = 10 μA) ^d	V
LED Junction Temperature	110		°C
Operating Temperature Range	-40 t	°C	
Storage Temperature Range	-40 to	o +100	°C

a. Derate linearly as shown in Figure 5 and Figure 10.

b. Duty factor 30%, frequency 1 kHz.

c. Duty factor 10%, frequency 1 kHz.

d. Indicates product final testing; long-term reverse bias is not recommended.

Electrical/Optical Characteristics, $T_J = 25^{\circ}C$

Parameter	Symbol	Min.	Тур.	Max.	Units	Test Conditions
Forward Voltage Red Amber Green Blue	V _F	1.8 1.8 2.8 2.8	2.1 2.1 3.2 3.2	2.4 2.4 3.8 3.8	V	I _F = 20 mA
Reverse Voltage Red and Amber Green and Blue	V _R	5 5			V	I _R = 100 μA I _R = 10 μA
Dominant Wavelength ^a Red Amber Green Blue	λ _d	618.0 584.5 519.0 460.0	626.0 590.0 525.0 470.0	630.0 594.5 539.0 480.0		I _F = 20 mA
Peak Wavelength Red Amber Green Blue	λρεακ		634 594 516 464		nm	Peak of Wavelength of Spectral Distribution at I _F = 20 mA
Thermal Resistance	$R\theta_{J-PIN}$		130		°C/W	LED Junction-to-Pin
Luminous Efficacy ^b Red Amber Green Blue	ην		200 520 530 65		lm/W	Emitted Luminous Power/Emitted Radiant Power
Thermal coefficient of λ _d Red Amber Green Blue			0.059 0.103 0.028 0.024		nm/°C	I _F = 20 mA; +25 °C ≤ T _J ≤ +100 °C

a. The dominant wavelength is derived from the Chromaticity Diagram and represents the color of the lamp.

b. The radiant intensity, I_e in watts per steradian, may be found from the equation $I_e = I_V/\eta_V$ where I_V is the luminous intensity in candelas and η_V is the luminous efficacy in lumens/watt.

AllnGaP

Figure 2: Relative Intensity vs. Wavelength




Figure 4: Relative Intensity vs. Forward Current





Figure 6: Relative Dominant Wavelength Shift vs. Forward Current



100 80 FORWARD CURRENT - mA 60 40 20

Figure 3: Forward Current vs. Forward Voltage





Figure 5: Maximum Forward Current vs. Ambient Temperature



NOTE: Rθ_{J-A} = 460 °C/W.

InGaN

Figure 7: Relative Intensity vs. Wavelength




Figure 9: Relative Intensity vs. Forward Current




Figure 11: Dominant Wavelength Shift vs. Forward Current




Figure 8: Forward Current vs. Forward Voltage




Figure 10: Maximum Forward Current vs. Ambient Temperature




Figure 12: Radiation Pattern for X Axis




Figure 14: Relative Intensity Shift vs. Junction Temperature





Figure 16: Recommended Soldering Land Pattern



NOTE: Recommended stencil thickness is 0.1524 mm (6 mils) minimum and above.

Figure 13: Component Axis for Radiation Pattern




Figure 15: Forward Voltage Shift vs. Junction Temperature




Figure 17: Carrier Tape Dimension




Figure 18: Reel Dimension






Figure 19: Unit Orientation from Reel




Soldering

Recommended reflow soldering condition.


(i) Leaded reflow soldering



(ii) Lead-free reflow soldering



- Reflow soldering must not be done more than twice. Make sure you take the necessary precautions for handling a moisture-sensitive device, as stated in the following section.
- Recommended board reflow direction:




- Do not apply any pressure or force on the LED during reflow and after reflow when the LED is still hot.
- Use reflow soldering to solder the LED. Use hand soldering only for rework if unavoidable but must be strictly controlled to the following conditions:
 - Soldering iron tip temperature = 320°C maximum.
 - Soldering duration = 3 seconds maximum.
 - Number of cycles = 1 only.
 - Power of soldering iron = 50 W maximum.
- Do not touch the LED body with a hot soldering iron except the soldering terminals because this may damage the LED.
- For de-soldering, use a double-flat tip.
- Confirm beforehand whether the functionality and performance of the LED is affected by hand soldering.

Precautionary Notes

Handling Precautions

For automated pick and place, Broadcom has tested the following nozzle size made with urethane material to work well with this LED. However, due to the possibility of variations in other parameters, such as pick-and-place, machine maker/model and other settings of the machine, verify the nozzle selected.



NOTE:

- 1. The nozzle tip should touch the LED flange during pick-and-place.
- 2. Outer dimensions of the nozzle should be able to fit into the carrier tape pocket.

Handling of Moisture-Sensitive Devices

This product has a Moisture Sensitive Level 2a rating per JEDEC J-STD-020. Refer to Broadcom Application Note AN5305, *Handling of Moisture Sensitive Surface Mount Devices*, for additional details and a review of proper handling procedures.

Before use

- An unopened moisture barrier bag (MBB) can be stored at <40°C / 90%RH for 12 months. If the actual shelf life has exceeded 12 months and the humidity indicator card (HIC) indicates that baking is not required, it is safe to reflow the LEDs per the original MSL rating.
- Do not open the MBB prior to assembly (for example, for IQC).

Control after opening the MBB

Read the HIC immediately upon opening of MBB.

The LEDs must be kept at <30°C/60% RH at all times and all high-temperature-related processes, including soldering, curing, or rework, must be completed within 672 hours.

Control for unfinished reel

Unused LEDs must be stored in a sealed MBB with desiccant or desiccator at <5% RH.

Control of assembled boards

If the PCB soldered with the LEDs is to be subjected to other high-temperature processes, store the PCB in a sealed MBB with desiccant or desiccator at <5% RH to ensure that all LEDs have not exceeded their floor life of 672 hours.

Baking is required if the following conditions exist

- The HIC indicator is not BROWN at 10% and is AZURE at 5%.
- The LEDs are exposed to condition of >30°C / 60% RH at any time.
- The LED floor life exceeded 672 hrs.

The recommended baking condition is: $60^{\circ}C \pm 5^{\circ}C$ for 20 hours. Baking should only be done once.

Storage

The soldering terminals of these Broadcom LEDs are silver plated. If the LEDs are being exposed in an ambient environment for too long, the silver plating might be oxidized and thus affecting its solderability performance. As such, keep unused LEDs in a sealed MBB with desiccant or in desiccator at <5% RH.

Application Precautions

- Drive current of the LED must not exceed the maximum allowable limit across temperature as stated in the data sheet. Constant current driving is recommended to ensure consistent performance.
- LEDs exhibit slightly different characteristics at different drive currents that might result in larger performance variations (such as intensity, wavelength, and forward voltage). Set the application current as close as possible to the test current to minimize these variations.
- The LED is not intended for reverse bias. Use other appropriate components for such purposes. When driving the LED in matrix form, ensure that the reverse bias voltage does not exceed the allowable limit of the LED.
- Avoid rapid change in ambient temperatures, especially in high-humidity environments, because they will cause condensation on the LED.
- If the LED is intended to be used in an outdoor or a harsh environment, protect the LED leads with suitable potting material against damages caused by rain water, oil, corrosive gases, and so on. Use a louver or shade to reduce direct sunlight on the LEDs.

Eye Safety Precautions

LEDs may pose optical hazards when in operation. Do not look directly at operating LEDs because it may be harmful to the eyes. For safety reasons, use appropriate shielding or personal protective equipment.

Disclaimer

Broadcom's products and software are not specifically designed, manufactured, or authorized for sale as parts, components, or assemblies for the planning, construction, maintenance, or direct operation of a nuclear facility or for use in medical devices or applications. The customer is solely responsible, and waives all rights to make claims against Broadcom or its suppliers, for all loss, damage, expense, or liability in connection with such use.

Broadcom, the pulse logo, Connecting everything, Avago Technologies, Avago, and the A logo are among the trademarks of Broadcom and/or its affiliates in the United States, certain other countries, and/or the EU.

Copyright © 2016–2020 Broadcom. All Rights Reserved.

The term "Broadcom" refers to Broadcom Inc. and/or its subsidiaries. For more information, please visit www.broadcom.com.

Broadcom reserves the right to make changes without further notice to any products or data herein to improve reliability, function, or design. Information furnished by Broadcom is believed to be accurate and reliable. However, Broadcom does not assume any liability arising out of the application or use of this information, nor the application or use of any product or circuit described herein, neither does it convey any license under its patent rights nor the rights of others.



