

LISA2-RS-PIN

~19° spot beam. 6.8 mm high variant with location pin installation.

TECHNICAL SPECIFICATIONS:

Dimensions	Ø 9.9 mm
Height	6.8 mm
Fastening	glue, pin
ROHS compliant	yes 🕕



MATERIAL SPECIFICATIONS:


Component	Type	Material	Colour	Finish
LISA2-RS	Single lens	PMMA	clear	
LISA2-HLD-PIN	Holder	PC	black	

ORDERING INFORMATION:

» Box size: 310 x 230 x 60 mm

Component		Qty in box	MOQ	MPQ	Box weight (kg)
FP11055_LISA2-RS-PIN	Single lens	2000	300	100	1.4






See also our general installation guide: www.ledil.com/installation_guide



PHOTOMETRIC DATA (MEASURED):






PHOTOMETRIC DATA (MEASURED):

LEDs/each optic

Required components:

Light colour

IR






PHOTOMETRIC DATA (MEASURED):

SAMSUNG

LED LH181B
FWHM / FWTM 16.0° / 50.0°
Efficiency 71 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour White

Required components:



SHARP

LED Double Dome (GM2BB)

FWHM / FWTM 18.0°
Efficiency 90 %
LEDs/each optic 1
Light colour White
Required components:



PHOTOMETRIC DATA (SIMULATED):

CREE 💠

LED XQ-A


FWHM / FWTM 10.0° / 20.0° Efficiency 90 %

Efficiency 90 %

Peak intensity 21.5 cd/lm LEDs/each optic 1

White

Light colour
Required components:



CREE 🕏

LED XQ-E HD


FWHM / FWTM 14.5° / 28.5°

Efficiency 91 %

Peak intensity 10.1 cd/lm LEDs/each optic 1

LEDs/each optic 1
Light colour White

Required components:



UMILEDS


LED LUXEON IR 2720

FWHM / FWTM 14.0° / 34.0°

Efficiency 88 % LEDs/each optic 1

Light colour IR

Required components:



OSRAM


LED OSLON Black Flat

FWHM / FWTM 12.0° / 28.0° Efficiency 89 %

Peak intensity 11.4 cd/lm

LEDs/each optic 1
Light colour White

Required components:





PHOTOMETRIC DATA (SIMULATED):

OSRAM

LED

OSLON Square EC

FWHM / FWTM

18.0° / 40.0° 90 %

Efficiency Peak intensity


5.6 cd/lm

LEDs/each optic

White

Light colour

Required components:



OSRAM

LED OSLON SSL 150 FWHM / FWTM 16.0° / 32.0°

Efficiency

92 %

Peak intensity

9 cd/lm


LEDs/each optic

1

Light colour

White

Required components:



OSRAM Opto Semiconductor

LED OSLON SSL 80

FWHM / FWTM 16.0° / 35.0°


Efficiency 90 % 7.5 cd/lm

Peak intensity LEDs/each optic

1

Light colour White

Required components:



OSRAM

LED

SFH 4170S

FWHM / FWTM

10.0° / 22.0°

Efficiency


77 %

1

LEDs/each optic

Required components:

IR Light colour





PRODUCT DATASHEET FP11055_LISA2-RS-PIN

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

www.ledil.com/ where_to_buy