


Data sheet

valid from: 2/8/19



Short Version
Float in PVDF without magnet
With solvent cement sockets PVC-U BS Inch

Model:

- Union nuts and valve ends in other materials on request

Type	Scale range (l/h)	d (inch)	DN (mm)	Taper tube in Polysulfone O-rings in EPDM Code	Taper tube in PVC- U transp. Orings in EPDM Code	Weight (kg)	D (mm)	L (mm)	L1 (mm)	L2 (mm)
SK50	2.5 - 25	3/8	10	198 807 000	20014A290	0.190	35	199	171	165
SK51	5 - 50	3/8	10	198 807 001	20014A291	0.190	35	199	171	165
SK52	10 - 100	3/8	10	198 807 002	20014A292	0.190	35	199	171	165
SK60	8 - 80	1/2	15	198 807 003	20014A293	0.260	43	223	191	185
SK61	15 - 150	1/2	15	198 807 004	20014A294	0.260	43	223	191	185
SK62	2 - 200	1/2	15	198 807 005	20014A295	0.260	43	223	191	185
SK70	15 - 150	1	25	198 807 006	20014A296	0.470	60	250	206	200
SK71	30 - 300	1	25	198 807 007	20014A297	0.470	60	250	206	200
SK72	50 - 500	1	25	198 807 008	20014A298	0.470	60	250	206	200
SK73	100 - 1000	1	25	198 807 009	20014A299	0.470	60	250	206	200

The technical data are not binding. They neither constitute expressly warranted characteristics nor guaranteed properties nor a guaranteed durability. They are subject to modification. Our General Terms of Sale apply.

Georg Fischer Piping Systems Ltd, Postfach, CH-8201 Schaffhausen/Switzerland

Phone +41 -(0)52-631 1111

e-mail: info.ps@georgfischer.com

Internet: <http://www.gfps.com>