

APT1608LSECK/J4-PRV

1.6 x 0.8 mm SMD Chip LED Lamp



DESCRIPTIONS

- The Orange source color devices are made with AIGaInP Light Emitting Diode
- · Electrostatic discharge and power surge could damage the LEDs
- · It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- · All devices, equipments and machineries must be electrically grounded

FEATURES

- 1.6 mm x 0.8 mm SMD LED, 0.75 mm thickness
- Low power consumption
- Wide viewing angle
- · Ideal for backlight and indicator
- Package: 2000 pcs / reel
- Moisture sensitivity level: 3
- Halogen-free
- RoHS compliant

APPLICATIONS


- Backlight
- Status indicator
- · Home and smart appliances
- · Wearable and portable devices
- Healthcare applications

ATTENTION

Observe precautions for handling electrostatic discharge sensitive devices



PACKAGE DIMENSIONS



RECOMMENDED SOLDERING PATTERN

(units : mm: tolerance : ± 0.1)



Notes

All dimensions are in millimeters (inches).
 Tolerance is ±0.1(0.004") unless otherwise noted.
 The specifications, characteristics and technical data described in the datasheet are subject to

change without prior notice. The device has a single mounting surface. The device must be mounted according to the specifications.

SELECTION GUIDE

| Part Number | Emitting Color (Material) | Lens Type | Iv (mcd) @ 2mA ^[2] | | Viewing Angle ^[1] | |
|---------------------|----------------------------------|-------------|-------------------------------|------|------------------------------|--|
| | | | Min. | Тур. | 201/2 | |
| APT1608LSECK/J4-PRV | Super Bright Orange (AlGaInP) | Water Clear | 80 | 150 | 400 [°] | |
| | | | *30 | *50 | 120° | |

Notes

1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
 2. Luminous intensity / luminous flux: +/-15%.
 * Luminous intensity value is traceable to CIE127-2007 standards.

Kingbright

ELECTRICAL / OPTICAL CHARACTERISTICS at T_A=25°C

| Parameter | Querra ha a l | E 100 A 1 | Value | | | |
|--|--------------------------------|-------------------------|-------|-----------|------|-------|
| Parameter | Symbol | Emitting Color | Min. | Typ. Max. | Unit | |
| Wavelength at Peak Emission I_F = 2mA | λ_{peak} | Super Bright Orange | - | 611 | - | nm |
| Dominant Wavelength I_F = 2mA | λ_{dom} ^[1] | Super Bright Orange | - | 605 | - | nm |
| Spectral Bandwidth at 50% Φ REL MAX I _F = 2mA | Δλ | Super Bright Orange | - | 17 | - | nm |
| Capacitance | С | Super Bright Orange | - | 27 | - | pF |
| Forward Voltage $I_F = 2mA$ | V _F ^[2] | Super Bright Orange | 1.5 | 1.8 | 2.1 | V |
| Reverse Current ($V_R = 5V$) | I _R | Super Bright Orange | - | - | 10 | μΑ |
| Temperature Coefficient of λ_{peak} I_F = 2mA, -10°C \leq T \leq 85°C | TC _{λpeak} | Super Bright Orange | - | 0.13 | - | nm/°C |
| Temperature Coefficient of λ_{dom} I _F = 2mA, -10°C \leq T \leq 85°C | TC _{λdom} | Super Bright Orange | - | 0.06 | - | nm/°C |
| Temperature Coefficient of V _F I_F = 2mA, -10°C \leq T \leq 85°C | TCv | Super Bright Orange | - | -2 | - | mV/°C |

The dominant wavelength (λd) above is the setup value of the sorting machine. (Tolerance λd : ±1nm.)
 Forward voltage: ±0.1V.
 Wavelength value is traceable to CIE127-2007 standards.

4. Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.


ABSOLUTE MAXIMUM RATINGS at $T_A=25^{\circ}C$

| Parameter | Symbol | Value | Unit |
|--|-----------------------------------|------------|------|
| Power Dissipation | P _D | 84 | mW |
| Reverse Voltage | V _R | 5 | V |
| Junction Temperature | Tj | 115 | °C |
| Operating Temperature | T _{op} | -40 to +85 | °C |
| Storage Temperature | T _{stg} | -40 to +85 | °C |
| DC Forward Current | I _F | 30 | mA |
| Peak Forward Current | ۱ _{FM} ^[1] | 150 | mA |
| Electrostatic Discharge Threshold (HBM) | - | 3000 | V |
| Thermal Resistance (Junction / Ambient) | R _{th JA} ^[2] | 410 | °C/W |
| Thermal Resistance (Junction / Solder point) | R _{th JS} ^[2] | 310 | °C/W |


Notes: 1. 1/10 Duty Cycle, 0.1ms Pulse Width. 2. R_{th. Js}, R_{th. JS} Results from mounting on PC board FR4 (pad size ≥ 16 mm² per pad). 3. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.

Kingbright

TECHNICAL DATA




SPATIAL DISTRIBUTION




2.5


SUPER BRIGHT ORANGE




Luminous Intensity vs. Ambient Temperature




REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS




TAPE SPECIFICATIONS (units:mm)



REEL DIMENSION (units : mm)





Notes

- Don't cause stress to the LEDs while it is exposed to high temperature.
 The maximum number of reflow soldering passes is 2 times.
 Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.


Short Short Strate Contraction (Contraction) Spec No: DSAN8388 / 1203014456 Rev No: V.35A Date: 02/17/2021

Kingbright

APT1608LSECK/J4-PRV

PACKING & LABEL SPECIFICATIONS

(XXXXXXXXX-XXX



PRECAUTIONARY NOTES

- The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications. 2.
- When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening 3.
- 4. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright. All design applications should refer to Kingbright application notes available at <u>https://www.KingbrightUSA.com/Application</u>
- 5.
- 6. onNotes