Y5V Dielectric

General Specifications






GENERAL DESCRIPTION


Y5V formulations are for general-purpose use in a limited temperature range. They have a wide temperature characteristic of +22% capacitance change over the operating temperature range of -30°C to $+85^{\circ}\text{C}$.


These characteristics make Y5V ideal for decoupling applications within limited temperature range.





PART NUMBER (SEE PAGE 4 FOR COMPLETE PART NUMBER EXPLANATION)



















Y5V Dielectric

Specifications and Test Methods



Parame	ter/Test	Y5V Specification Limits	Measuring Conditions						
	perature Range	-30°C to +85°C	Temperature Cycle Chamber						
	itance on Factor	Within specified tolerance ≤ 5.0% for ≥ 50V DC rating ≤ 7.0% for 25V DC rating ≤ 9.0% for 16V DC rating ≤ 12.5% for ≤ 10V DC rating	Freq.: 1.0 kHz ± 10% Voltage: 1.0Vrms ± .2V For Cap > 10 μF, 0.5Vrms @ 120Hz						
Insulation	Resistance	10,000MΩ or 500MΩ - μF, whichever is less	Charge device with rated voltage for 120 ± 5 secs @ room temp/humidity						
Dielectric	Strength	No breakdown or visual defects	Charge device with 250% of rated voltage for 1-5 seconds, w/charge and discharge current limited to 50 mA (max)						
	Appearance	No defects	Deflection						
Resistance to	Capacitance Variation	≤ ±30%	Test Time: 30 seconds 1mm/sec						
Flexure Stresses	Dissipation Factor	Meets Initial Values (As Above)							
	Insulation Resistance	≥ Initial Value x 0.1	90 mm —						
Solder	ability	≥ 95% of each terminal should be covered with fresh solder	Dip device in eutection for 5.0 ± 0.						
	Appearance	No defects, <25% leaching of either end terminal							
Resistance to Solder Heat	Capacitance Variation	≤ ±20%	<u> </u>						
	Dissipation Factor	Meets Initial Values (As Above)	Dip device in eutectic solder at 260°C for 60 seconds. Store at room temperature for 24 ± 2						
	Insulation Resistance	Meets Initial Values (As Above)	hours before measuring electrical properties.						
	Dielectric Strength	Meets Initial Values (As Above)							
	Appearance	No visual defects	Step 1: -30°C ± 2°	30 ± 3 minutes					
	Capacitance Variation	≤ ±20%	Step 2: Room Temp	≤ 3 minutes					
Thermal Shock	Dissipation Factor	Meets Initial Values (As Above)	Step 3: +85°C ± 2°	30 ± 3 minutes					
	Insulation Resistance	Meets Initial Values (As Above)	Step 4: Room Temp	≤ 3 minutes					
	Dielectric Strength	Meets Initial Values (As Above)	Repeat for 5 cycles 24 ±2 hours at ro						
	Appearance	No visual defects							
	Capacitance Variation	≤ ±30%	Charge device with twice rated voltage in test						
Load Life	Dissipation Factor	≤ Initial Value x 1.5 (See Above)	chamber set at 85°C ± 2°C for 1000 hours (+48, -0)						
	Insulation Resistance	≥ Initial Value x 0.1 (See Above)	Remove from test chamber and stabilize at room temperature for 24 ± 2 hours before measuring.						
	Dielectric Strength	Meets Initial Values (As Above)	, and a second s						
	Appearance	No visual defects							
	Capacitance Variation	≤ ±30%	Store in a test chamber set at 85°C ± 2°C/ 85% ± 5% relative humidity for 1000 hours (+48, -0) with rated voltage applied. Remove from chamber and stabilize at room temperature and humidity for 24 ± 2 hours before measuring.						
Load Humidity	Dissipation Factor	≤ Initial Value x 1.5 (See above)							
riumuity	Insulation Resistance	≥ Initial Value x 0.1 (See Above)							
	Dielectric Strength	Meets Initial Values (As Above)							



Y5V Dielectric

Capacitance Range



PREFERRED SIZES ARE SHADED

SIZE	SIZE 0201		0402				0603			0805				1206				1210						
Solderii	ng	Reflov	v Only	,		Reflow/Wave		Reflow/Wave			Reflow/Wave			ReflowMfeve			Reflow/Wave							
Packagi	ng	All P	aper	All Paper			All Paper		Paper/Embossed			Paper/Embossed			Paper/Embossed									
(L) Length		0.60 ±	£ 0.09	1.00 ± 0.10				1.60 ± 0.15				2.01 ± 0.20			3.20 ± 0.20			3.20 ± 0.20						
(L) Length	(0.024 ±		(0.040 ± 0.004)				(0	0.063 :	± 0.00	6)	(0.079 ± 0.008)				(0.126 ± 0.008)				(0.126 ± 0.008)					
W) Width	mm	0.30 ±			0.50 ± 0.10			.81 ± 0.15			1.25 ± 0.20				1.60 ± 0.20				2.50 ± 0.20					
vv) vvidili	(in.)	(£ 0.004)	(0.020 ± 0.004)				(0.032 ± 0.006)			(0.049 ± 0.008)				(0.063 ± 0.008)				(0.098 ± 0.008)					
(t) Terminal mm (in.)		0.15 ±			25 ± 0.					± 0.15				± 0.25				± 0.25		4-		0.25		
		(0.006 ±	(0.010 ± 0.006)			,	0.014 :			(0.020 ± 0.010)			-,	(0.020 ± 0.010)				(0.020 ± 0.010)						
Сар	WVDC 820	63	10	6	10	16	25	50	10	16	25	50	10	16	25	50	10	16	25	50	10	16	25	50
(pF)	1000																				~	' 	₹w.	
(pr)	2200		A															*						
	4700		A																<u> </u>	(5		\Box	ŢT
Сар	0.010	Α	A																	_	$\overline{}$			
(μF)	0.022	A	_ ^																		4	-		
(μι)	0.047	A				С														ı	, '		1 1	, 1
	0.10	,,			С	C					G	G				К				İ				i l
	0.22									G										İ				i
	0.33									G														
	0.47					С				G	G		İ		İ		İ			İ				i i
	1.0			С	С				G	G	J			N	N	N		М	М	М				N
	2.2				С				J					N	N				K	Q				
	4.7												N	N	N			Р	Q			N	N	
	10.0												N	Р			Q	Q	Х		Х	Q	Q	Х
	22.0																Q				Х	Z		
	47.0	63	10		10	16	25	50	10	16	25	50	10	16	25	- 50	10	16	25	50	10	16	25	50
SIZE	WVDC			6	10	0402	_ 25_	50	10			_50_	10 16 25 50 0805		50	10 16 25 50 1206			1210			_ 50		
SIZE	SIZE 0201					0402				0603				Uð	UJ			12	00		1210			

Letter	Α	С	E	G	J	K	М	N	Р	Q	Х	Υ	Z			
Max.	0.33	0.56	0.71	0.90	0.94	1.02	1.27	1.40	1.52	1.78	2.29	2.54	2.79			
Thickness	(0.013)	(0.022)	(0.028)	(0.035)	(0.037)	(0.040)	(0.050)	(0.055)	(0.060)	(0.070)	(0.090)	(0.100)	(0.110)			
	PAPER						FMBOSSED									

