

Electrical Specifications

Rated Power ($T_U=40^{\circ}\text{C}$):	0,4W
Operating Voltage, Max.:	500V DC
Insulation Voltage:	1000V AC
Insulation Resistance	5G Ω
Resistance Tolerance	
100 Ω ...1M Ω :	20%
>1M Ω :	30%

Mechanical Specifications

Rotation Angle (Mechanical):	300° \pm 5°
Operating Torque:	0,4...1,5Ncm
Stop Strength, Max.:	80Ncm
Weight:	ca. 11g

Dimensions

Plastic Spindle	
Dimensions (D):	6,0mm
Length (L):	50,0mm
Bush (C):	8,0mm
Spindle (A):	M10x0,75
PC Terminations:	5/5 (10)mm