


Hyperfast Rectifier, 2 A FRED Pt[®]

eSMP[®] Series



Top View

Bottom View

SlimSMAW (DO-221AD)

FEATURES

- Low profile package
- Ideal for automated placement
- Low forward voltage drop, low power losses
- Low leakage current
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Compatible to SOD-128 package case outline
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

DESIGN SUPPORT TOOLS

[click logo to get started](#)

3D
Models
Available

DESCRIPTION / APPLICATIONS

For use in high frequency, freewheeling, DC/DC converters, PFC, and in snubber industrial, and automotive applications.

MECHANICAL DATA

Case: SlimSMAW (DO-221AD)

Molding compound meets UL 94 V-0 flammability rating
Halogen-free, RoHS-compliant

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

Polarity: color band denotes the cathode end

| PRIMARY CHARACTERISTICS | |
|-------------------------|---------------------|
| $I_{F(AV)}$ | 2 A |
| V_R | 100 V, 200 V |
| V_F at I_F | 0.69 V |
| I_{FSM} | 60 A |
| t_{rr} (typ.) | 15 ns |
| T_J max. | 175 °C |
| Package | SlimSMAW (DO-221AD) |
| Circuit configuration | Single |

| ABSOLUTE MAXIMUM RATINGS | | | | |
|---|----------------------------|--------------------------------------|-------------|-------|
| PARAMETER | SYMBOL | TEST CONDITIONS | VALUES | UNITS |
| Peak repetitive reverse voltage | VS-2EYH01-M3 | V_{RRM} | 100 | V |
| | VS-2EYH02-M3 | | 200 | |
| Average rectified forward current | $I_{F(AV)}$ ⁽¹⁾ | $T_C = 151$ °C | 2 | A |
| Non-repetitive peak surge current | I_{FSM} | $T_J = 25$ °C, 10 ms sine pulse wave | 60 | |
| Operating junction and storage temperatures | T_J, T_{Stg} | | -55 to +175 | °C |

Note

⁽¹⁾ Mounted on infinite heatsink

| ELECTRICAL SPECIFICATIONS ($T_J = 25$ °C unless otherwise specified) | | | | | | | |
|---|--------------|-----------------------------------|---------------------|------|------|---------|---|
| PARAMETER | SYMBOL | TEST CONDITIONS | MIN. | TYP. | MAX. | UNITS | |
| Breakdown voltage, blocking voltage | VS-2EYH01-M3 | V_{BR}, V_R | $I_R = 100$ μ A | 100 | - | - | V |
| | VS-2EYH02-M3 | | | 200 | - | - | |
| Forward voltage, per diode | V_F | $I_F = 2$ A | - | 0.86 | 0.93 | | |
| | | $I_F = 2$ A, $T_J = 150$ °C | - | 0.69 | 0.75 | | |
| Reverse leakage current, per diode | I_R | $V_R = V_R$ rated | - | - | 2 | μ A | |
| | | $T_J = 150$ °C, $V_R = V_R$ rated | - | - | 20 | | |
| Junction capacitance | C_T | $V_R = 200$ V | - | 12 | - | pF | |



| DYNAMIC RECOVERY CHARACTERISTICS (T _J = 25 °C unless otherwise specified) | | | | | | |
|--|------------------|---|------|------|------|-------|
| PARAMETER | SYMBOL | TEST CONDITIONS | MIN. | TYP. | MAX. | UNITS |
| Reverse recovery time | t _{rr} | I _F = 1.0 A, di _F /dt = 50 A/μs, V _R = 30 V | - | 22 | - | ns |
| | | I _F = 1.0 A, di _F /dt = 100 A/μs, V _R = 30 V | - | 15 | - | |
| | | I _F = 0.5 A, I _R = 1A, I _{rr} = 0.25 A | - | - | 28 | |
| | | T _J = 25 °C | - | 16 | - | |
| | | T _J = 125 °C | - | 26 | - | |
| Peak recovery current | I _{RRM} | T _J = 25 °C | - | 2.7 | - | A |
| | | T _J = 125 °C | - | 3.4 | - | |
| Reverse recovery charge | Q _{rr} | T _J = 25 °C | - | 20 | - | nC |
| | | T _J = 125 °C | - | 43 | - | |

| THERMAL - MECHANICAL SPECIFICATIONS | | | | | | |
|--|-----------------------------------|---|------|------|------|-------|
| PARAMETER | SYMBOL | TEST CONDITIONS | MIN. | TYP. | MAX. | UNITS |
| Maximum junction and storage temperature range | T _J , T _{Stg} | | -55 | - | 175 | °C |
| Thermal resistance, junction to mount | R _{thJM} ⁽¹⁾ | Infinite heatsink | - | 12 | 15 | °C/W |
| Thermal resistance, junction to ambient | R _{thJA} | Device mounted on FR4 PCB, 2 oz. standard footprint | - | 120 | 150 | |
| Marking device | VS-2EYH01-M3 | Case style SlimSMAW (DO-221AD) | 2H1 | | | |
| | VS-2EYH02-M3 | | 2H2 | | | |

Note

(1) Thermal resistance junction to mount follows JEDEC® 51-14 transient dual interface test method (TDIM)




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics




Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current




Fig. 6 - Forward Power Loss Characteristics

Note

- (1) Formula used: $T_C = T_J - (P_d + P_{dREV}) \times R_{thJC}$;
- P_d = forward power loss = $I_{F(AV)} \times V_{FM}$ at $(I_{F(AV)}/D)$ (see fig. 5);
- P_{dREV} = inverse power loss = $V_{R1} \times I_R (1 - D)$; I_R at V_{R1} = rated V_R




Fig. 7 - Typical Reverse Recovery Time vs. di_F/dt




Fig. 8 - Typical Stored Charge vs. di_F/dt

ORDERING INFORMATION TABLE

| | | | | | | | | |
|-------------|--|----------|----------|----------|----------|-----------|----------|-----------|
| Device code | VS- | 2 | E | Y | H | 02 | - | M3 |
| | ① | ② | ③ | ④ | ⑤ | ⑥ | | ⑦ |
| | 1 | 2 | 3 | 4 | 5 | 6 | | 7 |
| | - | - | - | - | - | - | | - |
| | Vishay Semiconductors product | | | | | | | |
| | Current rating (2 = 2 A) | | | | | | | |
| | Circuit configuration: | | | | | | | |
| | E = single diode | | | | | | | |
| | Y = SlimSMAW (DO-221AD) | | | | | | | |
| | Process type, | | | | | | | |
| | H = hyperfast recovery | | | | | | | |
| | Voltage code (02 = 200 V) | | | | | | | |
| | M3 = halogen-free, RoHS-compliant, and terminations lead (Pb)-free | | | | | | | |

| ORDERING INFORMATION (Example) | | | | |
|--------------------------------|-----------------|------------------------|---------------|------------------------------------|
| PREFERRED P/N | UNIT WEIGHT (g) | PREFERRED PACKAGE CODE | BASE QUANTITY | PACKAGING DESCRIPTION |
| VS-2EYH01-M3/H | 0.033 | H | 3500 | 7" diameter plastic tape and reel |
| VS-2EYH01-M3/I | 0.033 | I | 14 000 | 13" diameter plastic tape and reel |
| VS-2EYH02-M3/H | 0.033 | H | 3500 | 7" diameter plastic tape and reel |
| VS-2EYH02-M3/I | 0.033 | I | 14 000 | 13" diameter plastic tape and reel |





| LINKS TO RELATED DOCUMENTS | |
|----------------------------|--|
| Dimensions | www.vishay.com/doc?96582 |
| Part marking information | www.vishay.com/doc?95562 |
| Packaging information | www.vishay.com/doc?88869 |
| SPIICE model | www.vishay.com/doc?96585 |



SlimSMAW (DO-221AD)

DIMENSIONS in inches (millimeters)

SlimSMAW (DO-221AD)



Mounting pad layout



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.