



44 Flux-Cored Wire

Activated Rosin Cored Wire for Lead-Free and Leaded Alloys

Product Description

Kester 44 Flux-Cored Wire is an activated rosin formula for use in flux-cored solder wire. 44 has virtually dominated the field of activated rosin core solders for well over five decades. An outstanding performance feature of this flux is the "instant- action" wetting behavior. The high mobility and fast-spreading action of this flux results in more reliable production line soldering. Under IPC J-STD-004, 44 is classified as ROM1. Despite the increased activity and soldering performance, 44 passes both 85 °C/85% RH and 40 °C/90% RH SIR test methods.

Performance Characteristics:

- High activity RA formulation
- Passes both 85 °C/85% RH and 40°C/90% RH IPC SIR testing
- Excellent solderability to a wide range of metallizations
- Industry standard RA cored wire for decades
- Classified as ROM1 per J-STD-004

RoHS Compliance

Kester does not determine any applicable Restriction of Hazardous Substances (RoHS) exemptions for our lead containing products at the user level. (Applies only if this core flux is combined with a lead-free alloy.)

Reliability Properties

Copper Mirror Corrosion: Moderate

Tested to J-STD-004, IPC-TM-650, Method 2.3.32

Corrosion Test: Moderate

Tested to J-STD-004, IPC-TM-650, Method 2.6.15

Silver Chromate: Fail

Tested to J-STD-004, IPC-TM-650, Method 2.6.33

Chloride and Bromides: 0.44%

Tested to J-STD-004, IPC-TM-650, Method 2.6.35







Fluorides by Spot Test: Pass

Tested to J-STD-004, IPC-TM-650, Method 2.6.35.1

Surface Insulation Resistance (SIR) 40 °C/90% RH, IPC (typical): Pass

Tested to J-STD-004B, IPC-TM-650, Method 2.6.3.7

Surface Insulation Resistance(SIR), IPC (typical): Pass

Tested to J-STD-004, IPC-TM-650, Method 2.6.3.3

Test Conditions: 85 °C, 85% RH, 7 days, 100V

	Blank	44
Day 1	7.46*10 ⁹ Ω	2.2*10 ⁸ Ω
Day 4	4.9*10 ⁹ Ω	2.88*10 ⁹ Ω
Day 7	7.7*10 ⁹ Ω	7.14*10 ⁹ Ω

Availability

44 is available in a wide variety of alloys, wire diameters, flux percentages and roll sizes in both leaded and lead-free alloys. The most common alloys are Sn63Pb37 and Sn60Pb40. Please refer to https://www.kester.com for more information.

Note: Core size 50, 58 and 66 = 1.1%, 2.2% and 3.3% flux core, respectively.

Process Considerations

Solder iron tip temperatures are most commonly between 315 to 343 °C (600 to 650 °F) for leaded alloys and 371 to 400 °C (700 to 750 °F) for lead-free alloys. Heat both the land area and component lead to be soldered with the iron tip prior to applying the solder wire to land area or component lead. Do not apply the wire directly to the soldering iron tip; doing so will shorten the life of the soldering tip.

Additional liquid flux should only be used as a last resort. Any flux applied to the solder location should be kept to the area of the connection being reworked. If needed, Kester 186 or Kester NF372-TB may be used as a compatible liquid fluxes to aid in reworking soldered joints. Kester 186 and Kester NF372-TB are also available in Flux-Pens® for optimum board cleanliness.

Cleaning

44 possesses excellent fluxing ability; the flux residues are non-corrosive, non-conductive and do not require removal for most applications under normal conditions of use. IPA will not clean the residues off the surface of the circuit board after the soldering process. If removal is required, a saponifier or cleaning agent specifically designed to clean a no-clean flux is required to clean the residues. Please contact Kester Technical Support for further information.





TECHNICAL DATA SHEET

Storage, Handling and Shelf Life

Storage must be in a dry, non-corrosive environment between 10 to 40 °C (50 to 104 °F). The surface may lose its shine and appear a dull shade of grey. This is a surface phenomenon and is not detrimental to product functionality. Flux-cored solder wire has a shelf life determined by the alloy used in the wire. For alloys containing more than 70% lead, the shelf life is 2 years from the date of manufacture. Other alloys have a shelf life of 3 years from the date of manufacture.

Health and Safety

This product, during handling or use, may be hazardous to your health or the environment. Read the Safety Data Sheet and warning label before using this product. Safety Data Sheets are available at https://www.kester.com/downloads/sds.

Contact Information

To confirm this document is the most recent version, please contact Assembly@MacDermidAlpha.com

North America	Asia Pacific	Europe
800 West Thorndale Avenue	8/F., Paul Y. Centre	Ganghofer Strasse 45
Itasca, IL USA 60143	51 Hung To Road Kwun Tong, Kowloon, Hong Kong	82216 Gernlinden, Germany
Phone: +1 800.2.KESTER	Phone: +852.3190.3100	Phone: +49 (0) 8142 4785 0

Also read carefully warning and safety information on the Safety Data Sheet. This data sheet contains technical information required for safe and economical operation of this product. READ IT THOROUGHLY PRIOR TO PRODUCT USE. Emergency safety directory assistance: US 1 202 464 2554, Europe + 44 1235 239 670, Asia + 65 3158 1074, Brazil 0800 707 7022 and 0800 172 020, Mexico 01800 002 1400 and (55) 559 1588

DISCLAIMER: All statements, technical information and recommendations contained herein are based on tests we believe to be reliable, but the accuracy or completeness thereof is not guaranteed. No statement or recommendation shall constitute a representation unless set forth in an agreement signed by officers of seller and manufacturer. NO WARRANTY OF MERCHANTABILITY, WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY IS MADE. The following warranty is made in lieu of such warranties and all other warranties, express, implied, or statutory, Products are warranted to be free from defects in material and workmanship at the time sold. The sole obligation of seller and manufacturer under this warranty shall be to replace any noncompliant product at the time sold. Under no circumstances shall manufacturer or seller be liable for any loss, damage or expense, direct, incidental or consequential, arising out of the inability to use the product. Notwithstanding the foregoing, if products are used under conditions exceeding said parameters, the customer by acceptance or use thereof assumes all risk of product failure and of all direct, indirect, incidental and consequential damages that may result from use of the products under such conditions, and agrees to exonerate, indemnify, defend and hold harmless MacDermid, incorporated and its affiliates therefrom. No suggestion for product use nor anything contained herein shall be construed as a recommendation to use any product in a manner that infringes any patent or other intellectual property rights, and seller and manufacturer assume no responsibility or liability for any such infringement.

© 2019 MacDermid, Inc. and its group of companies. All rights reserved. "(R)" and "TM" are registered trademarks of MacDermid, Inc. and its group of companies in the United States and/or other countries.

