

APHHS1005F3C-70MAV

1.0 x 0.5 mm Infrared Emitting Diode



DESCRIPTION

• F3 Made with Gallium Arsenide Infrared Emitting diodes


FEATURES


- 1.0 mm x 0.5 mm SMD LED, 0.5 mm thickness
- · Mechanically and spectrally matched to the phototransistor
- Package: 2000 pcs / reel
- Moisture sensitivity level: 3
- · RoHS compliant


APPLICATIONS


- Infrared Illumination for cameras
- · Machine vision systems
- Surveillance systems
- · Industrial electronics
- · IR data transmission
- Remote control

PACKAGE DIMENSIONS










RECOMMENDED SOLDERING PATTERN

(units : mm; tolerance : ± 0.1)



Notes

1. All dimensions are in millimeters (inches).

Tolerance is ±0.1(0.004") unless otherwise noted.
 The specifications, characteristics and technical data described in the datasheet are subject to

change without prior notice. 4. The device has a single mounting surface. The device must be mounted according to the specifications.

SELECTION GUIDE

Part Number	Emitting Color (Material)	Lens Type	Po (mW/sr) @ 70mA ^[2]		Viewing Angle ^[1]	
			Min.	Тур.	201/2	
APHHS1005F3C-70MAV	Infrared (GaAs)	Water Clear	5	8		
			*3	*5	140°	

- Notes:
 0.1/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
 Radiant Intensity / luminous flux: +/-15%.
 * Radiant intensity value is traceable to CIE127-2007 standards.

Kingbright

ELECTRICAL / OPTICAL CHARACTERISTICS at T_A=25°C

Parameter	Symbol	Emitting Color	Value		Unit
Farameter		Emitting Color	Тур.	Max.	Unit
Wavelength at Peak Emission I_F = 70mA	λ_{peak}	Infrared	940	-	nm
Spectral Bandwidth at 50% Φ REL MAX I _F = 70mA	Δλ	Infrared	50	-	nm
Capacitance	С	Infrared	90	-	pF
Forward Voltage $I_F = 70 \text{mA}$	V _F ^[1]	Infrared	1.33	1.9	V
Reverse Current (V_R = 5V)	I _R	Infrared	-	10	uA

Notes:

Forward voltage: ±0.1V.
 Wavelength value is traceable to CIE127-2007 standards.
 Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.

ABSOLUTE MAXIMUM RATINGS at T_A=25°C


Parameter	Symbol	Value	Unit
Power Dissipation	P _D	133	mW
Reverse Voltage	V _R	5	V
Junction Temperature	Tj	115	°C
Operating Temperature	T _{op}	-40 to +85	°C
Storage Temperature	T _{stg}	-40 to +85	°C
DC Forward Current	I _F	70	mA
Peak Forward Current	۱ _{FM} ^[1]	1200	mA
Electrostatic Discharge Threshold (HBM)	-	8000	V

Notes:


1. 1/100 Duty Cycle, 10us Pulse Width. 2. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.

Kingbright


TECHNICAL DATA




SPATIAL DISTRIBUTION




INFRARED




REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS



TAPE SPECIFICATIONS (units : mm)



REEL DIMENSION (units : mm)



- Notes: 1. Don't cause stress to the LEDs while it is exposed to high temperature. 2. The maximum number of reflow soldering passes is 2 times. 3. Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.

Kingbright


(33P) CODE: XXXX

TY: XXXXXXXXXXXXXXXX

APHHS1005F3C-70MAV

PACKING & LABEL SPECIFICATIONS

1 RoHS Complian



PRECAUTIONARY NOTES

- 1.
- The information included in this document reflects representative usage scenarios and is intended for technical reference only. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening 3.
- 4 The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright. All design applications should refer to Kingbright application notes available at <u>http://www.KingbrightUSA.com/Application</u>
- 5.
- 6. onNotes